30mm Pushbutton NEMA 4, 12, and 13 Wall-Mount







Applications

Designed to hold all standard 30mm [1.18 in] brands of pushbuttons, switches and pilot lights. Provides protection from dirt, dust, oil and water.

Construction

- Bodies and doors fabricated from 14-gauge steel
- · Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures 9.50 x 6.25 x 3.09in [241 x 159 x 78mm] and larger have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- · Grounding provisions provided

Finish

• ANSI 61 gray polyester powder inside and out over phosphatized surfaces

Listings

- UL 508, 4, 12, and 13 [UL File E64791]
- NEMA/EEMAC 4, 12, and 13
- PB16(BC) and PB25(BC) meet NEMA 12 only



Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days Color indicates shipping lead time in business days.


1	30mm Pushbutton NEMA 4, 12, and 13 Wall-Mount							
Pushbutton Enclosure	Price	With Blank Cover	Price	# Holes	Enclosure Size HxWxD			
<u>PB1</u>	\$76.00	PB1BC	\$76.00	1	3.76 x 3.56 x 3.14 [96 x 90 x 80]			
<u>PB2</u>	\$87.00	PB2BC	\$89.00	2	6.01 x 3.56 x 3.10 [153 x 90 x 79]			
<u>PB3</u>	\$97.00	PB3BC	\$100.00	3	8.26 x 3.56 x 3.10 [210 x 90 x 79]			
<u>PB4</u>	\$110.00	PB4BC	\$110.00	4	10.51 x 3.56 x 3.10 [267 x 90 x 79]			
PB4S	\$124.00	PB4SBC	\$107.00	4	7.51 x 6.56 x 3.38 [191 x 167 x 86]			
<u>PB5</u>	\$120.00	PB5BC	\$120.00	5	12.76 x 3.56 x 3.10 [324 x 90 x 79]			
<u>PB6</u>	\$149.00	PB6BC	\$141.00	6	9.76 x 6.56 x 3.38 [248 x 167 x 86]			
PB6VL	\$134.00	PB6VLBC	\$133.00	6	15.01 x 3.56 x 3.10 [381 x 90 x 79]			
<u>PB8</u>	\$161.00	PB8BC	\$157.00	8	20.51 x 3.56 x 3.10 [521 x 90 x 79]			
<u>PB9</u>	\$165.00	PB9BC	\$146.00	9	9.76 x 8.81 x 3.38 [248 x 224 x 86]			
<u>PB10</u>	\$183.00	PB10BC	\$170.00	10	25.01 x 3.56 x 3.14 [635 x 90 x 80]			
PB12	\$186.00	PB12BC	\$186.00	12	12.01 x 8.81 x 3.38 [305 x 224 x 86]			
PB16	\$213.00	PB16BC	\$209.00	16	12.01 x 11.06 x 3.38 [305 x 281 x 86]			
PB25	\$263.00	PB25BC	\$263.00	25	14.26 x 13.31 x 3.38 [362 x 338 x 86]			

Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawings. Letters in table correspond to letters on dimensional drawings.
*Only meets N12.

30mm Pushbutton NEMA 4, 12, and 13 Wall-Mount



Dimensions



22mm Pushbutton NEMA 4, 4X, 12, and 13 **Stainless Steel Wall-Mount**





PBGX2SS

Applications

Designed to hold all standard 22mm brands of miniature oil-tight pushbuttons, switches and pilot lights. Provide protection from dirt, dust, oil and water.

Construction

- Fabricated from 304 or 316 stainless steel
- · Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" miniature pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 6 or more holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- · Grounding provisions provided

Finish

· Smooth-grained finish

Listings

- UL 508A, Type 4, 4X, 12, 13 [File E64791]
- NEMA Type 4, 4X, 12, and 13
- cULus Certified Type 4, 4X, 12, and 13
- IEC 60529, IP66




Shipping Schedule Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days Color indicates shipping lead time in business days

22mm Pushbutton NEMA 4, 4X, 12, and 13 Wall-Mount							
304 Stainless Steel	Price	316 Stainless Steel	Price	# Holes	Size HxWxD	Drawing Link	
PBGX1SS	\$272.00	PBGX1SSA	\$544.00	1	3.56 x 3.06 x 3.83 [90 x 78 x 97]	PDF	
PBGX2SS	\$309.00	PBGX2SSA	\$618.00	2	5.44 x 3.06 x 3.83 [138 x 78 x 97]	PDF	
PBGX3SS	\$349.00	PBGX3SSA	\$698.00	3	7.31 x 3.06 x 3.83 [186 x 78 x 97]	<u>PDF</u>	
PBGX4SS	\$462.00	PBGX4SSA	\$924.00	4	9.19 x 3.06 x 3.83 [233 x 78 x 97]	<u>PDF</u>	
PBGX6SS	\$582.00	PBGX6SSA	\$1,164.00	6	8.81 x 5.31 x 4.58 [224 x 135 x 116]	PDF	
Note: Dimensions in inches [millimeters].							

22mm Pushbutton NEMA 4, 4X, 12, and 13 **Stainless Steel Wall-Mount**



Dimensions



PBGX1SS PBGX2SS PBGX3SS PBGX4SS PBGX6SS

30mm Pushbutton NEMA 4, 4X, 12, and 13 Stainless Steel Wall-Mount



Application

Designed to hold standard 30mm [1.18 in] pushbuttons, switches, and pilot lights. Provides protection from dirt, dust, oil and water. Also used in areas where serious corrosion problems exist.



Construction

- Fabricated from 14-gauge 304 stainless steel
- Continuously-welded seams ground smooth
- Cover secured by stainless steel captive screws threaded into sealed wells
- Closed-cell oil-resistant neoprene gasket
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches, and pilot lights
- External mounting plate on top and bottom of enclosure
- · Grounding provisions provided
- PBSS Enclosures with 6 or more holes have internal detachable hinges to hold cover open during service, yet permit quick removal

Finish

 Stainless steel cover and outside of enclosure have #3 intermediate polished finish

Listings

• UL 508, 4, 4X, 12, and 13 [UL file E64791]



• NEMA/EEMAC 4, 4X, 12, and 13


Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days


Color indicates shipping lead time in business days.

30mm Pushbutton NEMA 4, 4X, 12, and 13 Stainless Steel Wall-Mount						
304 Stainless Steel	Price	316L Stainless Steel	Price	# Holes	Enclosure Size HxWxD	
PBSS1	\$148.00	PBSS1A	\$188.00	1	3.75 x 3.56 x 3.01 [95 x 90 x 76]	
PBSS2	\$175.00	PBSS2A	\$223.00	2	6.00 x 3.56 x 3.01 [152 x 90 x 76]	
PBSS3	\$202.00	PBSS3A	\$257.00	3	8.25 x 3.56 x 3.01 [230 x 90 x 76]	
PBSS4	\$236.00	PBSS4A	\$291.00	4	10.50 x 3.56 x 3.01 [267 x 90 x 76]	
PBSS6	\$310.00	PBSS6A	\$385.00	6	9.75 x 6.56 x 3.29 [248 x 167 x 84]	
PBSS9	\$369.00	PBSS9A	\$518.00	9	9.75 x 8.81 x 3.29 [248 x 224 x 84]	
PBSS12	\$422.00	PBSS12A	\$593.00	12	12.00 x 8.81 x 3.29 [305 x 224 x 84]	
Note: Dimensions in inches [millimeters].						

Dimensions



PBSS HOLE ARRANGEMENTS





30mm Pushbutton NEMA 12 and 13 Slim Line Wall-Mount






Dimensions





STANDARD 4-WAY PUSHBUTTON

PB HOLE ARRANGEMENTS



Applications

Designed to hold all standard 30mm [1.18 in] brands of pushbuttons, switches and pilot lights. Provides protection from dirt, dust, oil and water. This slimline model is designed for conditions where enclosures must fit within very limited areas.

Construction

- Fabricated from 14-gauge steel
- Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- · Grounding provisions provided

Finish

• ANSI 61 gray polyester powder inside and out over phosphatized surfaces

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

30mm Pushbutton NEMA 12 and 13 Slim Line Wall-Mount				
Part Number	Price	# Holes	Size HxWxD	
PSL1	\$70.00	1	4.32 x 2.81 x 2.83 [110 x 71 x 72]	
PSL2	\$78.00	2	6.57 x 2.81 x 2.83 [167 x 71 x 72]	
PSL3	\$87.00	3	8.82 x 2.81 x 2.83 [224 x 71 x 72]	
PSL4	\$97.00	4	11.07 x 2.81 x 2.83 [281 x 71 x 72]	
PSL4		-	11.07 x 2.81 x 2.83 [281 x 71 x 72]	

Notes: Dimensions in inches [millimeters].

22mm Pushbutton NEMA 12 and 13 Wall-Mount



PBGX9

Applications

Designed to hold all standard 22mm [0.87 in] brands of miniature oil-tight pushbuttons, switches and pilot lights. Provide protection from dirt, dust, oil and water.

Construction

- Fabricated from 14-gauge steel,
- Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" miniature pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 6 or more holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- · Grounding provisions provided

Wwiegwann[®]

Finish

• ANSI 61 gray polyester powder inside and out over phosphatized surfaces

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13




Shipping Schedule						
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days		
Color indicates shipping lead time in business days.						


22mm P	22mm Pushbutton NEMA 12 and 13 Wall-Mount						
Carbon Steel	Price	# Holes	Size HxWxD	Drawing Link			
PBGX1	\$81.00	1	3.56 x 3.06 x 3.83 [90 x 78 x 97]	<u>PDF</u>			
PBGX2	\$84.00	2	5.44 x 3.06 x 3.83 [138 x 78 x 97]	<u>PDF</u>			
PBGX3	\$101.00	3	7.31 x 3.06 x 3.83 [186 x 78 x 97]	<u>PDF</u>			
PBGX4	\$111.00	4	9.19 x 3.06 x 3.83 [233 x 78 x 97]	PDF			
PBGX6	\$141.00	6	8.81 x 5.31 x 4.58 [224 x 135 x 116]	PDF			
PBGX9	\$189.00	9	8.81 x 6.81 x 4.58 [224 x 173 x 116]	<u>PDF</u>			
PBGX12	\$175.00	12	10.69 x 6.81 x 4.58 [272 x 173 x 116]	<u>PDF</u>			
PBGX20	\$193.00	20	12.56 x 8.31 x 4.58 [319 x 211 x 116]	<u>PDF</u>			
PBGX25	\$209.00	25	12.56 x 9.81 x 4.58 [319 x 249 x 116]	PDF			
Note: Dimensions in inches [millimeters].							

22mm Pushbutton NEMA 12 and 13 Wall-Mount





Dimensions





PBGX HOLE ARRANGEMENTS





PBGX1SS PBGX2SS PBGX3SS PBGX4SS PBGX6SS

30mm Pushbutton Extra-Deep Wall-Mount

WIEGMANN®

Applications

Designed to hold 30mm [1.18 in] oiltight pushbuttons, switches and pilot lights. Provides protection from dirt, dust, oil and water. Extra deep design accommodates additional contact blocks for pushbuttons.



Construction

- Bodies and doors fabricated from 14-gauge steel
- Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 2 or more holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- · Grounding provisions provided

Finish

- Painted Steel: ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Stainless steel: #3 intermediate polished finish

- UL 508, 4, 12 and 13 (stainless steel enclosures also 4X) [UL File E64791]
- NEMA/EEMAC 4, 12 and 13 (stainless steel enclosures also 4X)



Shipping Schedule						
Same day	1 - 5 days	1 - 7 days	1-10 days	1 - 15 days	1 - 20 days	
Color indicates shipping lead time in business days.						


30mm Pushbutton Extra-Deep Wall-Mount Painted Steel							
Painted Steel	Price	Enclosure Size HxWxD	# Holes	Drawing Link			
PBXD1	\$94.00	4.32 x 4.38 x 5.14 [110 x 111 x 131]	1	PDF			
PBXD2	\$137.00	6.31 x 4.38 x 5.14 [160 x 111 x 131]	2	<u>PDF</u>			
PBXD3	\$122.00	8.26 x 4.38 x 5.14 [210 x 111 x 131]	3	<u>PDF</u>			
PBXD4S	\$138.00	7.57 x 6.63 x 5.14 [192 x 168 x 131]	4	<u>PDF</u>			
PBXD4	\$147.00	10.31 x 4.38 x 5.14 [262 x 111 x 131]	4	PDF			
PBXD6	\$158.00	9.82 x 6.63 x 5.14 [249 x 168 x 131]	6	PDF			
PBXD9	\$181.00	9.82 x 8.88 x 5.14 [249 x 226 x 131]	9	PDF			
PBXD10	\$197.00	14.32 x 6.63 x 5.14 [364 x 168 x 131]	10	PDF			
PBXD12	\$207.00	12.07 x 8.88 x 5.14 [307 x 226 x 131]	12	PDF			
PBXD16	\$232.00	12.07 x 11.13 x 5.14 [307 x 283 x 131]	16	PDF			
PBXD16V	\$256.00	21.07 x 6.63 x 5.14 [535 x 168 x 131]	16	PDF			
PBXD20	\$260.00	14.32 x 11.13 x 5.14 [364 x 283 x 131]	20	<u>PDF</u>			
PBXD25	\$293.00	14.32 x 13.38 x 5.14 [364 x 340 x 131]	25	<u>PDF</u>			
Note: Dimensions in inches [millimeters].							

30mm Pushbutton Extra-Deep Wall-Mount Stainless Steel								
Stainless Steel	Price	Enclosure Size HxWxD	# Holes	Drawing Link				
PBXD1SS	\$181.00	4.25 x 4.34 x 5.01 [108 x 110 x 127]	1	PDF				
PBXD2SS	\$218.00	6.25 x 4.34 x 5.01 [159 x 110 x 127]	2	<u>PDF</u>				
PBXD4SS	\$284.00	10.25 x 4.34 x 5.01 [260 x 110 x 127]	4	<u>PDF</u>				
PBXD3SS	\$365.00	8.25 x 4.34 x 5.01 [210 x 110 x 127]	3	<u>PDF</u>				
PBXD16SS	\$649.00	12.00 x 11.09 x 5.01 [305 x 282 x 127]	16	<u>PDF</u>				
Note: Dimensions in inches [millimeters].								

30mm Pushbutton Extra-Deep Wall-Mount



Dimensions



PBXD HOLE ARRANGEMENTS 0 0 0000 0 0 000 000 \bigcirc \bigcirc \circ 00 \bigcirc 000 \circ 0 \bigcirc \circ \circ \bigcirc \circ PBXD1 **PBXD2** PBXD3 PBXD4 PBXD4S PBXD6 PBXD9 PBXD10 PBXD12 \bigcirc 0 0 0.67 -[17.0] 0.19 0 [4.8] 00000 00 0000 00000 000 \circ 0 0000 ø1.20 -[ø30.5] 00000 0000 0000 0 \circ 0000 0 000 00000 STANDARD 4-WAY PUSHBUTTON 00000 000 \bigcirc 000

PBXD16V

PBXD20

PBXD25

PBXD16

30mm Pushbutton with 2.5 in Hole Spacing NEMA 12 and 13 Wall-Mount



Applications

Designed to hold 30mm [1.18 in] oil-tight pushbuttons, switches and pilot lights with extra size to allow 2.5 in [63.5 mm] between centers of pushbutton holes. Provides protection from dirt, dust, oil and water.

Construction

- Fabricated from 14-gauge steel
- Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- Cover held in place by continuous hinge
- Subpanel included with enclosure
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tightpushbuttons, witches and pilot lights
- · Grounding provisions provided

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days
Color indicates shipping lead time in business days.

30mm Pushbutton with 2.5 in Hole Spacing NEMA 12 and 13 Wall-Mount					
Part Number	Price	# Holes	Enclosure Size HxWxD		
PBYX4S	\$174.00	4	8.82 x 7.88 x 6.33 [224 x 200 x 161]		
PBYX6	\$205.00	6	11.32 x 7.88 x 6.33 [288 x 200 x 161]		
PBYX9	\$239.00	9	11.32 x 10.38 x 6.33 [288 x 264 x 161]		
PBYX12	\$270.00	12	13.82 x 10.38 x 6.33 [351 x 264 x 161]		
PBYX16	\$309.00	16	13.82 x 12.88 x 6.33 [351 x 327 x 161]		
PBYX20	\$346.00	20	16.32 x 12.88 x 6.33 [415 x 327 x 161]		
PBYX25	\$389.00	25	16.32 x 15.38 x 6.33 [415 x 391 x 161]		
PBYX30	\$424.00	30	18.82 x 15.38 x 6.33 [478 x 391 x 161]		
PBYX36	\$479.00	36	18.82 x 17.88 x 6.33 [478 x 454 x 161]		
PBYX42	\$525.00	42	21.32 x 17.88 x 6.33 [542 x 454 x 161]		
Note: Dimensions in inches [millimeters].					

WINES WIANN®

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Included subpanels are white polyester powder over phosphatized surfaces


- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13




30mm Pushbutton with 2.5 in Hole Spacing NEMA 12 and 13 Wall-Mount




Dimensions





PBYX HOLE ARRANGEMENTS



30mm Pushbutton NEMA 12 and 13 Operator Consolet



Applications

Designed for use where slanted control surfaces are wanted. Enclosures may be mounted in a variety of ways to meet specific requirements. Receives standard 30mm [1.18 in] oil-tight pushbuttons, switches and pilot lights. Provides protection from dirt, dust, oil, and water.

W.WIEGWANN[®]

Construction

- Fabricated from 14-gauge steel
- Closed-cell oil- resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 2 or more rows of holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- Grounding provisions provided

Finish

 ANSI 61 gray polyester powder inside and out over phosphatized surfaces

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



Shipping Schedule						
Same day	1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days					
Color indicates shipping lead time in business days.						

30mm Pushbutton NEMA 12 and 13						
		Operato	r Consolet			
Part Number	Price	# Holes	Enclosure Size HxWxD			
WPBA1	\$101.00	1	3.77 x 3.59 x 4.88 [96 x 91 x 124]			
WPBA2	\$118.00	2	3.77 x 5.84 x 4.88 [96 x 148 x 124]			
WPBA3	\$134.00	3	3.77 x 8.09 x 4.88 [96 x 205 x 124]			
WPBA4	\$151.00	4	3.77 x 10.34 x 4.88 [96 x 263 x 124]			
WPBA4S	\$169.00	4	7.52 x 6.59 x 6.76 [191 x 167 x 172]			
WPBA6	\$196.00	6	7.52 x 8.84 x 6.76 [191 x 225 x 172]			
WPBA8	\$222.00	8	7.52 x 11.09 x 6.76 [191 x 282 x 172]			
WPBA9	\$232.00	9	9.77 x 8.84 x 7.88 [248 x 225 x 200]			
WPBA10	\$246.00	10	7.52 x 13.34 x 6.76 [191 x 339 x 172]			
WPBA12	\$269.00	12	7.52 x 15.59 x 6.76 [191 x 396 x 172]			
WPBA12S	\$258.00	12	12.02 x 8.84 x 9.01 [305 x 225 x 229]			
WPBA16	\$288.00	16	7.52 x 20.09 x 6.76 [191 x 510 x 172]			
WPBA16S	\$333.00	16	12.02 x 11.09 x 9.01 [305 x 282 x 229]			
WPBA20	\$332.00	20	12.02 x 13.34 x 9.01 [305 x 339 x 229]			
WPBA25	\$378.00	25	14.27 x 13.34 x 10.13 [362 x 339 x 257]			
WPBA30	\$412.00	30	14.27 x 15.59 x 10.13 [362 x 396 x 257]			
Note: Dimensions in inches [millimeters].						

30mm Pushbutton NEMA 12 and 13 Operator Consolet



Dimensions

