

#### **Subpanels**

Subpanels are not included with most enclosures and must be purchased separately.

The specifications table for each enclosure family list the part number of the subpanel that goes with each enclosure.

#### Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14-gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures:B, B\_CH, BN4, BN4\_CH, BN4\_CHQT, BN4\_SS, BN4\_CHSS, BN4\_CHSSA, BN4\_CHQTSS, BN4\_ CHQTSSA ("\_" refers to dimensions).




Shipping Schedule						
Same day	Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days					
Color indicates shipping lead time in business days.						

	Subpanels for B and BN4 Enclosures									
Painted Steel	Price	304 Stainless Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW	Subpanel Size AxB			
P0604	\$5.00	P0604SS	\$16.75	P0604G	Retired	6 x 4	4.88 x 2.88 [124 x 73]			
<u>P0606</u>	\$6.00	P0606SS	\$20.50	P0606G	Retired	6 x 6	4.88 x 4.88 [124 x 124]			
<u>P0806</u>	\$6.75	P0806SS	\$24.50	P0806G	Retired	8 x 6	6.88 x 4.88 [175 x 124]			
P0808	\$8.00	_	_	P0808G	Retired	8 x 8	6.88 x 6.88 [175 x 175]			
P1008	\$8.75	P1008SS	\$35.50	P1008G	Retired	10 x 8	8.88 x 6.88 [226 x 175]			
<u>P1010</u>	\$11.00	_	_	P1010G	Retired	10 x 10	8.88 x 8.88 [226 x 226]			
P1206	\$8.75	_	_	P1206G	Retired	12 x 6	10.88 x 4.88 [276 x 124]			
P1210	\$12.75	P1210SS	\$50.00	P1210G	Retired	12 x 10	10.88 x 8.88 [276 x 226]			
P1212	\$15.00	P1212SS	\$58.00	P1212G	Retired	12 x 12	10.88 x 10.88 [276 x 276]			
P1408	\$12.00	_	_	P1408G	Retired	14 x 8	12.88 x 6.88 [327 x 175]			
P1412	\$16.50	P1412SS	\$67.00	P1412G	Retired	14 x 12	12.88 x 10.88 [327 x 276]			
P1610	\$16.25	_	_	P1610G	Retired	16 x 10	14.88 x 8.88 [378 x 226]			
P1614	\$22.00	P1614SS	\$88.00	<u>P1614G</u>	Retired	16 x 14	14.88 x 12.88 [378 x 327]			

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.





#### Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

- 14-gauge
- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized panels have a conductive finish (no paint)
- Panels listed fit the following enclosures:
- NEMA 1 small (N1C)
- NEMA 3R small (RHC)
- NEMA 12 WA\_GIE




	Shipping Schedule						
Same day	Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days						
Color indicates shipping lead time in business days.							


	Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures									
Painted Steel	Price	Galvanized	Price	Perforated	Price	Nominal Enclosure Size HxW	Subpanel Size AxB			
N1P0606	\$5.00	N1P0606G	Retired	N1P0606PP	Retired	6 x 6	4.25 x 4.25 [108 x 108]			
N1P0608	\$5.75	N1P0608G	\$5.75	N1P0608PP	Retired	6 x 8	6.25 x 4.25 [159 x 108]			
N1P0808	\$6.75	N1P0808G	\$6.75	N1P0808PP	Retired	8 x 8	6.25 x 6.25 [159 x 159]			
N1P0810	\$8.00	N1P0810G	\$8.00	N1P0810PP	Retired	8 x 10	8.25 x 6.25 [210 x 159]			
N1P1010	\$9.50	N1P1010G	Retired	N1P1010PP	Retired	10 x 10	8.25 x 8.25 [210 x 210]			
N1P1012	\$11.00	N1P1012G	Retired	N1P1012PP	Retired	10 x 12	10.25 x 8.25 [260 x 210]			
N1P1212	\$13.25	N1P1212G	Retired	N1P1212PP	Retired	12 x 12	10.25 x 10.25 [260 x 260]			
N1P1214	\$14.75	N1P1214G	Retired	N1P1214PP	Retired	12 x 14	12.25 x 10.25 [311 x 260]			
N1P1216	\$16.50	N1P1216G	Retired	N1P1216PP	Retired	12 x 16	14.25 x 10.25 [362 x 260]			
N1P1220	\$23.00	N1P1220G	Retired	N1P1220PP	Retired	12 x 20	18.25 x 10.25 [464 x 260]			

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

#### **Dimensions**





Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25in [6 mm] spacing.



#### **Subpanels for Medium NEMA 1 Enclosures**

- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Panels listed fit NEMA 1 large (N1C) enclosures




Letters in table correspond to letters on dimensional drawing.



		Subpanels fo	r Mediu	ım NEMA 1 Eı	nclosures	
Painted Steel	Price	Perforated	Price	Nominal Enclosure Size HxW	Steel Gauge	Subpanel Size AxB
N1P1216L	\$17.25	N1P1216LPP	Retired	16 x 12	14	13.00 x 10.50 [330 x 267]
N1P1616	\$21.00	N1P1616PP	Retired	16 x 16	14	13.00 x 14.50 [330 x 368]
N1P1620	\$25.00	N1P1620PP	Retired	20 x 16	14	17.00 x 14.50 [432 x 368]
N1P1624	\$31.00	N1P1624PP	Retired	24 x 16	14	21.00 x 14.50 [533 x 368]
N1P2016	\$25.50	N1P2016PP	Retired	16 x 20	14	13.00 x 18.50 [330 x 470]
N1P2020	\$34.00	N1P2020PP	Retired	20 x 20	14	17.00 x 18.50 [432 x 470]
N1P2024	\$38.50	N1P2024PP	Retired	24 x 20	14	21.00 x 18.50 [533 x 470]
N1P2030	\$83.00	N1P2030PP	Retired	30 x 20	14	26.00 x 18.50 [660 x 470]
N1P2420	\$39.00	N1P2420PP	Retired	20 x 24	14	17.00 x 22.50 [432 x 572]
N1P2424	\$72.00	N1P2424PP	Retired	24 x 24	14	21.00 x 22.50 [533 x 572]
N1P2430	\$96.00	N1P2430PP	Retired	30 x 24	14	26.00 x 22.50 [660 x 572]
N1P2436	\$98.00	N1P2436PP	Retired	36 x 24	14	32.00 x 22.50 [813 x 572]
N1P3030	\$116.00	N1P3030PP	Retired	30 x 30	14	26.00 x 28.50 [660 x 724]
N1P3036	\$141.00	N1P3036PP	Retired	36 x 30	14	32.00 x 28.50 [813 x 724]
Notes: Dimensions i	n inches [mi	llimeters].				

#### **Dimensions**



NOTE: SUBPANELS LARGER THAN 20 X 20 HAVE (2) 0.31" GROUND HOLES.

Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25in [6 mm] spacing.




## Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

- 12-gauge steel (perforated subpanels are 14-gauge)
- Subpanels with any side over17 in [432 mm] have 0.25 in [6mm] flange on all sides
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)Panels listed fit the following enclosures:
- NEMA 1 large (N1C, 42 in [1067 mm] width and wider)
- NEMA 12 single door wall-mount (N12)
- NEMA 12 two-door wall-mount (WA\_WF)
- NEMA 12 single door flush wall-mount (WA\_FM)
- NEMA 4 (N4) and 4X (SSN) single door wall-mount
- NEMA 12 operator consoles (WC9)
- NEMA 12 Wall Disconnect (SDN12\_PL and ABN12)
- NEMA 4 and 4X Wall-Mount Disconnect (SSN4 and SSN4X)

Note: Use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures only. Do NOT use NPxxxx subpanels in N412 Ultimate Series enclosures with a C in the suffix.



#### **Dimensions**



NOTE: SUBPANELS LARGER THAN 20 X 20 HAVE (2) 0.31" GROUND HOLES.

Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25 in [6 mm] spacing.



**Shipping Schedule** Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days Color indicates shipping lead time in business days.

Subpan	els for	NEMA 1,	12, 4	and 4X W	all-Mo Cons		sures	and WC9 NE	MA 12 Operator
Painted Steel	Price	Galvanized	Price	Perforated	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
NP1212	\$18.50	NP1212G	Retired	_	_	_	_	12 x 12	9.00 x 9.00 [229 x 229]
NP1224	\$45.50	NP1224G	Retired	_	_	_	_	24 x 12	9.00 x 21.00 [229 x 533]
NP1612	\$33.00	<u>NP1612G</u>	Retired	<u>NP1612PP</u>	Retired	<u>NP1612SS</u>	\$87.00	12 x 16 16 x 12	13.00 x 9.00 [330 x 229]
NP1616	\$40.50	NP1616G	Retired	NP1616PP	Retired	NP1616SS	\$106.00	16 x 16	13.00 x 13.00 [330 x 330]
NP2012	\$38.00	NP2012G	Retired	_	_	_	_	20 x 12	17.00 x 9.00 [432 x 229]
NP2016	\$48.00	NP2016G	Retired	NP2016PP	Retired	NP2016SS	\$128.00	20 x 16	17.00 x 13.00 [432 x 330]
NP2020	\$58.00	NP2020G	Retired	NP2020PP	Retired	NP2020SS	\$165.00	20 x 20	17.00 x 17.00 [432 x 432]
NP2416	\$56.00	NP2416G	Retired	_	_	NP2416SS	\$159.00	24 x 16	21.00 x 13.00 [533 x 330]
NP2420	\$75.00	NP2420G	Retired	NP2420PP	Retired	NP2420SS	\$200.00	24 x 20	21.00 x 17.00 [533 x 432]
NP2424	\$86.00	NP2424G	Retired	NP2424PP	Retired	NP2424SS	\$233.00	24 x 24	21.00 x 21.00 [533 x 533]
NP3016	\$75.00	NP3016G	Retired	_	_	_	_	30 x 16	27.00 x 13.00 [686 x 330]
NP3020	\$90.00	NP3020G	Retired	_	_	NP3020SS	\$268.00	30 x 20	27.00 x 17.00 [686 x 432]
NP3024	\$105.00	NP3024G	Retired	NP3024PP	Retired	NP3024SS	\$283.00	24 x 30 30 x 24	27.00 x 21.00 [686 x 533]
NP3030	\$147.00	NP3030G	Retired	NP3030PP	Retired	NP3030SS	\$452.00	30 x 30	27.00 x 27.00[686 x 686]
NP3624	\$125.00	NP3624G	Retired	NP3624PP	Retired	NP3624SS	\$386.00	36 x 24	33.00 x 21.00 [838 x 533]
NP3630	\$167.00	NP3630G	Retired	NP3630PP	Retired	NP3630SS	\$443.00	30 x 36 36 x 30	33.00 x 27.00 [838 x 686]
NP3636	\$196.00	NP3636G	Retired	NP3636PP	Retired	NP3636SS	\$535.00	36 x 36	33.00 x 33.00 [838 x 838]
NP4024	\$151.00	_	_	_	_	_	_	40 x 24	37.00 x 21.00 [940 x 533]
NP4224	\$144.00	NP4224G	Retired	_	_	_	_	42 x 24	39.00 x 21.00 [991 x 533]
NP4230	\$191.00	NP4230G	Retired	NP4230PP	Retired	NP4230SS	\$563.00	42 x 30	39.00 x 27.00 [991 x 686]
NP4236	\$225.00	NP4236G	Retired	NP4236PP	Retired	NP4236SS	\$676.00	42 x 36	39.00 x 33.00 [991 x 838]
NP4824	\$163.00	NP4824G	Retired	_	_	_		48 x 24	45.00 x 21.00 [1143 x 533]
NP4830	\$215.00	NP4830G	Retired	_	_	_		48 x 30	45.00 x 27.00 [1143 x 686]
NP4836	\$254.00	NP4836G	Retired	NP4836PP	Retired	NP4836SS	\$731.00	48 x 36	45.00 x 33.00 [1143 x 838]
NP6030	\$263.00	NP6030G	Retired	_	_	_	_	60 x 30	57.00 x 27.00 [1448 x 686]
NP6036	\$313.00	NP6036G	Retired	NP6036PP	Retired	NP6036SS	\$965.00	60 x 36	57.00 x 33.00 [1448 x 838]
NP7230	\$302.00	NP7230G	\$327.00	_	_	_	_	72 x 30	69.00 x 27.00 [1753 x 686]
NP7236	\$371.00	NP7236G	\$402.00	_	_	_	_	72 x 36	69.00 x 33.00 [1753 x 838]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions in this table.





## **Subpanels for Ultimate Series Wall-Mount Enclosures**

- 12-gauge steel
- $\bullet$  Subpanels with dimensions 30 x 30 in [ 762 x 762 mm] and larger are flanged on all sides. Smaller subpanels are flanged on two sides
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels listed fit all styles of N412 Ultimate Series wall-mount enclosures, including slope top and disconnect enclosures

Note: NPxxxxC subpanels will not fit in older NEMA 4/12 enclosures (purchased prior to 3-23-05) that do not have a C suffix. For example: Subpanel NP1212C will not fit enclosures N412121206 or N412121206SS.









#### **Subpanels for Ultimate Series Wall-Mount Enclosures**



		Oubpullele	or ordin	idto Correo I	vall ivi	ount Enclosur	<u></u>
Painted Steel	Price	Galvanized	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW*	Subpanel Size HxW
NP1212C	\$15.50	NP1212CG	Retired	_	_	12 x 12	10.20 x 10.20 [259 x 259]
NP1612C	\$16.75	NP1612CG	Retired	<u>NP1612SSC</u>	\$87.00	16 x 12	14.20 x 10.20 [361 x 259]
NP1616C	\$40.50	NP1616CG	Retired	<u>NP1616SSC</u>	\$106.00	16 x 16	14.20 x 14.20 [361 x 361]
NP2016C	\$48.00	NP2016CG	Retired	NP2016SSC	\$128.00	16 x 20 20 x 16	18.20 x 14.20 [462 x 361]
NP2020C	\$58.00	NP2020CG	Retired	NP2020SSC	\$165.00	20 x 20	18.20 x 18.20 [462 x 462]
NP2416C	\$56.00	NP2416CG	Retired	NP2416SSC	\$159.00	24 x 16	22.20 x 14.20 [564 x 361]
NP2420C	\$56.00	NP2420CG	Retired	NP2420SSC	\$200.00	24 x 20	22.20 x 18.20 [564 x 462]
NP2424C	\$86.00	NP2424CG	Retired	NP2424SSC	\$233.00	24 x 24	22.20 x 22.20 [564 x 564]
NP3020C	\$90.00	NP3020CG	Retired	_	_	30 x 20	28.20 x 18.20 [716 x 462]
NP3024C	\$105.00	NP3024CG	Retired	<u>NP3024SSC</u>	\$306.00	30 x 24	28.20 x 22.20 [716 x 564]
NP3030C	\$147.00	NP3030CG	Retired	NP3030SSC	\$418.00	30 x 30	28.20 x 28.20 [716 x 716]
NP3624C	\$125.00	NP3624CG	Retired	NP3624SSC	\$357.00	24 x 36 36 x 24	34.20 x 22.20 [869 x 564]
NP3630C	\$167.00	NP3630CG	Retired	NP3630SSC	\$443.00	36 x 30	34.20 x 28.20 [869 x 716]
NP3636C	\$196.00	NP3636CG	Retired	NP3636SSC	\$535.00	36 x 36	34.20 x 34.20 [869 x 869]
NP4224C	\$244.00	_	_	_	_	24 x 42	40.20 x 22.20 [1021 x 564]
NP4024C	\$151.00	NP4024CG	Retired	_	_	40 x 24	38.20 x 22.20 [970 x 564]
NP4242C	\$418.00	_	_	_	_	42 x 42	40.20 x 40.20 [1021 x 1021]
NP4230C	\$225.00	_	_	_	_	30 x 42 42 x 32	40.20 x 28.20 [1021 x 716]
NP4236C	\$225.00	NP4236CG	Retired	NP4236SSC	\$676.00	36 x 42 42 x 36	40.20 x 34.20 [1021 x 869]
NP4824C	\$163.00	NP4824CG	Retired	_	_	24 x 48 48 x 24	46.20 x 22.20 [1173 x 564]
NP4830C	\$336.00	_	_	_	_	30 x 48	46.20 x 28.20 [1173 x 716]
NP4842C	\$562.00			_	_	42 x 48	46.20 x 40.20 [1173 x 1021]
NP4836C	\$254.00	NP4836CG	Retired	NP4836SSC	\$676.00	36 x 48 48 x 36	46.20 x 34.20 [1173 x 869]
NP4848C	\$625.00	_	_	_	_	48 x 48	46.20 x 46.20 [1173 x 1173]
NP6030C	\$446.00	_	_	_	_	30 x 60	58.20 x 28.20 [1478 x 716]
NP6036C	\$313.00	NP6036CG	Retired	NP6036SSC	\$965.00	36 x 30 60 x 36	58.20 x 34.20 [1478 x 869]
NP6042C	\$627.00	_	_	_	_	42 x 60	58.20 x 40.20 [1478 x 1021]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions in this table.



#### **Subpanels for Two-Door Floor-Mount Enclosures**

- Subpanels are fabricated from 10-gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor-mount enclosures and some double-door wall-mount enclosures




	Subpanels for Two-door Floor-Mount Enclosures							
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB			
NPDD4242	\$260.00	NPDD4242G	Retired	42 x 42	39.00 x 39.00 [991 x 991]			
NPDD4260	Retired	NPDD4260G	Retired	42 x 60	38.00 x 56.00 [965 x 1422]			
NPDD4842	\$294.00	NPDD4842G	Retired	48 x 42	45.00 x 39.00 [1143 x 991]			
NPDD4848	\$352.00	NPDD4848G	Retired	48 x 48	44.00 x 44.00 [1118 x 1118]			
NPDD5442	\$314.00	NPDD5442G	Retired	54 x 42	50.00 x 38.00 [1270 x 965]			
NPDD6048	\$427.00	NPDD6048G	Retired	60 x 48	44.00 x 56.00 [1118 x 1422]			
NPDD6060	\$527.00	NPDD6060G	Retired	60 x 60	56.00 x 56.00 [1422 x 1422]			
NPDD7260	\$628.00	NPDD7260G	Retired	72 x 60	56.00 x 68.00 [1422 x 1727]			
NPDD7272	\$750.00	_	_	72 x 72	68.00 x 68.00 [1727 x 1727]			




Letters in table correspond to letters on dimensional drawing.


\*Some floor-mount enclosures may be up to 2 in [51 mm] taller than height listed in this table.

Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions listed in this table.





# WA-F1/F2 Panels for Single-Door Freestanding Enclosures



#### **Description**

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- · Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories

## Same day 1 - 5 days 1 - 7 days 1 - 15 days Color indicates shipping lead time in business days.


Painted Steel	Price	Galvanized	Price	Steel Gauge	Panel Size HxW	Subpanel Type
WA60P24F1	\$342.00	WA60P24F1G	Retired	12	48.00 x 20.00[1219 x 508]	Full
WA60P24F2	\$246.00	WA60P24F2G	Retired	10	24.88 x 20.00 [632 x 508]	Half
WA60P36F1	\$441.00	WA60P36F1G	\$441.00	12	48.00 x 32.00 [1219 x 813]	Full
WA60P36F2	\$278.00	WA60P36F2G	\$278.00	12	24.88 x 32.00 [632 x 813]	Half
WA72P24F1	\$383.00	<u>WA72P24F1G</u>	\$383.00	12	60.00 x 20.00 [1524 x 508]	Full
WA72P24F2	Retired	WA72P24F2G	Retired	12	30.88 x 20.00 [784 x 508]	Half
WA72P30F1	\$445.00	WA72P30F1G	\$482.00	12	60.00 x 26.00 [1524 x 660]	Full
WA72P30F2	Retired	WA72P30F2G	Retired	10	30.88 x 26.00 [784 x 660]	Half
WA72P36F1	\$507.00	WA72P36F1G	\$507.00	12	60.00 x 32.00 [1524 x 813]	Full
WA72P36F2	Retired	WA72P36F2G	Retired	12	30.88 x 32.00 [784 x 813]	Half
WA90P24F1	\$445.00	WA90P24F1G	\$445.00	12	78.00 x 20.00 [1981 x 508]	Full
WA90P24F2	Retired	WA90P24F2G	Retired	10	39.88 x 20.00 [1013 x 508]	Half
WA90P36F1	\$607.00	WA90P36F1G	\$607.00	12	78.00 x 32.00 [1981 x 813]	Full
WA90P36F2	Retired	WA90P36F2G	Retired	10	39.88 x 32.00 [1013 x 813]	Half


Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

If used in a two-door enclosure, a center panel support must be ordered.

Suffix F1= full panel, F2 = half panel





Full
Half
Full
Half
Full
Half
Full
Half
Full
Half

Half


Full

Half

Full

Half

# WA-F1/F2 Panels for Two-Door Freestanding Enclosures Www.EGMANN®



#### **Description**

- Panels for two-door single-access and two-door dual-access, freestanding NEMA 12 enclosures
- Manufactured of 10-gauge steel and can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)

Color indicates shipping le	ad time in business days.	20 days		
Painted Steel	Price	Galvanized	Price	Panel Size AxB
WA60P48F1	\$708.00	WA60P48F1G	\$708.00	48.00 x 44.00 [1219 x 1118]
WA60P48F2	Retired	WA60P48F2G	Retired	24.88 x 44.00 [632 x 1118]
WA72P48F1	\$801.00	<u>WA72P48F1G</u>	\$801.00	60.00 x 44.00 [1524 x 1118]
<u>WA72P48F2</u>	Retired	<u>WA72P48F2G</u>	Retired	30.88 x 44.00 [784 x 1118]
<u>WA72P60F1</u>	\$928.00	<u>WA72P60F1G</u>	\$928.00	60.00 x 56.00 [1524 x 1422]
<u>WA72P60F2</u>	Retired	<u>WA72P60F2G</u>	Retired	30.88 x 56.00 [784 x 1422]
<u>WA72P72F1</u>	\$1,055.00	_		68.00 x 68.00 [1727 x 1727]

**WA72P72F2G** 

WA90P48F1G

WA90P48F2G

WA90P72F2G

Retired

Retired

Retired

\$1,020.00

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

Retired

\$942 00

Retired

\$1,272.00

Retired

Suffix F1 = full panel, F2 = half panel

#### **Dimensions**

**WA72P72F2** 


WA90P48F1

WA90P48F2

WA90P72F1

WA90P72F2

Note: Center panel support is supplied with a regular two-door enclosure panel. This support is used only as a brace. It is not intended to be used as a support for single-door subpanels, relay racks, etc. Use WA\_FSCPS panel supports for this purpose.



30.88 x 68.88 [784 x 1727]

78.00 x 44.00 [1981 x 1118]


39.88 x 44.00 [1013 x 1118]

78.00 x 68.00 [1981 x 1727]

39.88 x 68.00 [1013 x 1727]

# WA-SMP Series Side-Mount Panels for Freestanding Enclosures







#### **Description**

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12-gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels

## Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days Color indicates shipping lead time in business days.


Painted Steel	Price	Galvanized	Price	Panel Size AxB			
WA60SMP14	Retired	WA60SMP14G	Retired	48.00 x 14.00 [1219 x 356]			
<u>WA72SMP14</u>	\$236.00	WA72SMP14G	Retired	60.00 x 14.00 [1524 x 356]			
<u>WA72SMP20</u>	\$288.00	WA72SMP20G	Retired	60.00 x 20.00 [1524 x 508]			
<u>WA90SMP14</u>	Retired	<u>WA90SMP14G</u>	Retired	78.00 x 14.00 [1981 x 356]			
<u>WA90SMP20</u>	Retired	WA90SMP20G	Retired	78.00 x 20.00 [1981 x 508]			
Note: Dimensions i	Note: Dimensions in inches [millimeters].						





# WASP-F3/F4 Series Accessory Swing-Out Panels For Freestanding Enclosures





#### **Description**

- Panels for freestanding NEMA 12 enclosures and freestanding NEMA 4 enclosures
- Full-height and half-height swing-out panels are available
- Half-height panels can be located in the upper or lower portion of the enclosure
- · Mounting can be on either side of the enclosure
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with otherfreestanding accessories
- Fabricated from 12-gauge steel
- Mounting hardware is furnished with each panel


	Shipping Schedule							
Same day	Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days							
Color indica	Color indicates shipping lead time in business days.							

Painted Steel	Price	Galvanized	Price	Panel Size AxB	Subpanel Type
WA60SP24F3	Retired	WA60SP24F3G	Retired	48.00 x 19.00 [1219 x 483]	Full
WA60SP24F4	Retired	WA60SP24F4G	Retired	24.88 x 19.00 [632 x 483]	Half
WA60SP36F3	Retired	WA60SP36F3G	Retired	48.00 x 31.00 [1219 x 787]	Full
WA60SP36F4	Retired	WA60SP36F4G	Retired	24.88 x 31.00 [632 x 787]	Half
<u>WA72SP24F3</u>	Retired	<u>WA72SP24F3G</u>	Retired	60.00 x 19.00 [1524 x 483]	Full
<u>WA72SP24F4</u>	Retired	<u>WA72SP24F4G</u>	Retired	30.88 x 19.00 [784 x 483]	Half
WA72SP30F3	Retired	<u>WA72SP30F3G</u>	Retired	60.00 x 25.00 [1524 x 635]	Full
WA72SP30F4	Retired	WA72SP30F4G	Retired	30.88 x 25.00 [784 x 635]	Half
WA72SP36F3	Retired	WA72SP36F3G	Retired	60.00 x 31.00 [1524 x 787]	Full
WA72SP36F4	Retired	<u>WA72SP36F4G</u>	Retired	30.88 x 31.00 [784 x 787]	Half
WA90SP36F3	Retired	<u>WA90SP36F3G</u>	Retired	78.00 x 31.00 [1981 x 787]	Full
WA90SP36F4	Retired	WA90SP36F4G	Retired	39.88 x 31.00 [1013 x 787]	Half

Notes: Dimensions in inches [millimeters].


If used in a two-door enclosure, a center panel support must be ordered.

Suffix F3 =full panel, F4 =half panel



## Swing-Out Panels for Ultimate Series Enclosures





Note: HFWNSPxxxxC swing-out panels will not fit in older NEMA 4/12 enclosures (purchased prior to 3-23-05) that do not have a C suffix. For example: Swing-out panel HFWNSP1212C will not fit enclosures N41212126 or N412121206SS.

## Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days Color indicates shipping lead time in business days.

For N412 Ultimate Series Wall-Mount Enclosures except N412-1PTC, -3PTC, -SS1PTC, -SS3PTC, -SSA1PTC, and -SSA3PTC

- Maximum swing 107°
- Convenient access to sub enclosure is provided via 1/4 turn pull-tab
- On solid doors, the clearance from the swing panel face to the interior door face is 1.25in [31.8mm] on window doors (when the door is closed)
- The kit includes the swing panel, brackets and hardware necessary for a tub flange install. Swing out panels meet 1 with enclosure door open
- Painted steel subpanels are painted white polyester powder over phosphated surfaces
- Fabricated from 14-gauge steel
- Mounting hardware is furnished with each panel


Swing-Out Panels for Ultimate Series Enclosures							
Part Number	Price	Panel Size CxE	Overall Dimensions HxW	Enclosure Nominal Size			
HFWNSP1212C	\$128.00	9.75 x 9.75 [248 x 248]	10.50 x 10.62 [267 x 270]	12 x 12			
HFWNSP1612C	\$133.00	13.75 x 9.75 [349 x 248]	14.50 x 10.62 [368 x 270]	16 x 12			
HFWNSP1616C	\$140.00	13.75 x 13.75 [349 x 349]	14.50 x 14.62 [368 x 37]	16 x 16			
HFWNSP1620C	\$160.00	13.75 x 17.75 [349 x 451]	14.50 x 18.62 [368 x 473]	16 x 20			
HFWNSP2016C	\$147.00	17.75 x 13.75 [451 x 349	18.50 x 14.62 [470 x 371]	20 x 16			
HFWNSP2020C	\$156.00	17.75 x 17.75 [451 x 451]	18.50 x 18.62 [ 470 x 473]	20 x 20			
HFWNSP2024C	\$179.00	17.75 x 21.75 [451 x 552]	18.50 x 22.62 [470 x 575]	20 x 24			
HFWNSP2416C	\$167.00	21.75 x 13.75 [552 x 349]	22.50 x 14.62 [572 x 371]	24 x 16			
HFWNSP2420C	\$165.00	21.75 x 17.75 [552 x 451]	22.50 x 18.62 [572 x 473]	24 x 20			
HFWNSP2424C	\$176.00	21.75 x 21.75 [552 x 552]	22.50 x 22.62 [572 x 575]	24 x 24			
HFWNSP3020C	\$194.00	27.75 x 17.75 [705 x 451]	28.50 x 18.62 [724 x 473]	30 x 20			
HFWNSP3024C	\$192.00	27.75 x 21.75 [705 x 552]	28.50 x 22.62 [724 x 575]	30 x 24			
HFWNSP3030C	\$212.00	27.75 x 27.75 [705 x 705]	28.50 x 28.62 [724 x 727]	30 x 30			
HFWNSP3624C	\$208.00	33.75 x 21.75 [857 x 552]	34.50 x 22.62 [876 x 575]	36 x 24			
HFWNSP3630C	\$232.00	33.75 x 27.75 [857 x 705]	34.50 x 28.62 [876 x 727]	36 x 30			
HFWNSP3636C	\$256.00	33.75 x 33.75 [857 x 857]	34.50 x 34.62 [876 x 879]	36 x 36			


Notes: Dimensions in inches [millimeters].


Letters in table correspond to letters on dimensional drawings.

If used in a two-door enclosure, a center panel support must be ordered.

#### **Dimensions**







DOOR REMOVED

www.automationdirect.com

# Accessory Panels For WC14 Series Operator Consoles







#### **Description**

- Panels for WC14 Series operator consoles
- Full-height and half-height swing-out panels are available
- Half-height panels can be located in the upper or lower portion of enclosure
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Fabricated from 14-gauge steel
- Mounting hardware is furnished with each panel

## Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days Color indicates shipping lead time in business days.

Accessory Panels for WC14 Operator Consoles						
Part Number	Price	Panel Size HxWxD	Subpanel Type			
WC14P1	Retired	22.00 x 19.75 x 2.69 [559 x 502 x 68]	Swing			
WC14P2	Retired	22.00 x 17.00 x 0.813 [559 x 432 x 21]	Half			
WC14P3	Retired	42.25 x 17.00 x 0.81 [1073 x 432 x 21]	Full			
WC1436P1	Retired	22.00 x 31.69 x 2.75 [559 x 805 x 70]	Swing			
WC1436P2	Retired	22.00 x 29 x 0.81 [559 x 737 x 21]	Half			
WC1436P3	Retired	42.25 x 29.00 x 0.81 [1073 x 737 x 21]	Full			
WC1448P2	Retired	22.00 x 41.00 x 0.81 [559 x 1041 x 21]	Half			
WC1448P3	Retired	42.25 x 41.00 x 0.81 [1073 x 1041 x 21]	Full			
WC1460P2	Retired	22.00 x 53.00 x 0.81 [559 x 1346 x 21]	Half			
WC1460P3	Retired	42.25 x 53.00 x 0.81 [1073 x 1346 x 21]	Full			
Note: Letters in table correspond to letters on dimensional drawings.						





Full or Half Subpanel