


AUTOMATIONDIRECT.com

Model: PBT-AN-2H



Made in Germany

Inductive proximity sensor



voltage:	15...30 V DC	IP 67
out max:	100 mA NPN (normally open)	
range:	15 mm	

The device shall be supplied from an isolating transformer having a secondary Listed fuse rated either
a) max 5 amps for voltages 0~20 Vrms (0~28.3 Vp) or
b) 100/Vp for voltages of 20~30 Vrms (28.3~42.4 Vp).

