


ROHS

0000

PRODUCT WEIGHT:

REVISION LIST

REV	DESCRIPTION	DATE
A	INITIAL RELEASE DF DWG	AUG.03.2007
B	ADDED OPEN/SHORT TEST	DEC.08.2007
C	ADD LABEL&LENGTH	JAN.22.2008
D	CHG CUST. PART NO.	APR.01.2008



**ELECTRICAL PROPERTIES:**  
**1. 100% OPEN AND SHORT TEST**

**BILL OF MATERIAL**

⑥	LABEL+UL CLEAR HEAT SHRINK TUBE(Ø8.0mm,L:50mm)	1PCS	CC017
⑤	45P PVC, BLACK COLOR	52.0g	CC002
④	THUMB SCREW: UNC#4-40, AG4*24.0. BLACK COLOR MOLDING.	4 pcs	CC008
③	D-SUB 25P FEMALE SOLDERING TYPE. INSULATION: PBT, BLACK COLOR. CONTACT: BRASS, GOLD FLASH.	1 pc	CB001
②	D-SUB 25P MALE SOLDERING TYPE. INSULATION: PBT, BLACK COLOR. CONTACT: BRASS, GOLD FLASH.	1 pc	CB001
①	UL2464 28AWG 25C+DRAIN+AL FOIL CABLE OD:7.0mm, JACKET BLACK COLOR.	2093mm	CA003
NO	SPECIFICATION	Q'TY	VENDOR

DRAWN BY	□□	CHECK BY	APPROVED BY
----------	----	----------	-------------

MOLD DESIGN LIST:  
**J1 & J2.**  
 DW096<OUT>  
 DW095<IN>

TOLERANCE:	.XX= .XXX=
SCALE:	NONE
UNIT:	mm

CUST APPROVED

\*\*\* PINOUT DIAGRAM \*\*\*

J1	J2	J1	J2
1	1	14	14
2	2	15	15
3	3	16	16
4	4	17	17
5	5	18	18
6	6	19	19
7	7	20	20
8	8	21	21
9	9	22	22
10	10	23	23
11	11	24	24
12	12	25	25
13	13	SHELL	—DRAIN—SHELL

**MATCH** Data International Co.,Ltd

PART NO:	SC01A040025	DWG NO:	REV:
CUST NO:	ZL-DB25-CBL-2	CKC01708009	D
TITLE :	DB25M/DB25F	SHEET 1 OF 1	