

Improve your process AND save money

It's time to try AutomationDirect!

ProSense™ Digital Pressure Switches/Pressure Transmitters

Designed for air, non-corrosive gas and non-flammable gas applications, these small (1.2" by 1.2" by 1.7" deep) digital pressure switches/pressure transmitters have a 3-color LCD display and provide digital pressure control via two digital outputs and one analog output.

These compact pressure switches are easy to install and are ideal for use as pneumatic pressure switches or vacuum pressure switches.

Features:

- 1.2" x 1.2" x 1.7" deep
- 1/8" NPT process connection for: air, non-corrosive gases, non-flammable gases. (NOT for use in liquid applications)
- Repeatability +/- 3% of full scale
- Two digital outputs (NPN or PNP) which may be set individually, and a 4-20 mA analog output
- Two vacuum to pressure ranges (-14.5 to 14.5 psi and -14.5 to 145 psi)
- Three operation modes: Easy, Window and Hysteresis
- 3-color digital LCD display
- 6 pressure unit conversions
- Lockable keypad
- Unit parameters are easily copied to other pressure switch units
- Selectable response times to eliminate output chattering
- Fast zero reset
- Optional panel mount and bracket kits
- Agency approvals: cULus (E157382), CE, RoHS
- 2-year warranty



www.automationdirect.com/digital-pressure-switches

www.automationdirect.com

Go online or call to get complete information,
request your free catalog, or place an order.

1-800-633-0405

Also Available



Current Sensors



Solo™ Process
Controllers



Signal
Conditioners



Pressure
Switches



**Order Today,
Ships Today!**

* See our Web site for details and restrictions.
© Copyright 2012 AutomationDirect, Cumming, GA USA. All rights reserved.



AUTOMATIONDIRECT.com
the #1 value in automation