

Screwdriver Application Guide

Application Guide

AutomationDirect also sells high-quality insulated screwdrivers. Use these tables to find the right screwdriver to use for your DINnectors or PLC terminals.

See the Tools section in this catalog for more information on these screwdrivers.



Screwdriver Application Guide							
DINnectors & PLC Terminals	Insulated Slotted Screwdrivers				Insulated Phillips Screwdrivers		6mm Hex Head
	TW-SD-VSL-1, DN-SS1	TW-SD-VSL-2, DN-SS3	TW-SD-VSL-3, DN-SS4	TW-SD-VSL-4, DN-SS5	TW-SD-VPH-1, DN-SP1	TW-SD-VPH-2, DN-SP2	
DN-D10-A		X					
DN-D10DR-A		X					
DN-D10LED1-A		X					
DN-D10X-A		X					
DN-DIS10			X				
DN-F6			X				
DN-F6L24			X				
DN-F6L110			X				
DN-F6L220			X				
DN-F10		X					
DN-F10L24		X					
DN-F10L110		X					
DN-F10L220		X					
DN-G1/0				X			
DN-G4				X			
DN-G6			X				
DN-G8			X				
DN-G10		X					
DN-KBD12	X						
DN-M10-A		X					
DN-M10B-A		X					
DN-MG10		X					
DN-T1/0				X			
DN-T1/0B				X			
DN-T3/0							X
DN-T4				X			
DN-T4B				X			
DN-T6			X				
DN-T6B			X				
DN-T8			X				
DN-T8B			X				
DN-T10-A		X					
DN-T10B-A		X					
DN-T12-A	X						
DN-T12B-A	X						
DN-TL14	X						
DN-TL14S	X						
DN-TL14SLP	X						
DN-TL14SLN	X						
D2-8IOCON					X		
D2-16IOCON	X						
D3-16IOCON					X		
D4-16IOCON						X	

Note: See next page for additional selections.

- Company Information
- Systems Overview
- Programmable Controllers
- Field I/O
- Software
- C-more & other HMI
- Drives
- Soft Starters
- Motors & Gearbox
- Steppers/ Servos
- Motor Controls
- Proximity Sensors
- Photo Sensors
- Limit Switches
- Encoders
- Current Sensors
- Pressure Sensors
- Temperature Sensors
- Pushbuttons/ Lights
- Process
- Relays/ Timers
- Comm.
- Terminal Blocks & Wiring
- Power
- Circuit Protection
- Enclosures
- Tools
- Pneumatics
- Appendix
- Product Index
- Part # Index

Screwdrivers Application Guide (continued)



Screwdriver Application Guide Cont.							
DINnectors & PLC Terminals	Insulated Slotted Screwdrivers				Insulated Phillips Screwdrivers		Hex Head
	TW-SD-VSL-1, DN-SS1	TW-SD-VSL-2, DN-SS3	TW-SD-VSL-3, DN-SS4	TW-SD-VSL-4, DN-SS5	TW-SD-VPH-1, DN-SP1	TW-SD-VPH-2, DN-SP2	
CO-3TB	X						
CO-4TB	X						
CO-8TB	X						
CO-16TB	X						
DN-THERM1	X						
DN-THERM2	X						
DN-FE2		X					
DN-FE2L12		X					
DN-FE2L24		X					
DN-FE4		X					
DN-FE4L12		X					
DN-FE4L24		X					
DN-DIS2		X					
DN-DIS2L12		X					
DN-DIS2L24		X					
DN-DIS4		X					
DN-DIS4L12		X					
DN-DIS4L24		X					
DN-EMXM1		X					
DN-EMXDV		X					
DN-QEMXM1			X				
DN-QEMXDV			X				
DN-Q12		X					
DN-Q12B		X					
DN-Q10			X				
DN-Q10B			X				
DN-Q8			X				
DN-Q8B			X				
F0-IOCON	X						
F1-IOCON					X		
P3-RTB					X		