

# NEMA 12 JIC Handy Screw Cover Wall Mount



## Applications

Designed for use where protection from dirt, dust, oil and water is needed. Particularly suitable for use with liquid-tight flexible conduit.

- External mounting plates, top and bottom of enclosure
- Screw holes for cover match conventional outlet mounting criteria



## Construction

- Bodies and doors fabricated from 14 gauge steel
- Drawn lid that features no welded seams or sharp corners
- No holes or conduit knockouts
- Lids are sealed with closed cell oil resistant neoprene gasket
- Cover screws thread into neoprene gasket for maximum seal

## Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces

## Listings

- UL 50, Types 12 & 13
- UL File E64791
- CSA Certified, Type 12
- CSA File LL66078
- NEMA/EEMAC Types 12 & 13
- JIC EL-1-71



Enclosure Shipping Schedule		
Same day	1 - 7 days	1 - 10 days
Color indicates shipping lead time in business days.		

Part Number	Price	Body/Door Steel Gauge	Size HxWxD
JIC040202	<--->	14/14	4x2x2 (102x51x51)
JIC0403025	<--->	14/14	4.25x2.88x2.63 (108x73x67)
JIC040403	<--->	14/14	4x4x3 (102x102x76)
Note: Dimensions in inches (millimeters)			

## Dimensions

