

# NEMA 4 Two-Door Floor Mount



## Applications

Designed to house electrical and electronic controls, components and instruments in wet, non-corrosive environments. Typical applications for these enclosures include dairies, breweries and other food processing activities that may require hose down. Enclosures are also suitable for outdoor applications.

- Standard 12" high floor kits are welded to bottom of enclosure
- Easily removable center post permits easy panel installations
- Print pocket is provided
- Heavy duty removable lifting eyes
- Grounding provisions provided
- Doors are sealed with closed cell neoprene gasket



## Construction

- Bodies, doors and floor stand feet are fabricated from 10 gauge steel
- Continuously welded seams ground smooth, less knockouts or holes
- Closed cell neoprene gasket
- X-type body stiffeners are added for extra strength
- Collar studs for mounting optional panels
- Rolled lip around three sides of door and along top of enclosures opening excludes liquids and contaminants from entering
- Quick and easy-to-operate stainless steel door clamps around three sides
- Heavy gauge continuous hinges
- Doors are removable by pulling stainless steel continuous hinge pin
- Hasp and staple are provided for padlocking

## Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces
- Optional subpanels are white polyester powder over phosphatized surfaces

## Listings

- UL 508, Types 3, 4 & 12
- UL File E64791
- CSA Certified, Types 3,4 & 12
- CSA File LL66078
- NEMA/EEMAC Types 3,4 & 12

Enclosure Shipping Schedule		
Same day	1 - 7 days	1 - 10 days
Color indicates shipping lead time in business days.		

Part Number	Price	Body/Door	Enclosure Size HxWxD	Subpanel Part Number	Price	Subpanel Size AxB
<b>N4D624810</b>	<--->	10/10	62.12x48.12x10.12 (1578x1222x257)	<b>NPDD6048</b>	<--->	56x44 (1422x1118)
<b>N4D626012</b>	<--->	10/10	62.12x60.12x12.12 (1578x1527x308)	<b>NPDD6060</b>	<--->	56x56 (1422X1422)
<b>N4D746012</b>	<--->	10/10	74.12x60.12x12.12 (1883x1527x308)	<b>NPDD7260</b>	<--->	68x56 (1727X1422)
<b>N4D747212</b>	<--->	10/10	74.12x72.12x12.12 (1883x1832x308)	<b>NPDD7272</b>	<--->	68x68 (1727X1727)
<b>N4D747224</b>	<--->	10/10	74.12x72.12x24.12 (1883x1832x613)	<b>NPDD7272</b>	<--->	68x68 (1727X1727)

Note: Subpanels must be ordered separately. Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.

# NEMA 4 Two-Door Floor Mount

Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/ Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/ Lights

Process

Relays/ Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics

Appendix

Product Index

Part # Index

## Dimensions

