

# NEMA 4X Stainless Steel Two-Door Floor Mount



## Applications

This two-door enclosure provides industry-leading protection for systems incorporating large components or complex configurations in highly corrosive environments. It is typically used in the following areas: food processing plants, pharmaceutical manufacturing facilities, petrochemical plants, pulp and paper processing, and waste water treatment facilities.



## Construction

- Bodies and doors fabricated from 10 gauge 304 stainless steel
- Continuously welded seams ground smooth, less knockouts or holes
- X-type body stiffeners are added for extra strength
- Rolled lip around three sides of door and along top of enclosure opening excludes liquids and contaminants from entering
- Quick and easy to operate stainless steel door clamps around three sides of doors are provided
- Heavy gauge stainless steel continuous hinges are provided

- Doors are removable by pulling stainless steel continuous hinge pin
- Hasp and staple are provided for padlocking
- Print pocket is provided
- Standard 12" high floor kits are welded to bottom of enclosure
- Heavy duty removable lifting eyes
- Doors are sealed with closed cell oil resistant neoprene gasket
- Grounding provisions provided
- Easily removable center post permits easy panel installations
- Collar studs for mounting optional subpanels

## Finish

- Enclosures have a smooth grained finish on all exterior surfaces
- Optional subpanels are painted white polyester powder over phosphatized surfaces

## Listings

- UL 508, Types 4, 4X and 12 (UL file E64791)
- CSA Certified, Types 4 and 12 (CSA file LL66078)
- Meets NEMA/EEMAC Types 4, 4X and 12 requirements

### Enclosure Shipping Schedule

Same day	1 - 7 days	1 -10 days
----------	------------	------------

Color indicates shipping lead time in business days.

Part Number	Price	Body/Door	Enclosure Size HxWxD (not incl. 12" legs)	Subpanel P/N	Price	Subpanel Size AxB
<b>SSN4D624812</b>	<-->	10/10	62.12x48.12x12.12 (1578x1222x308)	<b>NPDD6048</b>	<-->	56x44 (1422x1118)
<b>SSN4D626012</b>	<-->	10/10	62.12x60.12x12.12 (1578x1527x308)	<b>NPDD6060</b>	<-->	56x56 (1422x1422)
<b>SSN4D747212</b>	<-->	10/10	74.12x72.12x12.12 (1883x1832x308)	<b>NPDD7272</b>	<-->	68x68 (1727x1727)
<b>SSN4D747224</b>	<-->	10/10	74.12x72.12x24.12 (1883x1832x613)	<b>NPDD7272</b>	<-->	68x68 (1727x1727)

Note: Subpanels must be ordered separately. Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.

# NEMA 4X Stainless Steel Two-Door Floor Mount

## Dimensions

