



Tools – Jobber Length Drill Bits



214816 shown

Jobber Length Drill Bits									
	Part # High Speed Steel	Pcs/Pkg	Price	Part # Titanium Coated	Drill Size (Gauge)	Ø Size A (in. dec.)	Flute Length B (in.)	Overall Length C (in.)	Use With
Number	2149003	10	<--->	Titanium coating not available in these sizes	3	0.2130	2 1/2	3 3/4	265014UNF
	2149007	10	<--->		7	0.2010	2 7/16	3 5/8	265014UNC
	2149014	10	<--->		14	0.1820	2 3/16	3 3/8	265120UNF
	2149016	10	<--->		16	0.1770	2 3/16	3 3/8	265120UNC
	2149021	10	<--->		21	0.1590	2 1/8	3 1/4	265100UNF
	2149025	10	<--->		25	0.1495	1 7/8	3	265100UNC
	2149029	10	<--->		29	0.1360	1 3/4	2 7/8	265080UNC, 265080UNF
	2149033	10	<--->		33	0.1130	1 1/2	2 5/8	265060UNF
	2149036	10	<--->		36	0.1065	1 7/16	2 1/2	265060UNC
	2149037	10	<--->		37	0.1040	1 7/16	2 1/2	265050UNF
	2149038	10	<--->		38	0.1015	1 7/16	2 1/2	265050UNC
	2149042	10	<--->		42	0.0935	1 1/4	2 1/4	265040UNF
	2149043	10	<--->		43	0.0890	1 1/4	2 1/4	265040UNC
	Letter	214900F	10		<--->	F	0.2570	2 7/8	4 1/8
214900I		10	<--->	I	0.2720	2 7/8	4 1/8	265516UNF	
214900Q		10	<--->	Q	0.3320	3 7/16	4 3/4	265038UNF	



Tools – Drill Bit Kits

Step and jobber length fractional size drill bits in convenient kits of 3 (step), 21 or 29 (jobber length) pieces.



Jobber length drill set 214850 shown

Drill Bit Kits			
Part #	Pcs/Pkg	Price	Description
101026US	3	<--->	Three-piece Step Drill Bit Kit High Speed Steel, bright finish, spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
214850	21	<--->	Jobber Length Drill Set Fractional sizes 1/16" to 3/8" in increments of 1/64" High-speed steel, 118 degrees point
214851	29	<--->	Jobber Length Drill Set Fractional sizes 1/16" to 1/2" in increments of 1/64" High-speed steel, 118 degrees point.
250850T	21	<--->	Jobber Length Drill Set Fractional sizes 1/16" to 3/8" in increments of 1/64" TiN-coated high-speed steel, 118 degrees point
250851T	29	<--->	Jobber Length Drill Set Fractional sizes 1/16" to 1/2" in increments of 1/64" TiN-coated high-speed steel, 118 degrees point