

NEW PRODUCT BULLETIN



from **AutomationDirect**

Non-Fusible Disconnects SIRCO Series



Overview

Ferraz Shawmut SIRCO disconnect switches are heavy duty, manually operated, non-fused disconnect switches, designed using the latest technology available. SIRCO switches meet UL98 standards with a product that "makes and breaks" power circuits on load. These switches have been

tested and approved for use in the most demanding applications, including "service entrance". Visible blade contacts are standard in SIRCO switches up to 400A. Choose from a wide array of handles meeting OSHA padlocking requirements, NEMA configurations, def eater options and NFPA 79 requirements.

Features

- Service entrance rated
- Compact footprints
- Front operated switches
- Visible blade contacts up to 400A
- Line side shrouding supplied with switch
- Defeatable pistol handles automatically re-latch when panel door is closed - no tool necessary to reset latch
- External or direct operation handles

Applications

- Service entrance or main panel disconnects up to 600 VAC, 800 A
- "Make and Break" power circuit applications on load
- NFPA 79 Solutions

Rating

- 600 VAC, 250 VDC
- 30, 60, 100, 200, 400, 600, and 800 amperes
- Up to 200 kA short circuit rating when Class CC, J, or L fuses are used externally

Approvals

- All SIRCO switches meet UL98 requirements
- UL Listed Guide WHTY, File E191605
- CSA C22.2 # 4 Class 4652 04, File 703166
- IEC 947-3 as a load break disconnect
- CE mark


SIRCO Range: Non-Fusible Disconnect Switches

Ampere Rating	30	60	100	200	400	600	800
Catalog Number: 3 Pole	SCV30	SCV60	SCV100	SCV200	SCV400	SC600	SC800
Price	\$57.00	\$93.00	\$110.00	\$180.00	\$449.00	\$740.00	\$1,415.00

For complete part listing, specifications and pricing, visit: www.automationdirect.com/disconnects

Complete line of Accessories

- 1 - Terminal Shroud
- 2 - Terminal Lugs
- 3 - Auxiliary Contact Block
- 4 - Auxiliary Contact Holder
- 5 - NFPA 79 Compliant Handle
- 6 - Standard Shaft
- 7 - Direct Mount Handle
- 8 - External Door Handle



Fusible Disconnects FUSERBLOC Series



Overview

Ferraz Shawmut FUSERBLOC fusible disconnect switches employ double break contacts per pole to isolate the fuse when the switch is in the OFF position. They are durable, manually operated, and supplied with fuse covers and line side shrouding as a standard safety feature. When used with AutomationDirect's Class CC or J fuses, these switches are tops

in short circuit protection. Designed using the latest technology, they comply with UL98 requirements. FUSERBLOC switches are tested and approved for heavy duty applications, such as "service entrance" or main panel disconnects. Choose from a wide selection of handles meeting OSHA padlocking requirements, NEMA configurations, defeater options and NFPA 79 requirements.

Features

- Double break contacts per pole up to 200 A
- Touch-safe fuse covers and line shrouding standard
- Service entrance rated
- Compact footprints
- Front operated switches
- Defeatable pistol handles automatically re-latch when panel door is closed - no tool necessary to reset latch
- External or direct operation handles.

Applications

- Service entrance or main panel disconnects
- "Make and Break" power circuit applications on load
- Fusible isolation switches
- NFPA 79 Solutions

Rating

- 600 VAC, 250 VDC
- 30, 60, 100 and 200 Amperes
- Up to 200 kA short circuit rating with Class CC or J fuses


Approvals

- All FUSERBLOC switches are UL98 rated
- UL Listed Guide WHTY, File E191605
- CSA C22.2 # 4 Class #652 04, File 703166
- IEC 947-3
CE mark

SIRCO Range: Non-Fusible Disconnect Switches						
Ampere Rating	30 compact CC fuses	30 compact J fuses	30	60	100	200
Catalog Number:	FBCC30CDT	FBJ30CDT	FBJ30	FBJ60	FBJ100	FBJ200
Price	\$85.00	\$85.00	\$115.00	\$135.00	\$165.00	\$449.00

Complete line of Accessories

- 1 - Terminal Shroud
- 2 - Terminal Lugs
- 3 - Auxiliary Contact Block
- 4 - Auxiliary Contact Holder
- 5 - Fuses
- 6 - NFPA 79 Compliant Handle
- 7 - Standard Shaft
- 8 - Direct Mount Handle
- 9 - External Door Handle



© Copyright 2007 AutomationDirect.com
Encompassing **PLC Direct**
By Koyo



the #1 value in automation

© Copyright 2006 AutomationDirect, Cumming, GA USA. All rights reserved.

AUTOMATIONDIRECT.com

www.automationdirect.com | 1-800-633-0405