


## Legend plates

Aluminum legend plates feature a plastisol backing to help prevent rotation of the operator.



Approximate dimensions in inches (mm).

### E22VA8



Accessories			
Color	Part Number	Legend	Price
Black	<b>E22NS11</b>	"CLOSE"	<-->
Black	<b>E22NS12</b>	"DOWN"	<-->
Red	<b>E22NS13</b>	"EMERG. STOP"	<-->
Black	<b>E22NS15</b>	"FORWARD"	<-->
Black	<b>E22NS19</b>	"JOG"	<-->
Black	<b>E22NS25</b>	"ON"	<-->
Black	<b>E22NS26</b>	"OPEN"	<-->
Black	<b>E22NS30</b>	"REVERSE"	<-->
Black	<b>E22NS31</b>	"RUN"	<-->
Black	<b>E22NS33</b>	"START"	<-->
Red	<b>E22NS34</b>	"STOP"	<-->
Black	<b>E22NS35</b>	"UP"	<-->
Black	<b>E22NS36</b>	Blank plate	<-->
Red	<b>E22NS37</b>	Blank plate	<-->
Black	<b>E22NS38</b>	"FOR-REV"	<-->
Black	<b>E22NS39</b>	"HAND-AUTO"	<-->
Black	<b>E22NS41</b>	"JOG-RUN"	<-->
Black	<b>E22NS42</b>	"OFF-ON"	<-->
Black	<b>E22NS43</b>	"OPEN-CLOSE"	<-->
Black	<b>E22NS48</b>	"UP-DOWN"	<-->
Black	<b>E22NS50</b>	"FOR-OFF-REV"	<-->
Black	<b>E22NS51</b>	"HAND-OFF-AUTO"	<-->
Black	<b>E22NS80</b>	"POWER ON"	<-->
Black	<b>E22NS81</b>	"MOTOR RUN"	<-->
Black	<b>E22NS82</b>	"MOTOR STOP"	<-->
Black	<b>E22NL36</b>	Jumbo alum. blank plate (1.57 in wide x 1.85 in tall)	<-->
Red	<b>E22NL37</b>	Jumbo alum. blank plate (1.57 in wide x 1.85 in tall)	<-->
Red /black	<b>E22NSP77</b>	Plastic blank plate; red on one side, black on other side; either side can have letters engraved down into white plastic	<-->
Yellow	<b>E22VA8</b>	"EMERGENCY STOP" oversize yellow legend plate, 2.76" (70mm), printed	<-->

**NOTE:** Legend plates also work with the 22 mm metal switches. The removal of the locator tab on the legend plate is required for use with the 22 mm metal switches. This is easily accomplished with a round file or small grinder.