

# Enclosure Subpanels




Enclosures for Electrical/Electronic Equipment

## Subpanels for small NEMA 1, NEMA 3R and NEMA 12 enclosures

- 14 gauge
- Subpanels are painted white polyester powder
- Panels listed fit the following enclosures:

NEMA 1 small (N1C)  
NEMA 3R small (RHC)  
NEMA 12 WA\_GIE




Part Number	Price	Enclosure Size HxW	Subpanel Size AxB
<b>N1P0606</b>	<--->	6x6 (152x152)	4.25x4.25 (108x108)
<b>N1P0608</b>	<--->	6x8 (152x203)	6.25x4.25 (159x108)
<b>N1P0808</b>	<--->	8x8 (203x203)	6.25x6.25 (159x159)
<b>N1P0810</b>	<--->	8x10 (203x254)	8.25x6.25 (210x159)
<b>N1P1010</b>	<--->	10x10 (254x254)	8.25x8.25 (210x210)
<b>N1P1012</b>	<--->	10x12 (254x305)	10.25x8.25 (260x210)
<b>N1P1212</b>	<--->	12x12 (305x305)	10.25x10.25 (260x260)
<b>N1P1214</b>	<--->	12x14 (305x356)	12.25x10.25 (311x260)
<b>N1P1216</b>	<--->	12x16 (305x406)	14.25x10.25 (362x260)
<b>N1P1220</b>	<--->	12x20(305x508)	18.25x10.25 (464x260)

Note: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawing.

Enclosure Shipping Schedule		
Same day	1 - 7 days	1 -10 days
Color indicates shipping lead time in business days		

## Subpanels for large NEMA 1 enclosures

- 12 gauge
- Subpanels are painted white polyester powder
- Panels listed fit NEMA 1 large (N1C) enclosures



Part Number	Price	Enclosure Size HxW	Subpanel Size AxB
<b>N1P1216L</b>	<--->	16x12 (406x305)	13x10.50 (330x267)
<b>N1P1616</b>	<--->	16x16 (406x406)	13x14.50 (330x368)
<b>N1P1620</b>	<--->	20x16 (508x406)	17x14.50 (432x368)
<b>N1P1624</b>	<--->	24x16 (914x406)	21x14.50 (533x368)
<b>N1P2016</b>	<--->	16x20 (406x508)	13x18.50 (330x470)
<b>N1P2020</b>	<--->	20x20 (508x508)	17x18.50 (432x470)
<b>N1P2024</b>	<--->	24x20 (610x508)	21x18.50 (533x470)
<b>N1P2030</b>	<--->	30x20 (762x508)	26x18.50 (660x470)
<b>N1P2420</b>	<--->	20x24 (508x610)	17.00x22.50 (432x572)
<b>N1P2424</b>	<--->	24x24 (610x610)	21x22.50 (533x572)
<b>N1P2430</b>	<--->	30x24 (762x610)	26x22.50 (660x572)
<b>N1P2436</b>	<--->	36x24 (914x610)	32x22.50 (813x572)
<b>N1P3030</b>	<--->	30x30 (762x762)	26x28.5 (660x724)
<b>N1P3036</b>	<--->	36x30 (914x762)	32x28.50 (813x724)

Note: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawing.