

Enclosures Subpanels



Subpanels for NEMA 1, 12, 4 and 4X wall mount enclosures and WC9 NEMA 12 operator consoles

- 12 gauge steel
- Subpanels with any side over 17" have 3/4" flange on all sides
- Subpanels are painted white polyester powder

Panels listed fit the following enclosures:


- NEMA 1 large (NIC)
- NEMA 12 large (JIC)
- NEMA 12 single door wall mount
- NEMA 12 two door wall mount
- NEMA 12 single door flush wall mount
- NEMA 4 (N) and 4X (SSN) single door wall mount
- NEMA 12 operator consoles (WC9)

NOTE: Use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures only. Do NOT use NPxxxx subpanels in NEMA 4/12 enclosures with a C suffix.



Enclosure Shipping Schedule		
Same day	1 - 7 days	1 - 10 days
Color indicates shipping lead time in business days		

Part Number	Price	Enclosure Size HxW	Subpanel Size AxB
NP1212	<--->	12x12 (305x305)	9x9 (229x229)
NP1224	<--->	12x24 (305x610)	9x21 (229x533)
NP1612	<--->	16x12 (406x305)	13x9 (330x229)
NP1616	<--->	16x16 (406x406)	13x13 (330x330)
NP2012	<--->	20x12 (508x305)	17x9 (432x229)
NP2016	<--->	20x16 (508x406)	17x13 (432x330)
NP2020	<--->	20x20 (508x508)	17x17 (432x432)
NP2412	Use NP1224		21x9 (533x229)
NP2416	<--->	24x16 (610x406)	21x13 (533x330)
NP2420	<--->	24x20 (610x508)	21x17 (533x432)
NP2424	<--->	24x24 (610x610)	21x21 (533x533)
NP3016	<--->	30x16 (762x406)	27x13 (686x330)
NP3020	<--->	30x20 (762x508)	27x17 (686x432)
NP3024	<--->	30x24 (762x610)	27x21 (686x533)
NP3030	<--->	30x30 (762x762)	27x27 (686x686)
NP3624	<--->	36x24 (914x610)	33x21 (838x533)
NP3630	<--->	36x30 (914x762)	33x27 (838x686)
NP3636	<--->	36x36 (914x914)	33x33 (838x838)
NP4024	<--->	40x24 (1016x610)	37x21 (940x533)
NP4224	<--->	42x24 (1067x610)	39x21 (991x533)
NP4230	<--->	42x30 (1067x762)	39x27 (991x686)
NP4236	<--->	42x36 (1067x914)	39x33 (991x838)
NP4824	<--->	48x24 (1219x610)	45x21 (1143x533)
NP4830	<--->	48x30 (1219x762)	45x27 (1143x686)
NP4836	<--->	48x36 (1219x914)	45x33 (1143x838)
NP6030	<--->	60x30 (1527x762)	57x27 (1448x686)
NP6036	<--->	60x36 (1527x914)	57x33 (1448x838)
NP7230	<--->	72x30 (1832x762)	69x27 (1753x686)
NP7236	<--->	72x36 (1832x914)	69x33 (1753x838)



Note: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawing.