

Wera Screwdrivers

Miniature Screwdrivers

The hand support on the easy-turning cap and the fast-turning zone below the cap accelerate the screw driving process. This makes time-consuming grip adjustments, which are required with conventional precision screwdrivers, unnecessary.



Miniature Screwdrivers			
Part Number	Description	Pcs/Pkg	Price Each
TW-SD-SET-3	Six piece miniature screwdriver set, includes four flat (slotted) and two Phillips (#00 and #0) screwdrivers with rotating caps and wall mount rack.	1 set	<--->
TW-SD-MSL-1	Miniature flat (slotted) screwdriver, 0.4mm (0.016 inch) thick x 2mm (0.08 inch) wide x 60mm (2.36 inch) long blade.	1	<--->
TW-SD-MSL-2	Miniature flat (slotted) screwdriver, 0.4mm (0.016 inch) thick x 2.5mm (0.10 inch) wide x 80mm (3.15 inch) long blade.	1	<--->
TW-SD-MSL-3	Miniature flat (slotted) screwdriver, 0.5mm (0.02 inch) thick x 3mm (0.12 inch) wide x 80mm (3.15 inch) long blade.	1	<--->
TW-SD-MPH-1	Miniature Phillips screwdriver, #0 x 60mm (2.36 inch) long blade.	1	<--->



TW-SD-SET-3



TW-SD-MSL-1



TW-SD-MPH-1

Hex Keys


Hex-Plus L-keys for hexagon socket screws provide more contact surface inside the screw, which prevents rounding.

L-keys can transfer high torque but they must not twist to any great extent, or shear off, to minimize the risk of injuries. Wera's extensive experience with narrow tolerance manufacturing techniques, careful material selection and refined hardening technologies delivers maximum safety at work.

Hex Keys			
Part Number	Description	Pcs/Pkg	Price Each
TW-HK-SET-MM	Hex key set, nine-piece includes metric sizes from 1.5mm to 10mm with holder.	1 set	<--->
TW-HK-SET-STD	Hex key set, 13-piece includes inch sizes from 0.05 inch to 3/8 inch with holder.	1 set	<--->



TW-HK-SET-MM



TW-HK-SET-STD

Wera Screwdrivers

Bit Drivers and Screwdriver Bits

Wera bits have been designed for demanding applications in trade and industry. They are able to transfer high torque loads, are safe to use and extremely durable.



TW-DB-SET-SD1



TW-DB-SET-28R



TW-DB-SET-6A



TW-DB-ADT-MAG



TW-DB-PH-1



TW-DB-SL-1

Bit Drivers and Screwdriver Bits			
Part Number	Description	Pcs/Pkg	Price Each
TW-DB-SET-SD1	Bayonetting screwdriver with three flat (slotted) (4,5 to 6,5mm) and three Phillips (#1 to #3) bits stored in handle and carrying pouch.	1	<--->
TW-DB-SET-28R	Driver bit set, 28-piece in carrying case with mini bit ratchet, includes two adapters, one flat (slotted)(5,5mm), six Phillips (#1 to #3), five Hex-Plus (3/32 to 1/4 inch), six Torx (TX10 to TX40), five tamper-proof Torx (TX10 to TX30), and five Robertson (square)(#1 to #3) driver bits.	1	<--->
TW-DB-SET-6A	Driver bit set, six-piece in carrying case with 1/4 inch hex drive adapter, includes two flat (slotted) and four Phillips (#1 and #2) driver bits with diamond-coated tips.	1	<--->
TW-DB-ADT-MAG	Driver bit adapter, 1/4 inch hex x 75mm (3 inch) long with ring magnet.	1	<--->
TW-DB-PH-1	Driver bit, Phillips #1 x 70mm (2.75 inch) long, 1/4 inch hex drive, 10 bits per pack.	10	<--->
TW-DB-PH-2	Driver bit, Phillips #2 x 70mm (2.75 inch) long, 1/4 inch hex drive, 10 bits per pack.	10	<--->
TW-DB-SL-1	Driver bit, flat (slotted), 0,5mm (0,02 inch) thick x 3mm (0,12 inch) wide x 50mm (1,97 inch) long, 1/4 inch hex drive, 10 bits per pack.	10	<--->

Torque Tools

Wera torque tools permit torque-controlled tightening to prevent damage to screws or work pieces and to guarantee the safety of screw connection. This makes labor-intensive drilling, re-tapping and production downtimes a thing of the past.

All Wera torque tools are supplied with a calibration certificate.

Torque Tools			
Part Number	Description	Pcs/Pkg	Price Each
TW-TD-2-11	Torque driver, 2,5 to 11,5 in-lb adjustable setpoint, 1/4 inch hex driver. Driver bits not included.	1	<--->
TW-TD-11-29	Torque driver, 11 to 29 in-lb adjustable setpoint, 1/4 inch hex driver. Driver bits not included.	1	<--->



TW-TD-2-11



TW-TD-11-29