


Wiring Duct Cover



Duct Cover

Our standard wire duct products are supplied complete with covers. These replacement covers are manufactured from the same rigid self-extinguishing PVC material.

UL file E123572



Duct Cover Specifications					
Part Number	Price	Description	Color	Standard Carton	
				Pcs/Pkg	Actual Total Length ft (m)
COV-05G	<--->	Cover for 0.5" wide duct	Gray	25	164 (50)
COV-05G-1	<--->	Cover for 0.5" wide duct	Gray	1	6.56 (2)
COV-10G	<--->	Cover for 1.0" wide duct	Gray	25	164 (50)
COV-10G-1	<--->	Cover for 1.0" wide duct	Gray	1	6.56 (2)
COV-10W	<--->	Cover for 1.0" wide duct	White	25	164 (50)
COV-10W-1	<--->	Cover for 1.0" wide duct	White	1	6.56 (2)
COV-15G	<--->	Cover for 1.5" wide duct	Gray	25	164 (50)
COV-15G-1	<--->	Cover for 1.5" wide duct	Gray	1	6.56 (2)
COV-15W	<--->	Cover for 1.5" wide duct	White	25	164 (50)
COV-15W-1	<--->	Cover for 1.5" wide duct	White	1	6.56 (2)
COV-22G	<--->	Cover for 2.25" wide duct	Gray	25	164 (50)
COV-22G-1	<--->	Cover for 2.25" wide duct	Gray	1	6.56 (2)
COV-22W	<--->	Cover for 2.25" wide duct	White	25	164 (50)
COV-22W-1	<--->	Cover for 2.25" wide duct	White	1	6.56 (2)
COV-30G	<--->	Cover for 3.0" wide duct	Gray	25	164 (50)
COV-30G-1	<--->	Cover for 3.0" wide duct	Gray	1	6.56 (2)
COV-30W	<--->	Cover for 3.0" wide duct	White	25	164 (50)
COV-30W-1	<--->	Cover for 3.0" wide duct	White	1	6.56 (2)
COV-40G	<--->	Cover for 4.0" wide duct	Gray	20	131.2 (40)
COV-40G-1	<--->	Cover for 4.0" wide duct	Gray	1	6.56 (2)
COV-40W	<--->	Cover for 4.0" wide duct	White	20	131.2 (40)
COV-40W-1	<--->	Cover for 4.0" wide duct	White	1	6.56 (2)
COV-60G	<--->	Cover for 6.0" wide duct	Gray	20	131.2 (40)
COV-60G-1	<--->	Cover for 6.0" wide duct	Gray	1	6.56 (2)
COV-60W	<--->	Cover for 6.0" wide duct	White	20	131.2 (40)
COV-60W-1	<--->	Cover for 6.0" wide duct	White	1	6.56 (2)

Note: Standard length of covers is 6.56 feet (2m) to fit T1, T1E and TSH duct.

