


Louvers and Filters for Metal Enclosures




Louver Vent Kits



Louver vents provide ventilation or cooling in metal enclosures where excessive moisture or excessive internal heat is a problem. These kits are fabricated from 14-gauge steel and include all hardware for mounting. Kits are easily field installed by making a cutout of the proper size and attaching the louver vent in place. Finish is ANSI 61 gray polyester powder finish over phosphatized surfaces or 316 stainless steel. Filter kit must be ordered separately.

Filter Kits for Louver Vent Kits



Aluminum filters are good for stopping dust and dirt from penetrating the enclosures. These filters are designed to mount behind WAVK series louver vent kits. Mounting holes on filter brackets align with mounting holes on louver kits. Kit consists of aluminum filter, brackets and all necessary hardware for installation. Louver kit must be ordered separately.

Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Louver Vent and Filter Kits												
Louver Kit 14-gauge Steel	Price	Louver Kit 316 SS	Price	Filter Kit	Price	No. of Louvers	No. of Louver Rows	Louver Length in [mm]	A in [mm]	B in [mm]	C in [mm]	D in [mm]
WAVK0808	Retired	WAVK0203SSA	Retired	—	—	3	1	2.00 [51]	3.25 [83]	3.25 [83]	2.00 [51]	2.00 [51]
WAVK0303	\$29.00	WAVK0303SSA	\$121.00	WAFLT33	\$35.50	3	1	3.00 [76]	3.87 [98]	4.50 [114]	2.62 [67]	3.25 [83]
WAVK0304	\$30.50	WAVK0304SSA	\$126.00	WAFLT34	\$35.50	4	1	3.00 [76]	4.75 [121]	4.50 [114]	3.50 [89]	3.25 [83]
WAVK0404	\$33.00	WAVK0404SSA	\$138.00	WAFLT44	\$36.50	4	1	4.00 [102]	5.62 [143]	5.50 [140]	4.37 [111]	4.25 [108]
WAVK0604	Retired	WAVK0604SSA	Retired	WAFLT64	Retired	8	1	3.00 [76]	5.62 [143]	7.50 [191]	4.37 [111]	6.25 [159]
WAVK0606	\$39.50	WAVK0606SSA	\$165.00	WAFLT66	\$40.00	12	1	3.00 [76]	7.87 [200]	7.50 [191]	6.62 [168]	6.25 [159]
WAVK0806	Retired	WAVK0806SSA	Retired	WAFLT86	Retired	12	2	4.00 [102]	8.18 [208]	9.50 [241]	6.93 [176]	8.25 [210]
WAVK0808	Retired	WAVK0808SSA	Retired	WAFLT88	Retired	16	2	4.00 [102]	10.56 [268]	9.50 [241]	9.31 [236]	8.25 [210]
WAVK0812	Retired	WAVK0812SSA	Retired	WAFLT812	Retired	24	2	4.00 [102]	15.31 [389]	9.50 [241]	14.06 [357]	8.25 [210]

Note: Dimensions in inches [millimeters].

Dimensions

