

Wera Screwdriver Bit Sets



Screwdriver Bit Sets

Wera bits have been designed for demanding applications in trade and industry. They are able to transfer high torque loads, are safe to use and extremely durable.

Driver Bit Adapter		
Part Number	Description	Price
TW-DB-ADT-MAG	Wera Rapidaptor driver bit adapter, 1/4 inch drive, overall length 2-1/4 inch, ring magnet. Manufacturer part number: 052490.	\$21.50

Note: Bit-holders are warranted against manufacturer defect only.



TW-DB-ADT-MAG



Telescopic Blade

When the unique telescopic blade is lowered into the handle, fast, easy screw-driving action is possible, even in the tightest spots! By pushing the clamping sleeve, the telescopic blade can be extended out of the handle and the compact tool becomes a full-sized screwdriver. If the clamping sleeve is pushed again the telescopic blade can be taken out of the handle, and be used as a machine bit adapter.



Screwdriver Bit Set		
Part Number	Description	Price
TW-DB-SET-SD1	Wera Kraffform Kompakt driver bit set with screwdriver, 1/4 inch drive. 8 pieces. Durable cloth pouch included. Manufacturer part number 051024.	\$45.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



TW-DB-SET-SD1

TW-DB-SET-SD1 Contents		
	Kraffform Kompakt bit-holding bayonet screwdriver	
	1/4 Rapidaptor bit holder	1/4 x 50
	Slotted bit, 25mm long	0.6 x 4.5, 1.0 x 5.5, 1.2 x 6.5
	Phillips bit, 25mm long	PH1, PH2, PH3

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

Wera Driver Bit Sets



Bits, Bitholding Screwdriver and L-Keys in One Tool Set

This 52-piece set packs maximum screw-driving utility into a compact, lightweight set protected by an extremely robust folding textile box:

- BiTorsion bits for long service life
- Impaktor bits for extreme conditions
- Chrome-plated Hex-Plus L-keys with ball-end hex on long arm
- One Rapidaptor bit holder for quick, one-handed bit changes
- One Kraftform Kompact bit-holding screwdriver for that ergonomic Kraftform feel

Impact Driver Set		
Part Number	Description	Price
05057460055	Wera Kraftform Kompact series driver set with screwdriver, 1/4inch hex socket drive, metric. 52 pieces. Includes Kraftform Kompact bitholding screwdriver and durable cloth pouch. Manufacturer part number: 057460.	\$135.00

Note: Screwdriver bits, bit-holders and L-keys are warranted against manufacturer defect only.



05057460055



05057460055 Contents		
	1/4 Kraftform Kompact bitholding screwdriver	
	1/4 Rapidator holder	1/4 x 50
	BiTorsion Phillips, 25mm long	(2) PH1, (4) PH2, (2) PH3
	Impaktor Phillips bit, 50mm long	(2) PH2, PH3
	BiTorsion Pozidriv® bits, 25mm long	(2) PZ1, (4) PZ2, (2) PZ3
	Impaktor Pozidriv® bits, 50mm long	(2) PZ2, PZ3
	BiTorsion Torx® bits	(2) TX10, (2) TX15, (3) TX20, (2) TX25, (2) TX30, TX40
	Impaktor Torx® bits, 50mm long	TX25, TX30, TX40
	BiTorsion® slotted bit, 25mm long	0.8 x 5.5, 1.0 x 5.5
	Impaktor Hex-Plus bit, 50mm long	4.0, 5.0, 6.0
	Hex Plus L-key	1.5 x 50, 2.0 x 56, 2.5 x 63, 3.0 x 71, 4.0 x 80, 5.0 x 90, 6.0 x 100, 8.0 x 112

**Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.**






Wera Driver Bits

Standard Driver Bits

Wera bits have been designed for demanding applications in trade and industry. They are able to transfer high torque loads, are safe to use and extremely durable.




Standard Driver Bits								
Part Number	Part Image	Type	Tip Size	Bit Length	Drive Size	Description	Package Quantity	Price
<u>TW-DB-PH-1</u>		⊕ Phillips	#1	2.75in	1/4in	Wera #1 Phillips general purpose driver bit, 2.75in bit length, 1/4in drive, hexagonal. Package of 10.	10	\$14.00
<u>TW-DB-PH-2</u>			#2			Wera #2 Phillips general purpose driver bit, 2.75in bit length, 1/4in drive, hexagonal. Package of 10.		\$13.00
<u>TW-DB-SL-1</u>		● Slotted	3.0mm	2in		Wera 3.0mm slotted general purpose driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 10.		\$33.00

Note: Screwdriver bits are warranted against manufacturer defect only.

Wera Zyklop Mini Bit Ratchet Sets

Zyklop Mini Bit Ratchet Sets		
Part Number	Description	Price
05073220055	Wera Tool-Check driver bit and socket set with Zyklop Mini bit ratchet, 1/4 inch drive, metric. 38 pieces. Plastic case included. Manufacturer part number 073220.	\$108.00
05056491001	Wera Tool-Check standard socket and driver bit set, 39 pieces, 1in bit length, 1/4in drive, imperial.	\$113.00
TW-DB-SET-28R	Wera Bit-Check driver bit set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE. 31 pieces. Plastic case included. Manufacturer part number 346293.	\$81.00

Note: Screwdriver bits are warranted against manufacturer defect.



Wera Tool-Check driver bit and socket set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE, 38 pieces. Includes the pieces listed in the table below.

Wera Bit-Check driver bit set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE, 31 pieces. Includes the pieces listed in the table below.

Wera Tool-Check PLUS Imperial standard socket and driver bit set with mini bit ratchet; 1/4in drive, and Kraffform screwdriver handle. Includes the pieces listed in the table below:

05073220055 Contents		
	Zyklop Mini bit ratchet	
	Rapidaptor bit holder	1/4 x 50
	1/4 socket adaptor	1/4 x 25
	Slotted	1.0 x 5.5 x 25
	Hex-Plus bit, 25mm long	3, 4, 5, 6, 8
	Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30, TX40
	Tamper-proof Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30
	Posidriv® bit, 25mm long	PZ1, (3) PZ2, PZ3
	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0

TW-DB-SET-28R Contents		
	Zyklop Mini bit ratchet	
	1/4 Rapidaptor bit holder	1/4 x 50
	1/4 socket adaptor	1/4 x 25
	Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30, TX40
	Tamperproof Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30
	Slotted bit	1.0 x 5.5 x 25
	Hex-Plus bit, 25mm long	3/32, 1/8, 5/32, 3/16, 1/4
	Square bit, 25mm long	#1, (3) #2, #3

05056491001 Contents		
	Zyklop Mini bit ratchet	
	1/4 Rapidaptor bit holder	1/4 x 50
	1/4 socket adaptor	1/4 x 25
	Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30, TX40
	Tamperproof Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30
	Slotted bit	1.0 x 5.5 x 25
	Hex-Plus bit, 25mm long	3/32, 1/8, 5/32, 3/16, 1/4
	6-point socket	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.