

# VOLUME ONE:

# TABLE OF CONTENTS

---



## Chapter 1: Getting Started

<b>Introduction</b> .....	1-2
The Purpose of this Manual .....	1-2
Where to Begin .....	1-2
Supplemental Manuals .....	1-2
Technical Support .....	1-2
<b>Conventions Used</b> .....	1-3
Key Topics for Each Chapter .....	1-3
<b>DL05 Micro PLC Components</b> .....	1-4
The DL05 Micro PLC Family .....	1-4
<i>Direct</i> SOFT 5 Programming for Windows™ .....	1-4
Handheld Programmer .....	1-5
<b>I/O Selection Quick Chart</b> .....	1-5
<b>Quick Start for PLC Checkout and Programming</b> .....	1-6
<b>Steps to Designing a Successful System</b> .....	1-10
<b>Questions and Answers about DL05 Micro PLCs</b> .....	1-12

## Chapter 2: Installation, Wiring, and Specifications

<b>Safety Guidelines</b> .....	2-2
Plan for Safety .....	2-2
Three Levels of Protection .....	2-3
Emergency Stops .....	2-3
Emergency Power Disconnect .....	2-4
Orderly System Shutdown .....	2-4
Class 1, Division 2 Approval .....	2-4
<b>Orientation to DL05 Front Panel</b> .....	2-5
Connector Removal .....	2-6

## Table of Contents

---

<b>Mounting Guidelines</b> .....	<b>2-7</b>
Unit Dimensions .....	2-7
Enclosures .....	2-7
Panel Layout & Clearances .....	2-8
Using DIN Rail Mounting Rails .....	2-9
Environmental Specifications .....	2-10
Agency Approvals .....	2-10
Marine Use .....	2-10
<b>Wiring Guidelines</b> .....	<b>2-11</b>
Fuse Protection for Input Power .....	2-11
External Power Source .....	2-12
Planning the Wiring Routes .....	2-12
Fuse Protection for Input and Output Circuits .....	2-13
I/O Point Numbering .....	2-13
<b>System Wiring Strategies</b> .....	<b>2-14</b>
PLC Isolation Boundaries .....	2-14
Connecting Operator Interface Devices .....	2-15
Connecting Programming Devices .....	2-15
Sinking/Sourcing Concepts .....	2-16
I/O “Common” Terminal Concepts .....	2-17
Connecting DC I/O to Solid State Field Devices .....	2-18
Solid State Input Sensors .....	2-18
Solid State Output Loads .....	2-18
Relay Output Wiring Methods .....	2-20
Surge Suppression For Inductive Loads .....	2-21
Prolonging Relay Contact Life .....	2-22
DC Input Wiring Methods .....	2-24
DC Output Wiring Methods .....	2-25
High Speed I/O Wiring Methods .....	2-26
<b>Wiring Diagrams and Specifications</b> .....	<b>2-28</b>
D0-05AR I/O Wiring Diagram .....	2-28
D0-05DR I/O Wiring Diagram .....	2-30
D0-05AD I/O Wiring Diagram .....	2-32
D0-05DD I/O Wiring Diagram .....	2-34
D0-05AA I/O Wiring Diagram .....	2-36

D0–05DA I/O Wiring Diagram .....	2–38
D0–05DR-D I/O Wiring Diagram .....	2–40
D0–05DD–D I/O Wiring Diagram .....	2–42
<b>Glossary of Specification Terms .....</b>	<b>2–44</b>

## Chapter 3: CPU Specifications and Operation

<b>Introduction .....</b>	<b>3–2</b>
DL05 CPU Features .....	3–2
<b>CPU Specifications .....</b>	<b>3–3</b>
<b>CPU Hardware Setup .....</b>	<b>3–4</b>
Communication Port Pinout Diagrams .....	3–4
Connecting the Programming Devices .....	3–5
CPU Setup Information .....	3–5
Status Indicators .....	3–6
Mode Switch Functions .....	3–6
Changing Modes in the DL05 PLC .....	3–7
Mode of Operation at Power-up .....	3–7
Auxiliary Functions .....	3–8
Clearing an Existing Program .....	3–8
Initializing System Memory .....	3–8
Setting Retentive Memory Ranges .....	3–9
Using a Password .....	3–10
<b>CPU Operation .....</b>	<b>3–11</b>
CPU Operating System .....	3–11
Program Mode .....	3–12
Run Mode .....	3–12
Read Inputs .....	3–13
Service Peripherals and Force I/O .....	3–13
Update Special Relays and Special Registers .....	3–14
Solve Application Program .....	3–14
Write Outputs .....	3–15
Diagnostics .....	3–15
<b>I/O Response Time .....</b>	<b>3–15</b>
Is Timing Important for Your Application? .....	3–15
Normal Minimum I/O Response .....	3–15

## Table of Contents

---

Normal Maximum I/O Response .....	3-16
Improving Response Time .....	3-17
<b>CPU Scan Time Considerations .....</b>	<b>3-18</b>
Reading Inputs .....	3-18
Writing Outputs .....	3-18
Application Program Execution .....	3-19
PLC Numbering Systems .....	3-20
PLC Resources .....	3-20
V-memory .....	3-21
Binary-Coded Decimal Numbers .....	3-21
Hexadecimal Numbers .....	3-21
<b>Memory Map .....</b>	<b>3-22</b>
Octal Numbering System .....	3-22
Discrete and Word Locations .....	3-22
V-memory Locations for Discrete Memory Areas .....	3-22
Input Points (X Data Type) .....	3-23
Output Points (Y Data Type) .....	3-23
Control Relays (C Data Type) .....	3-23
Timers and Timer Status Bits (T Data Type) .....	3-23
Timer Current Values (V Data Type) .....	3-24
Counters and Counter Status Bits (CT Data type) .....	3-24
Counter Current Values (V Data Type) .....	3-24
Word Memory (V Data Type) .....	3-25
Stages (S Data type) .....	3-25
Special Relays (SP Data Type) .....	3-25
<b>DL05 System V-memory .....</b>	<b>3-26</b>
System Parameters and Default Data Locations (V Data Type) .....	3-26
DL05 Memory Map Table .....	3-28
<b>DL05 Aliases .....</b>	<b>3-29</b>
<b>X Input Bit Map .....</b>	<b>3-30</b>
<b>Y Output Bit Map .....</b>	<b>3-30</b>
<b>Control Relay Bit Map .....</b>	<b>3-31</b>
<b>Stage Control/Status Bit Map .....</b>	<b>3-32</b>
<b>Timer Status Bit Map .....</b>	<b>3-32</b>
<b>Counter Status Bit Map .....</b>	<b>3-33</b>

## Chapter 4: Configuration and Connections

<b>DL05 System Design Strategies</b> .....	<b>4-2</b>
I/O System Configurations .....	4-2
Networking Configurations .....	4-2
Automatic I/O Configuration .....	4-3
Power Budgeting .....	4-3
<b>Network Configuration and Connections</b> .....	<b>4-4</b>
Configuring the DL05's Comm Ports .....	4-4
DL05 Port Specifications .....	4-4
Networking DL05 to DL05 RS-232C .....	4-4
Networking Using RS-422 Converters .....	4-5
Modbus Port Configuration .....	4-6
<i>DirectNET</i> Port Configuration .....	4-7
<b>Network Slave Operation</b> .....	<b>4-8</b>
Modbus Function Codes Supported .....	4-8
Determining the Modbus Address .....	4-8
If Your Host Software Requires the Data Type and Address...	4-9
Example 1: V2100 .....	4-10
Example 2: Y20 .....	4-10
Example 3: T10 Current Value .....	4-10
Example 4: C54 .....	4-10
If Your Modbus Host Software Requires an Address ONLY .....	4-11
Example 1: V2100 584/984 Mode .....	4-13
Example 2: Y20 584/984 Mode .....	4-13
Example 3: T10 Current Value 484 Mode .....	4-13
Example 4: C54 584/984 Mode .....	4-13
<b>Network Master Operation</b> .....	<b>4-14</b>
Step 1: Identify Master Port # and Slave # .....	4-15
Step 2: Load Number of Bytes to Transfer .....	4-15
Step 3: Specify Master Memory Area .....	4-16
Step 4: Specify Slave Memory Area .....	4-16
Communications from a Ladder Program .....	4-17
Multiple Read and Write Interlocks .....	4-17

## Chapter 5: Standard RLL and Standard RLL

<b>Introduction</b> .....	5-2
Instruction List .....	5-2
<b>Using Boolean Instructions</b> .....	5-4
END Statement .....	5-4
Simple Rungs .....	5-4
Normally Closed Contact .....	5-5
Contacts in Series .....	5-5
Midline Outputs .....	5-5
Parallel Elements .....	5-6
Joining Series Branches in Parallel .....	5-6
Joining Parallel Branches in Series .....	5-6
Combination Networks .....	5-6
Comparative Boolean .....	5-7
Boolean Stack .....	5-7
Immediate Boolean .....	5-8
<b>Boolean Instructions</b> .....	5-9
<b>Comparative Boolean</b> .....	5-25
<b>Immediate Instructions</b> .....	5-31
<b>Timer, Counter and Shift Register Instructions</b> .....	5-35
Using Timers .....	5-35
Timer Example Using Discrete Status Bits .....	5-37
Timer Example Using Comparative Contacts .....	5-37
Accumulating Fast Timer (TMRAF) .....	5-38
Accumulating Timer Example using Discrete Status Bits .....	5-39
Accumulator Timer Example Using Comparative Contacts .....	5-39
Using Counters .....	5-40
Counter Example Using Discrete Status Bits .....	5-42
Counter Example Using Comparative Contacts .....	5-42
Stage Counter Example Using Discrete Status Bits .....	5-44
Stage Counter Example Using Comparative Contacts .....	5-44
Up / Down Counter Example Using Discrete Status Bits .....	5-46
Up / Down Counter Example Using Comparative Contacts .....	5-46
<b>Accumulator/Stack Load and Output Data Instructions</b> .....	5-48

Using the Accumulator . . . . .	5-48
Copying Data to the Accumulator . . . . .	5-48
Changing the Accumulator Data . . . . .	5-49
Using the Accumulator Stack . . . . .	5-50
Using Pointers . . . . .	5-51
<b>Logical Instructions (Accumulator) . . . . .</b>	<b>5-60</b>
<b>Math Instructions . . . . .</b>	<b>5-68</b>
<b>Bit Operation Instructions . . . . .</b>	<b>5-82</b>
<b>Number Conversion Instructions (Accumulator) . . . . .</b>	<b>5-87</b>
Shuffle Digits Block Diagram . . . . .	5-94
<b>Table Instructions . . . . .</b>	<b>5-96</b>
Copy Data From a Data Label Area to V-memory . . . . .	5-98
<b>CPU Control Instructions . . . . .</b>	<b>5-99</b>
<b>Program Control Instructions . . . . .</b>	<b>5-101</b>
Understanding Master Control Relays . . . . .	5-106
MLS/MLR Example . . . . .	5-107
<b>Interrupt Instructions . . . . .</b>	<b>5-108</b>
External Interrupt Program Example . . . . .	5-109
Timed Interrupt Program Example . . . . .	5-110
Independent Timed Interrupt . . . . .	5-110
<b>Message Instructions . . . . .</b>	<b>5-111</b>
Fault Example . . . . .	5-111
Data Label Example . . . . .	5-113
<b>Intelligent I/O Instructions . . . . .</b>	<b>5-118</b>
<b>Network Instructions . . . . .</b>	<b>5-120</b>
<b>Intelligent Box (IBox) Instructions . . . . .</b>	<b>5-124</b>
(IBox) Instructions List . . . . .	5-124

