

# Index

---

## A

Agency Approvals, 2-7  
ASCII Table, G-2  
Auxiliary Functions, 3-16, A-2  
    Handheld Programmer Configuration, A-10  
    Memory Cartridge Operations, A-11  
    Password Operations, A-12  
    RLL Operations, A-5

## B

Bases, 2-10  
    CPU DIP Switches, 2-12  
    Types, 2-11  
Battery Backup, 3-12  
BCD Numbers, 3-33  
Bit Maps, 3-44 to 3-57  
Boolean Instructions, 5-4, 5-10 to 5-25

## C

Cables, Programming, 2-15  
Clock and Calendar, A-8  
    Instructions, 5-175  
Communication Ports, Specifications, 3-9 to 3-12  
Connect Solid State Devices, 2-21

Connector, I/O Ribbon Cable, 2-31

## CPU

Auxiliary Functions, A-2  
Battery Replacement, 9-2  
Clock and Calendar, 3-15  
Features, 3-2, 3-6  
Memory Map, 3-34  
Operating Modes, A-4  
Operating System, 3-18  
Password Protection, 3-15  
Scan Time, 3-26  
Setup, A-8  
    Set the Network Address, A-9  
Specifications, 3-4 to 3-6  
Status Indicators, 9-9

CPU Control Instructions, 5-177

## D

Diagnostics, 3-23  
DIP Switches, 3-8  
**DirectNET**, Port Configuration, 4-21  
Disabling Outputs, A-9  
DL405 Aliases, 3-43  
Drum Instruction Programming, 6-2  
    Control Techniques, 6-10  
    Drum Operation, 6-8  
    Step Transitions, 6-4 to 6-7

Drum Instructions, 6-12 to 6-14  
Drum instructions, EDRUM, 6-14

## E

Error Codes, B-2 to B-8  
European Directives, I-2  
Event drum, 6-15

## F

Force I/O, 3-20

## H

Hexadecimal Numbers, 3-33

## I

I/O Modules, I/O Configuration, A-6  
I/O Response Time, 3-24  
I/O Wiring and Specifications, 2-27  
    I/O Module Charts, 2-33  
Instruction Execution Times, C-2 to C-22  
Instructions  
    Accumulator/Data Stack, 5-54 to 5-57  
    ASCII to HEX, 5-135  
    BCD to Binary, 5-128  
    Binary to BCD, 5-129  
    Binary to Real, 5-132  
    Bit Operations, 5-121 to 5-127  
    Comparative Boolean, 5-26 to 5-31  
    Counters, 5-46 to 5-48  
    Encode, 5-126  
    End Statement, 5-4  
    Execution Times, C-2 to C-28  
    Gray Code, 5-139  
    HEX to ASCII, 5-136  
    Immediate Instructions, 5-32 to 5-40  
    Interrupts, 5-186  
    Load Label, 5-162  
    Master Control Relays, 5-183  
    Move, 5-146  
    Move Memory Cartridge, 5-162  
    Out, 5-65 to 5-68  
    Real to Binary, 5-133  
    Set Bit, 5-167  
    Shift Register, 5-53

Stage, 7-23  
Stage Counter, 5-49 to 5-50  
Stage Programming, 7-2  
Subroutines, 5-181  
Timers, 5-41 to 5-45  
Up/Down Counter, 5-51 to 5-52

Intelligent I/O Instructions, 5-189  
Interrupt Instructions, 5-185  
Instructions, Compare, 5-82 to 5-86

## K

Keyswitch Functions, 3-7

## L

Local I/O Expansion, 4-11

## M

Maintenance, 9-2  
    Battery Maintenance, 9-2  
    Code Identifiers, 9-6  
    Diagnostics, 9-4  
    Error Code Locations, 9-5  
    System Error Codes, 9-8  
    Test Modes, 9-19  
Manual Organization, 1-2, 1-6  
Masked Drums, 6-18  
Math Instructions, 5-87  
    Increment, 5-117  
    Increment Binary, 5-120  
    Transcendental Functions, 5-118  
Memory, F-2  
    Set Retentive Ranges, A-9  
Memory Cartridge, 3-14  
Memory cartridge, battery replacement, 9-3  
Memory Map  
    DL430, 3-40  
    DL440, 3-41  
    DL450, 3-42  
Message Instructions, 5-194 to 5-204  
MODBUS, Port Configuration, 4-20  
Module Placement, 4-4  
    I/O Configuration, 4-5

Mounting Guidelines, 2-6  
 Base Dimensions, 2-5  
 Panel Layout, 2-6

## N

Network Address, A-9  
 Network connections, MODBUS & *DirectNET*, 4-18  
 Network Instructions, 5-191  
 Network Master Operation, 4-28 to 4-31  
 Network Slave Operation, 4-22  
 Number Conversion Instructions, 5-128  
 Numbering Systems  
 BCD, H-5  
 Binary, H-2  
 Floating Point, H-6  
 Hexadecimal, H-3  
 Octal, H-4

## O

Octal Numbers, 3-32

## P

Part Numbering, 1-8  
 Passwords, A-12  
 PID  
 Analog Filter, 8-53  
 Bumpless Transfer, 8-13, 8-27  
 Cascade Control, 8-63  
 Tuning, 8-67  
 Control Introduction, 8-4  
*DirectSOFT* 5 Filter, 8-54  
 DL450 Control, 8-6  
 Error Flags, 8-18  
 Error Term Selection, 8-33  
 Loop Modes, 8-28, 8-52  
 On/Off Control, 8-68  
 Operation, 8-9  
 Parameters, 8-32  
 PID View, 8-49 to 8-51  
 Ramp/Soak, 8-39  
 Reset Windup, 8-10, 8-34  
 Special Features, 8-52  
 Time Proportioning, 8-68  
 PID Alarms  
 Alarm Features, 8-3

Auto Tuning Error, 8-47  
 Hysteresis, 8-13, 8-36, 8-38  
 Monitor Limit, 8-35  
 Overflow/Underflow Error, 8-38  
 Programming Error, 8-38  
 PV Deviation, 8-36  
 Rate-of-Change, 8-13, 8-37  
 Setup Alarms, 8-35

PID Loop  
 Alarms, 8-13  
 Configure, 8-26  
 Features, 8-2, 8-3  
 Feedforward Control, 8-70  
 Freeze Bias, 8-11, 8-34  
 Loop Definitions, 8-21  
 Mode, 8-28  
 Operating Modes, 8-14  
 Special Loop Calculations, 8-14  
 Setup, 8-18  
 Terminology, 8-74  
 Time-Proportioning Control, On/Off Control  
 Example, 8-67  
 Transfer Mode, 8-27  
 Troubleshooting Tips, 8-72, 8-74  
 Tuning, 8-40  
 Auto , 8-44  
 Manual, 8-41 to 8-44

PID Mode 2 Word Description, 8-23  
 PID Mode Setting 1 Description, 8-22  
 PID Position Algorithm, 8-9, 8-15  
 Position Form, 8-9  
 PID Velocity Algorithm, 8-9  
 Algorithm Form, 8-12  
 Velocity Algorithm, 8-15  
 Pointers, 5-58  
 Power Budget, 4-7  
 Calculation Example, 4-9  
 Power Budget , Worksheet, 4-10  
 Product Weights, E-2  
 Program Control Instructions, 5-179  
 Program Media, 3-13  
 Program Mode, 3-19  
 Programming  
 Accumulator Logic Instructions, 5-70 to 5-85  
 Bit Operation Instructions, 5-121 to 5-127  
 Comparative Boolean, 5-7  
 Compare Instructions, 5-82 to 5-86  
 Counters, 5-46 to 5-48  
 Instruction Set Table, 5-2 to 5-4  
 Load Instructions, 5-59 to 5-64

Midline Outputs, 5-5  
Out Instructions, 5-65 to 5-68  
Pointers, 5-58  
POP Instruction, 5-69  
Shift Register, 5-53  
Timers, 5-41 to 5-45  
Programming Methods, 1-4

## Q

Quick Start, 1-10, 1-12

## R

Ramp/Soak Generator, 8-56  
  Controls, 8-58  
  **Direct**SOFT Example, 8-60  
  Flag Bit Description Table, 8-24  
  Profile Monitoring, 8-59  
  Table, 8-56  
  Table Flags, 8-58  
  Table Location, 8-25  
  Test the Profile, 8-62, 8-64  
  Testing, 8-59  
Remote I/O Expansion, 4-12  
Retentive Memory, A-9  
Run Mode, 3-19

## S

Safety Guidelines, 2-2  
  Emergency Stops, 2-3  
Safety guidelines, Orderly System Shutdown, 2-4  
Scan Time  
  Display, A-8  
  Set the Watchdog Timer, A-8  
Scan Time Configuration, 3-15  
Sinking/Sourcing, 2-19  
Special Relays, D-2 to D-4  
Specialty I/O, 3-20  
Stage Programming, 7-2  
  Garage Door Opener Example, 7-10  
  Initial Stages, 7-5  
  Introduction, 7-2  
  Jump Instruction, 7-7  
  Parallel Processing Concepts, 7-19  
  Power Flow Transition, 7-18

Program Organization, 7-15  
Stage View, 7-28  
State Transition Diagrams, 7-3  
Unconditional Outputs, 7-18  
Status Indicators, 3-7  
Surge Suppression, 2-24  
System Components, 1-4  
System CRs, 3-39  
System Design, 1-16  
System Design Strategies, 4-2  
System Parameters, 3-38

## T

Table Instructions, 5-142  
Technical Support, 1-2, 1-6  
Test Modes, A-9  
Timed Drum, 6-16  
Troubleshooting  
  Electrical Noise, 9-16  
  I/O modules, 9-14

## V

V-memory Operations, A-6

## W

Wiring  
  Expansion Unit, 2-14  
  I/O Module, 2-28  
  I/O Strategies, 2-16  
  I/O wiring strategies, 2-17  
  Multi-point Modules, 2-29  
  Power Input, 3-8  
Wiring Guidelines, 2-13