

Table of Contents

Chapter 1: Getting Started

Introduction	1-2
The Purpose of this Manual	1-2
Where to Begin	1-2
Supplemental Manuals	1-2
Technical Support	1-2
Conventions Used	1-3
Key Topics for Each Chapter	1-3
DL105 Micro PLC Components	1-4
The DL105 Micro PLC Family	1-4
Programming Methods	1-4
<i>Direct</i> SOFT Programming for Windows™	1-4
Handheld Programmer	1-5
I/O Quick Chart Selection	1-5
Quick Start for PLC Checkout and Programming	1-6
Step 1: Unpack the Recommended DL105 Equipment	1-6
Step 2: Connect Switches to Input Terminals	1-7
Step 3: Connect the Power Wiring	1-8
Step 4: Connect the Programming Device	1-8
Step 5: Switch on the System Power	1-9
Step 6: Initialize Scratchpad Memory	1-9
Step 7: Enter a Ladder Program	1-9
Steps to Designing a Successful System	1-10
Step 1: Review the Installation Guidelines	1-10
Step 2: Understand the PLC Setup Procedures	1-10
Step 3: Review the I/O Selection Criteria	1-10
Step 4: Choose a System Wiring Strategy	1-10
Step 5: Understand the System Operation	1-10
Step 6: Review the Programming Concepts	1-11
Step 7: Choose the Instructions	1-11
Step 8: Understand the Maintenance and Troubleshooting Procedures	1-11
Questions and Answers about DL105 Micro PLCs	1-12

Chapter 2: Installation, Wiring, and Specifications

Safety Guidelines	2-2
Plan for Safety	2-2
Safety Techniques	2-2
Three Levels of Protection	2-3
Emergency Stops	2-3
Emergency Power Disconnect	2-4
Orderly System Shutdown	2-4

Class 1, Division 2 Approval	2-4
Orientation to DL105 Front Panel	2-5
Accessing the I/O Terminals	2-5
Protective Sheet for DL105 Vents	2-6
Connector Removal	2-6
Mounting Guidelines	2-7
Unit Dimensions	2-7
Enclosures	2-7
Panel Layout & Clearances	2-8
Agency Approvals	2-9
Environmental Specifications	2-9
Using Mounting Rails	2-10
Wiring Guidelines	2-11
Power Input Wiring	2-11
Fuse Protection for Input Power	2-11
External Power Source	2-12
Planning the Wiring Routes	2-13
Fuse Protection for Input and Output Circuits	2-13
I/O Point Numbering	2-13
System Wiring Strategies	2-14
PLC Isolation Boundaries	2-14
Powering I/O Circuits with the Auxiliary Supply	2-15
Powering I/O Circuits Using Separate Supplies	2-16
Connecting Operator Interface Devices	2-17
Connecting Programming Devices	2-17
Sinking / Sourcing Concepts	2-18
I/O “Common” Terminal Concepts	2-19
Connecting DC I/O to “Solid State” Field Devices	2-20
Solid State Input Sensors	2-20
Solid State Output Loads	2-20
Relay Output Wiring Methods	2-22
Surge Suppression For Inductive Loads	2-23
Prolonging Relay Contact Life	2-24
DC Input Wiring Methods	2-25
DC Output Wiring Methods	2-26
High-Speed I/O Wiring Methods	2-27
F1-04SIM Input Simulator Wiring	2-28
Wiring Diagrams and Specifications	2-29
F1-130AR I/O Wiring Diagram	2-29
F1-130AR General Specifications	2-30
F1-130DR/F1-130DR-CE I/O Wiring Diagram	2-31
F1-130DR/F1-130DR-CE General Specifications	2-32
F1-130AD I/O Wiring Diagram	2-33
F1-130AD General Specifications	2-34
F1-130DD/F1-130DD-CE I/O Wiring Diagram	2-35
F1-130DD/F1-130DD-CE General Specifications	2-36
F1-130AA I/O Wiring Diagram	2-37
F1-130AA General Specifications	2-38
F1-130DA I/O Wiring Diagram	2-39
F1-130DA General Specifications	2-40

F1-130DR-D I/O Wiring Diagram	2-41
F1-130DR-D General Specifications	2-42
F1-130DD-D I/O Wiring Diagram	2-43
F1-130DD-D General Specifications	2-44
Glossary of Specification Terms	2-45
Chapter 3: High-Speed Input and Pulse Output Features	
Introduction	3-2
Built-in Motion Control Solution	3-2
Availability of HSIO Features	3-2
Dedicated High-Speed I/O Circuit	3-3
Wiring Diagrams for Each HSIO Mode	3-3
Choosing the HSIO Operating Mode	3-4
Understanding the Six Modes	3-4
Default Mode	3-4
Configuring the HSIO Mode	3-5
Configuring Inputs X0 - X3	3-5
Mode 10: High-Speed Counter	3-6
Purpose	3-6
Functional Block Diagram	3-6
Wiring Diagram	3-7
Interfacing to Counter Outputs	3-7
Setup for Mode 10	3-8
Presets and Special Relays	3-8
Preset Data Starting Location	3-9
Using Fewer than 24 Presets	3-9
Equal Relay Numbers	3-9
Calculating Your Preset Values	3-10
X Input Configuration	3-10
Writing Your Control Program	3-11
Program Example: Counter Without Preset	3-11
Program Example Cont'd	3-12
Counter With Presets Program Example	3-13
Counter With Preload Program Example	3-15
Troubleshooting Guide for Mode 10	3-16
Mode 20: Quadrature Counter	3-17
Purpose	3-17
Functional Block Diagram	3-17
Quadrature Encoder Signals	3-17
Wiring Diagram	3-18
Interfacing to Encoder Outputs	3-18
Setup for Mode 20	3-19
X Input Configuration	3-19
Writing Your Control Program	3-20
Quadrature Counter w/Preload Program Example	3-20
Program Example Cont'd	3-21
Counter Preload Program Example	3-22
Troubleshooting Guide for Mode 20	3-22
Mode 30: Pulse Output	3-23

Purpose	3-23
Functional Block Diagram	3-24
Wiring Diagram	3-25
Interfacing to Drive Inputs	3-25
Motion Profile Specifications	3-26
Physical I/O Configuration	3-26
Logical I/O Functions	3-26
Setup for Mode 30	3-27
Profile / Velocity Select Register	3-27
Profile Parameter Table	3-28
Trapezoidal Profile	3-28
Registration Profile	3-28
Velocity Profile	3-28
Choosing the Profile Type	3-29
Trapezoidal Profile Defined	3-29
Registration and Home Search Profiles Defined	3-29
Velocity Profile Defined	3-29
Trapezoidal Profile Operation	3-30
Trapezoidal Profile Applications	3-30
Trapezoidal Profile Program Example	3-31
Program Example Cont'd	3-32
Preload Position Value	3-32
Registration Profile Operation	3-33
Registration Applications	3-33
Registration Profile Program Example	3-34
Program Example Cont'd	3-35
Home Search Program Example	3-36
Velocity Profile Operation	3-38
Velocity Profile Applications	3-38
Velocity Profile Program Example	3-39
Program Example Cont'd	3-40
Pulse Output Error Codes	3-41
Troubleshooting Guide for Mode 30	3-41
Mode 40: High-Speed Interrupts	3-43
Purpose	3-43
Functional Block Diagram	3-43
Setup for Mode 40	3-44
Interrupts and the Ladder Program	3-44
External Interrupt Timing Parameters	3-45
Timed Interrupt Parameters	3-45
X Input / Timed INT Configuration	3-45
External Interrupt Program Example	3-46
Timed Interrupt Program Example	3-47
Mode 50: Pulse Catch Input	3-48
Purpose	3-48
Functional Block Diagram	3-48
Pulse Catch Timing Parameters	3-48
Setup for Mode 50	3-49
X Input Configuration	3-49
Pulse Catch Program Example	3-50
Mode 60: Discrete Inputs with Filter	3-51

Purpose	3-51
Functional Block Diagram	3-51
Input Filter Timing Parameters	3-51
Setup for Mode 60	3-52
X Input Configuration	3-52
Filtered Inputs Program Example	3-53

Chapter 4: CPU Specifications and Operation

Introduction	4-2
DL105 CPU Features	4-2
CPU Specifications	4-3
CPU Hardware Setup	4-4
Communication Port Pinout Diagrams	4-4
Connecting the Programming Devices	4-5
CPU Setup Information	4-5
CPU Modes	4-6
Mode of Operation at Power-up	4-6
Changing Modes in the DL105 PLC	4-6
Setting Bits in V7633	4-7
Auxiliary Functions	4-8
Clearing an Existing Program	4-9
Initializing System Memory	4-9
Setting Retentive Memory Ranges	4-9
Using a Password	4-10
CPU Operation	4-11
CPU Operating System	4-11
Program Mode	4-12
Run Mode	4-12
Read Inputs	4-13
Service Peripherals and Force I/O	4-13
Update Special Relays and Special Registers	4-13
Solve Application Program	4-14
Write Outputs	4-14
Diagnostics	4-14
I/O Response Time	4-15
Is Timing Important for Your Application?	4-15
Normal Minimum I/O Response	4-15
Normal Maximum I/O Response	4-16
Improving Response Time	4-17
CPU Scan Time Considerations	4-18
Reading Inputs	4-18
Writing Outputs	4-18
Application Program Execution	4-19
PLC Numbering Systems	4-20
PLC Resources	4-20
V-Memory	4-21
Binary-Coded Decimal Numbers	4-21
Hexadecimal Numbers	4-21

Memory Map	4-22
Octal Numbering System	4-22
Discrete and Word Locations	4-22
V-Memory Locations for Discrete Memory Areas	4-22
Input Points (X Data Type)	4-23
Output Points (Y Data Type)	4-23
Control Relays (C Data Type)	4-23
Timers and Timer Status Bits (T Data type)	4-23
Timer Current Values (V Data Type)	4-24
Counters and Counter Status Bits (CT Data type)	4-24
Counter Current Values (V Data Type)	4-24
Word Memory (V Data Type)	4-25
Stages (S Data type)	4-25
Special Relays (SP Data Type)	4-25
DL105 System V-memory	4-26
System Parameters and Default Data Locations (V Data Type)	4-26
DL105 Aliases	4-28
DL105 Memory Map	4-29
X Input Bit Map	4-30
Y Output Bit Map	4-30
Control Relay Bit Map	4-30
Stage Control / Status Bit Map	4-31
Timer Status Bit Map	4-31
Counter Status Bit Map	4-31
 Chapter 5: Standard RLL Instructions	
Introduction	5-2
Using Boolean Instructions	5-3
END Statement	5-3
Simple Rungs	5-3
Normally Closed Contact	5-4
Contacts in Series	5-4
Midline Outputs	5-4
Parallel Elements	5-5
Joining Series Branches in Parallel	5-5
Joining Parallel Branches in Series	5-5
Combination Networks	5-6
Comparative Boolean	5-6
Boolean Stack	5-7
Immediate Boolean	5-8
Boolean Instructions	5-9
Store (STR)	5-9
Store Not (STRN)	5-9
Or (OR)	5-10
Or Not (ORN)	5-10
And (AND)	5-11

And Not (ANDN)	5-11
And Store (AND STR)	5-12
Or Store (OR STR)	5-12
Out (OUT)	5-14
Or Out (OR OUT)	5-14
Positive Differential (PD)	5-15
Set (SET)	5-15
Reset (RST)	5-15
Set, Reset Instr. Continued	5-16
Pause (PAUSE)	5-16
Comparative Boolean	5-17
Store If Equal (STRE)	5-17
Store If Not Equal (STRNE)	5-17
Or If Equal (ORE)	5-18
Or If Not Equal (ORNE)	5-18
And If Equal (ANDE)	5-19
And If Not Equal (ANDNE)	5-19
Store (STR)	5-20
Store Not (STRN)	5-20
Or (OR)	5-21
Or Not (ORN)	5-21
And (AND)	5-22
And Not (ANDN)	5-22
Immediate Instructions	5-23
Store Immediate (STRI)	5-23
Store Not Immediate (STRNI)	5-23
Or Immediate (ORI)	5-23
Or Not Immediate (ORNI)	5-23
And Immediate (ANDI)	5-24
And Not Immediate (ANDNI)	5-24
Or Out Immediate (OROUTI)	5-25
Set Immediate (SETI)	5-26
Reset Immediate (RSTI)	5-26
Timer, Counter and Shift Register Instructions	5-27
Using Timers	5-27
Timer (TMR) and Timer Fast (TMRF)	5-28
Timer Example Using Discrete Status Bits	5-29
Timer Example Using Comparative Contacts	5-29
Accumulating Timer (TMRA) Accumulating Fast Timer (TMRAF)	5-30
Accumulating Timer Example using Discrete Status Bits	5-31
Accumulator Timer Example Using Comparative Contacts	5-31
Using Counters	5-32
Counter (CNT)	5-33
Counter Example Using Discrete Status Bits	5-34
Counter Example Using Comparative Contacts	5-34
Stage Counter (SGCNT)	5-35
Stage Counter Example Using Discrete Status Bits	5-36
Stage Counter Example Using Comparative Contacts	5-36
Up Down Counter (UDC)	5-37
Up / Down Counter Example Using Discrete Status Bits	5-38

Up / Down Counter Example Using Comparative Contacts	5-38
Shift Register (SR)	5-39
Accumulator / Stack Load and Output Data Instructions	5-40
Using the Accumulator	5-40
Copying Data to the Accumulator	5-40
Changing the Accumulator Data	5-40
Using the Accumulator Stack	5-42
Using Pointers	5-43
Load (LD)	5-45
Load Double (LDD)	5-46
Load Formatted (LDF)	5-47
Load Address (LDA)	5-48
Out (OUT)	5-49
Out Double (OUTD)	5-49
Out Formatted (OUTF)	5-50
Pop (POP)	5-50
Pop Instruction Continued	5-51
Logical Instructions (Accumulator)	5-52
And (AND)	5-52
And Double (ANDD)	5-53
Or (OR)	5-54
Or Double (ORD)	5-55
Exclusive Or (XOR)	5-56
Exclusive Or Double (XORD)	5-57
Compare (CMP)	5-58
Compare Double (CMPD)	5-59
Math Instructions	5-60
Add (ADD)	5-60
Add Double (ADDD)	5-61
Subtract (SUB)	5-62
Subtract Double (SUBD)	5-63
Multiply (MUL)	5-64
Divide (DIV)	5-65
Increment Binary (INCB)	5-66
Decrement Binary (DECB)	5-66
Bit Operation Instructions	5-67
Shift Left (SHFL)	5-67
Shift Right (SHFR)	5-68
Encode (ENCO)	5-69
Decode (DECO)	5-70
Number Conversion Instructions (Accumulator)	5-71
Binary (BIN)	5-71
Binary Coded Decimal (BCD)	5-72
Invert (INV)	5-73
Table Instructions	5-74
Move (MOV)	5-74
Move Memory Cartridge / Load Label (MOVMC), (LDLBL)	5-75
Copy Data From a Data Label Area to V-Memory	5-76
CPU Control Instructions	5-77

No Operation (NOP)	5-77
End (END)	5-77
Stop (STOP)	5-77
Program Control Instructions	5-78
Master Line Set (MLS)	5-78
Master Line Reset (MLR)	5-78
Understanding Master Control Relays	5-78
MLS/MLR Example	5-79
Interrupt Instructions	5-80
Interrupt (INT)	5-80
Interrupt Return (IRT)	5-80
Enable Interrupts (ENI)	5-80
Disable Interrupts (DISI)	5-80
External Interrupt Program Example	5-81
Timed Interrupt Program Example	5-82
Message Instructions	5-83
Fault (FAULT)	5-83
Fault Example	5-83
Data Label (DLBL)	5-84
ASCII Constant (ACON)	5-84
Numerical Constant (NCON)	5-84
Data Label Example	5-85
 Chapter 6: Drum Instruction Programming	
Introduction	6-2
Purpose	6-2
Drum Terminology	6-2
Drum Chart Representation	6-3
Output Sequences	6-3
Step Transitions	6-4
Drum Instruction Parameters	6-4
Timer-Only Transitions	6-4
Timer and Event Transitions	6-5
Event-Only Transitions	6-6
Counter Assignments	6-6
Last Step Completion	6-7
Overview of Drum Operation	6-8
Drum Instruction Block Diagram	6-8
Powerup State of Drum Registers	6-9
Drum Control Techniques	6-10
Drum Control Inputs	6-10
Self-Resetting Drum	6-11
Initializing Drum Outputs	6-11
Using Complex Event Step Transitions	6-11
Drum Instruction	6-12
Event Drum (EDRUM)	6-12
Handheld Programmer Drum Mnemonics	6-14

Chapter 7: RLL^{PLUS} Stage Programming

Introduction to Stage Programming	7-2
Overcoming “Stage Fright”	7-2
Learning to Draw State Transition Diagrams	7-3
Introduction to Process States	7-3
The Need for State Diagrams	7-3
A 2-State Process	7-3
RLL Equivalent	7-4
Stage Equivalent	7-4
Let’s Compare	7-5
Initial Stages	7-5
What Stage Bits Do	7-6
Stage Instruction Characteristics	7-6
Using the Stage Jump Instruction for State Transitions	7-7
Stage Jump, Set, and Reset Instructions	7-7
Stage Program Example: Toggle On/Off Lamp Controller	7-8
A 4-State Process	7-8
Four Steps to Writing a Stage Program	7-9
Stage Program Example: A Garage Door Opener	7-10
Garage Door Opener Example	7-10
Draw the Block Diagram	7-10
Draw the State Diagram	7-11
Add Safety Light Feature	7-12
Modify the Block Diagram and State Diagram	7-12
Using a Timer Inside a Stage	7-13
Add Emergency Stop Feature	7-14
Exclusive Transitions	7-14
Stage Program Design Considerations	7-15
Stage Program Organization	7-15
How Instructions Work Inside Stages	7-16
Using a Stage as a Supervisory Process	7-17
Stage Counter	7-17
Power Flow Transition Technique	7-18
Stage View in DirectSOFT	7-18
RLL^{PLUS} Stage Instructions	7-19
Stage (SG)	7-19
Initial Stage (ISG)	7-20
JUMP (JMP)	7-20
Questions and Answers about Stage Programming	7-21

Chapter 8: Maintenance and Troubleshooting

Hardware System Maintenance	8-2
Diagnostics	8-2
CPU Indicators	8-6

Communications Problems	8-7
I/O Point Troubleshooting	8-8
Noise Troubleshooting	8-10
Machine Startup and Program Troubleshooting	8-11

Appendix A: Auxiliary Functions

Introduction	A-2
Purpose of Auxiliary Functions	A-2
Accessing AUX Functions via DirectSOFT	A-3
Accessing AUX Functions via the Handheld Programmer	A-3
AUX 2* — RLL Operations	A-4
AUX 21 Check Program	A-4
AUX 22 Change Reference	A-4
AUX 23 Clear Ladder Range	A-4
AUX 24 Clear Ladders	A-4
AUX 3* — V-memory Operations	A-4
AUX 31 Clear V-Memory	A-4
AUX 4* — I/O Configuration	A-4
AUX 41 Show I/O Configuration	A-4
AUX 5* — CPU Configuration	A-5
AUX 51 Modify Program Name	A-5
AUX 53 Display Scan Time	A-5
AUX 54 Initialize Scratchpad	A-5
AUX 55 Set Watchdog Timer	A-5
AUX 57 Set Retentive Ranges	A-5
AUX 58 Test Operations	A-6
AUX 5B Counter Interface Configuration	A-6
AUX 6* — Handheld Programmer Configuration	A-6
AUX 61 Show Revision Numbers	A-6
AUX 62 Beeper On / Off	A-6
AUX 65 Run Self Diagnostics	A-6
AUX 7* — EEPROM Operations	A-7
Transferrable Memory Areas	A-7
AUX 71 CPU to HPP EEPROM	A-7
AUX 72 HPP EEPROM to CPU	A-7
AUX 73 Compare HPP EEPROM to CPU	A-7
AUX 74 HPP EEPROM Blank Check	A-7
AUX 75 Erase HPP EEPROM	A-7
AUX 76 Show EEPROM Type	A-7
AUX 8* — Password Operations	A-8
AUX 81 Modify Password	A-8
AUX 82 Unlock CPU	A-8
AUX 83 Lock CPU	A-8

Appendix B: DL105 Error Codes

DL105 Error Codes	B-2
-------------------------	-----

Appendix C: Instruction Execution Times

Introduction	C-2
V-Memory Data Registers	C-2
V-Memory Bit Registers	C-2
How to Read the Tables	C-2
Instruction Execution Times	C-3
Boolean Instructions	C-3
Comparative Boolean Instructions	C-3
Immediate Instructions	C-6
Timer, Counter, Shift Register, EDRUM Instructions	C-6
Accumulator Data Instructions	C-7
Logical Instructions	C-8
Math Instructions	C-8
Bit Instructions	C-9
Number Conversion Instructions	C-9
Table Instructions	C-9
CPU Control Instructions	C-10
Program Control Instructions	C-10
Interrupt Instructions	C-10
Message Instructions	C-10
RLL ^{PLUS} Instructions	C-10

Appendix D: Special Relays

DL105 PLC Special Relays	D-2
Startup and Real-Time Relays	D-2
CPU Status Relays	D-2
System Monitoring	D-2
Accumulator Status	D-3
HSIO Pulse Catch Relay	D-3
Equal Relays for HSIO Mode 10 Counter Presets	D-3

Appendix E: PLC Memory

DL105 PLC Memory	E-2
------------------------	-----

Appendix F: European Union Directives (CE)

European Union (EU) Directives	F-2
Member Countries	F-2
Special Installation Manual	F-4
Other Sources of Information	F-4
Basic EMC Installation Guidelines	F-5
Enclosures	F-5
AC Mains Filters	F-5
Suppression and Fusing	F-5

Internal Enclosure Grounding	F-6
Equi-potential Grounding	F-6
Communications and Shielded Cables	F-6
Analog and RS232 Cables	F-7
Multidrop Cables	F-7
Shielded Cables	F-7
within Enclosures	F-7
Network Isolation	F-7

Appendix G: Numbering Systems

Introduction	G-2
Binary Numbering System	G-2
Hexadecimal Numbering System	G-3
Octal Numbering System	G-4
Binary Coded Decimal (BCD) Numbering System	G-5
Real (Floating Point) Numbering System	G-6
BCD/Binary/Decimal/Hex/Octal - What is the Difference?	G-7
Data Type Mismatch	G-8
Signed vs. Unsigned Integers	G-9
AutomationDirect.com Products and Data Types	G-10
<i>Direct</i> LOGIC PLCs	G-10
C-more/C-more Micro-Graphic Panels	G-10

Index