

Table of Contents

Chapter 1: Introduction

About This Manual	1-2
The Purpose of this Manual	1-2
Supplemental Manuals	1-2
Technical Support	1-2
Conventions Used	1-3
Key Topics for Each Chapter	1-3
CPU-slot Controllers	1-4
DL205 System I/O Components	1-5
Bases	1-5
I/O Configuration	1-5
I/O Modules	1-5

Chapter 2: Installation and Power Wiring

Safety Guidelines	2-2
Plan for Safety	2-2
Safety Techniques	2-2
Orderly System Shutdown	2-3
System Power Disconnect	2-3
Mounting Guidelines	2-4
Base Dimensions	2-4
Panel Mounting and Layout	2-5
Enclosures	2-6
Environmental Specifications	2-7
Power	2-7
Agency Approvals	2-7
Component Dimensions	2-8
Installing DL205 Bases	2-9
Choosing the Base Type	2-9
Mounting the Base	2-9
Using Mounting Rails	2-10
Installing Components in the Base	2-11
Base Wiring Guidelines	2-12
Base Wiring	2-12

Chapter 3: I/O Wiring and Specifications

I/O Wiring Strategies	3-2
DL205 System Isolation Boundaries	3-2
Powering I/O Circuits with the Auxiliary Supply	3-3
Powering I/O Circuits Using Separate Supplies	3-4
Sinking / Sourcing Concepts	3-5
I/O "Common" Terminal Concepts	3-6
Connecting DC I/O to "Solid State" Field Devices	3-7

Solid State Input Sensors	3-7
Solid State Output Loads	3-7
Relay Output Guidelines	3-9
Surge Suppression For Inductive Loads	3-9
Prolonging Relay Contact Life	3-11
I/O Modules Position, Wiring, and Specification	3-14
Slot Numbering	3-14
Module Placement Restrictions	3-14
Discrete Input Module Status Indicators	3-15
Color Coding of I/O Modules	3-15
Wiring the Different Module Connectors	3-16
I/O Wiring Checklist	3-17
Glossary of Specification Terms	3-18
Inputs or Outputs Per Module	3-18
Commons / Module	3-18
Input Volt. Range	3-18
Output Volt. Range	3-18
Peak Voltage	3-18
AC Frequency	3-18
ON Voltage Level	3-18
OFF Voltage Level	3-18
Input Impedance	3-18
Input Current	3-18
Min. ON Current	3-18
Max. OFF Current	3-18
Minimum Load	3-18
Ext. DC Required	3-18
ON Voltage Drop	3-18
Max. Leakage Current	3-18
Max Inrush Current	3-18
Base Power Required	3-18
OFF to ON Response	3-18
ON to OFF Response	3-18
Terminal Type	3-18
Status Indicators	3-18
Weight	3-18
Fuses	3-18
D2-08ND3 DC Input	3-19
D2-16ND3-2 DC Input	3-19
D2-32ND3 DC Input	3-20
D2-32ND3-2 DC Input	3-21
D2-08NA-1 AC Input	3-22
D2-08NA-2 AC Input	3-22
D2-16NA AC Input	3-23
F2-08SIM Input Simulator	3-23
D2-04TD1 DC Output	3-24
D2-08TD1 DC Output	3-25
D2-16TD1-2 DC Output	3-25
D2-08TD2 DC Output	3-26

D2–32TD2 DC Output	3–26
D2–16TD2–2 DC Output	3–27
D2–32TD1 DC Output	3–27
D2–08TA AC Output	3–28
F2–08TA AC Output	3–28
D2–12TA AC Output	3–29
D2–04TRS Relay Output	3–30
D2–08TR Relay Output	3–31
F2–08TR Relay Output	3–32
F2–08TRS Relay Output	3–33
D2–12TR Relay Output	3–34
D2–08CDR 4 pt. DC Input / 4pt. Relay Output	3–35
F2–04AD-1 4 Channel 4–20mA Analog Input	3–36
F2–04AD-1L 4 Channel 4–20mA Analog Input	3–37
F2–04AD-2 4 Channel Voltage Analog Input	3–38
F2–04AD-2L 4 Channel Voltage Analog Input	3–39
F2–08AD-1 8 Channel 4–20mA Analog Input	3–40
F2–08AD-2 8 Channel Voltage Analog Input	3–41
F2–04RTD 4 Channel RTD Input	3–42
F2–04THM 4 Channel Thermocouple Input	3–43
F2–02DA-1(L) 2 Channel 4–20mA Analog Output	3–44
F2–02DA-2(L) 2 Channel Voltage Analog Output	3–45
F2–08DA–1 8-Channel Current Analog Output	3–46
F2–08DA–2 8-Channel Voltage Analog Output	3–47
F2–02DAS-1 Isolated 2 Channel 4–20mA Analog Output	3–48
F2–02DAS-2 Isolated 2 Channel Voltage Analog Output	3–49
F2-4AD2DA 4-Channel Analog Input / 2-Channel Analog Output	3–50

Appendix A: European Union Directives (CE)

European Union (EU) Directives	A–2
Member Countries	A–2
Special Installation Manual	A–3
Other Sources of Information	A–4
Basic EMC Installation Guidelines	A–4
Enclosures	A–4
Electrostatic Discharge (ESD)	A–4
Suppression and Fusing	A–5
Internal Enclosure Grounding	A–6
Equi-potential Grounding	A–6
Communications and Shielded Cables	A–6
Analog and RS232 Cables	A–7
Multidrop Cables	A–7
Shielded Cables	A–7
within Enclosures	A–7
Network Isolation	A–8
Items Specific to the DL205	A–8