


REV.	CNN	CNN DESCRIPTION	Date	Check in
01	3373	UPDATE MATERIAL	18/01/2012	Shaun Barron
02	3373	UPDATE MATERIAL	18/01/2012	Shaun Barron



NOTES:

1. MATERIAL: BLACK 38 60 SHORE, MATERIAL CODE C5560 VERSION 3
2. WALL THICKNESS 1.5mm MIN. / 2.0mm MAX
3. DIMENSIONS ARE INSIDE, THEREFORE THE DIMENSIONS SPECIFY THE SIZE OF THE MOULD TOOL.
4. IF THERE IS SIGNIFICANT SHRINKAGE PLEASE ALLOW FOR THIS.
5. ROUND EDGES WITH APPROX. RADIUS 3mm UNLESS OTHERWISE STATED.

APPLICATION	SLEEVE	D	H	L	h	d	R
RS	SLV26	19	28	50	12	5	5
M5	SLV37	12	20	50	7	7	3
M6	SLV38	17	30	60	10	10	5
M8	SLV39	22	35	70	12	15	6
M10	SLV40	28	40	80	15	20	8

Tel No. +44(0)1724 273200 Website www.dem-uk.com



PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
 ALPHA 3 MANUFACTURING.
 ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF
 ALPHA 3 MANUFACTURING IS PROHIBITED.

DEM DEM Manufacturing, Deltron Emcon House
 Hargreaves Way, Sawcliffe Ind. Park,
 Scunthorpe, North Lincolnshire, DN15 8RF, UK

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MILLIMETRES
 LINEAR TOLERANCE:
NO DECIMAL PLACES ±0.5mm
1 DECIMAL PLACE ±0.25mm
2 DECIMAL PLACES ±0.125mm
 ANGULAR TOLERANCE: ±1°

FINISH SEE NOTE
 DEBURR AND BREAK SHARP EDGES
 IF IN DOUBT ASK
 DO NOT SCALE DRAWING
 MATERIAL SEE NOTE

DRAWN BY SPB
 APPROVED BY SW
 THIRD ANGLE PROJECTION

SHEET 1 OF 1
 SCALE 1:1
 A4

TITLE
SLV37-40-PS
PROCUREMENT SPECIFICATION
RUBBER BOOTS

DRAWING NO. **SLV37-40**
 ISSUE **02**
 Release