

Quick reference guide 3200303

Technical data


Order Number	3200303
Cooling capacity L35L35	680 BTU
Temperature range	-4°F - 149°F
Air volume flow	Ambient air circuit: 70 / 153 cfm Cabinet air circuit: 70 / 153 cfm
Mounting	Recessed
Housing Material	Stainless steel AISI 304 (V2A)
Dimension HxBxT	15.7 x 7.1 x 6.7 (3.2) inch
Weight	22 lbs.
Cut out dimensions	14.6 x 6.1 inch
Voltage / Frequency	24 V DC
Current L35L35	10.8 A
Starting current	17 A
Max. current	11.6 A
Nominal power L35L35	260 W
Max. power	280 W
Fuse rating	16 A (T)
Connection	Connection terminal block
Ingress protection	IP 66, Type 4X
Approvals	CE, RoHS, cURus

The torque for the mounting nuts should be 4.5 Nm.

Seifert Systems GmbH	Seifert Systems Ltd.	Seifert Systems AG	Seifert Systems Inc.	Seifert Systems Pty Ltd.
Albert - Einstein Str. 3	HF09/10	Wilerstrasse 16	75 Circuit Drive	105 Lewis Road
42477 Radevormwald	Hal-Far Industrial Estate	4563 Gerlafingen	North Kingstown	Wantirna South
Deutschland	Birzebbuga, BBG 3000	Switzerland	RI 0285	3152 Victoria
Tel. +49 2195 68994-0	Tel. +356 2220 7000	Tel. +41 32 675 35 51	Tel. +1 401-294-6960	Tel. +61 3 98 01 19 06
Fax +49 2195 6899420	Fax +356 2165 2009	Fax +41 32 675 44 76	Fax +1 401-294-6963	Fax. +61 3 98 87 08 45
info.de@seifertsystems.com	info@seifertsystems.com	info.ch@seifertsystems.com	info.us@seifertsystems.com	info@seifertsystems.com.au

Mounting Principle

In order to maintain the TYPE 4 rating, the tightening torque for this unit should be 4.5 Nm and needs to follow the below sequence.



Wiring diagram

Partlist

TE	Thermoelectric Elements
IF	Internal Fan
AF	Ambient Fan

