

Quick reference guide 6105303

Technical data


Order Number	6105303
Cooling capacity L35L35	340 BTU
Temperature range	-4°F - 149°F
Air volume flow	Ambient air circuit: 75 / 125 cfm Cabinet air circuit: 27 / 53 cfm
Mounting	Recessed
Housing Material	Stainless steel AISI 304 (V2A)
Dimension HxBxT	11 x 13.8 x 7.2 (4.6) inch.
Weight	21 lbs.
Cut out dimensions	13.8 x 11 inch
Voltage / Frequency	120 - 230 V ~ 50/60 Hz
Current L35L35	1.1 A @ 120 V 0.5 A @ 230 V
Starting current	1.6 A @ 120 V 0.8 A @ 230 V
Max. current	1.1 A @ 120 V 0.6 A @ 230 V
Nominal power L35L35	126 W
Max. power	131 W
Fuse rating	2 A (T) @ 120 V 1 A (T) @ 230 V
Connection	8-Pole Connector
Ingress protection	IP 66, Type 4X
Approvals	CE, RoHS, cURus

The torque for the mounting nuts should be 4.5 Nm.

Seifert Systems GmbH Albert - Einstein Str. 3 42477 Radevormwald Deutschland Tel. +49 2195 68994-0 Fax +49 2195 6899420 info.de@seifertsystems.com	Seifert Systems Ltd. HF09/10 Hal-Far Industrial Estate Birzebbuga, BBG 3000 Malta Tel. +356 2220 7000 Fax +356 2165 2009 info@seifertsystems.com	Seifert Systems AG Wilerstrasse 16 4563 Gerlafingen Switzerland Tel. +41 32 675 35 51 Fax +41 32 675 44 76 info.ch@seifertsystems.com	Seifert Systems Inc. 75 Circuit Drive North Kingstown RI 0285 USA Tel. +1 401-294-6960 Fax +1 401-294-6963 info.us@seifertsystems.com	Seifert Systems Pty Ltd. 105 Lewis Road Wantirna South 3152 Victoria Australia Tel. +61 3 98 01 19 06 Fax. +61 3 98 87 08 45 info@seifertsystems.com.au
---	--	--	---	---

Mounting Principle

In order to maintain the TYPE 4X rating, the tightening torque for this unit should be 4.5 Nm and needs to follow the below sequence.



Wiring diagram

