

Specifications

In This Appendix. . . .
— Specifications

Specifications

H0-PSCM Profibus Slave Communications Module

Module Type	Profibus Network Interface Module
Maximum Expansion	32 stations per segment, 9 repeaters max./segment, 126 stations maximum
Communications	RS-485
Auto-configuring	GSD file in Master
ProfibusProfile	DP
Profibus Port	9-pin D-shell
Node Address	3 to 125 (decimal) set by DIP switches (0 used by the Master)
Segment distance	100 meters (327 feet) to 1200 meters (3270 feet)
Baud Rate	Selectable from 9.6 kbps to 12 Mbps
LED Indicators	STA (STATUS/Module): ON = module power-up check passed OFF = module power-up check failed ACT (ACTIVE/Link): ON = Network is active OFF = Network is not active LINK (Holding): ON = PBC is configured correctly and running OFF = Incorrect I/O configuration ERR (ERROR): ON = watchdog timer timeout represents hardware, communications, or network fault; power-on reset or reset within master device software
Communications Port	RJ12, RS232C (used for firmware upgrade only)
Base Power Requirement	530mA @ 5VDC (supplied by base power supply)

General Specifications

Installation Requirements	Installs in option slot
Operating Temperature	32° F to 131° F (0° C to 55° C)
Storage Temperature	-4° F to 158° F (-20° C to 70° C)
Relative Humidity	5 to 95% (non-condensing)
Environmental Air	No corrosive gases, pollution level = 2 (UL 840)
Vibration	MIL STD 810C 514.2
Shock	MIL STD 810C 516.2
Noise Immunity	NEMA ICS3-304 Impulse noise 1 μ s, 1000V FCC class A RFI (144MHz, 430MHz, 10W, 10cm)
Manufacturer	Host Automation Products

Cable Specifications

Permitted Ambient Conditions	
Operating Temperature	32° F to 131° F (–40° C to 60° C)
Storage Temperature	–4° F to 158° F (–40° C to 60° C)
Installation Temperature	(–40° C to 60° C)
Bending Radius	
First and final bend	≥ 75 mm
Repeated bending	≥ 150 mm