

# Index

---

## A

- Address
  - assigning a hardware address, 12,18
  - conventions, 20
  - setting the dip switch, 12
  - termination resistor, 12
- Addressing conventions, 20

## B

- Base register address, 20
- Baud rate, 17
- Bezel, 4
- Bit-of-Word, 21

## C

- Cable requirements, 8
  - cables, 9,10
- Communications Master, 8
- Connector specification, 9
  - Programming cable, 9
- Connector specifications, 10
  - PLC-to-Panel cable, 10
- Control relays, 29, 35
- Current Drain, 11
- Cutout area for panel, 7

## D

- Dimensions for mounting, 7
- DIP switch, 3,12
- DirectSOFT, 1
  
- Downloading, 18

## F

- File number (Allen-Bradley), 18
- 5/04, 10
- Force function, 15

## I

- Internal Relays, 21

## L

- Labels, 4
  - Preparing labels, 4
  - Template, 5
- Lamps, 15
- LEDs, 15

## M

- Memory mapping, 2,14
-

## N

NEMA, 6

## O

Octal numbers, 23

OP-9001, 8,13

OP-CMCON-1, 10

OP-CMCON-2, 10

OPWinEdit, 1,16

## P

Power supply, 11

Product support, 1

Pushbuttons, 14

## R

R-memory, 20

Remapping, 21

Ribbon cable, 8

RS422, 13  
pinouts, 9

## S

Separation of LED, 15

SIMATIC, 10

SLC500, 10

5/03, 10

Slice I/O, 10

Specifications, 6

communication link, 6

diagnostics, 6

NEMA rating, 6

storage temperature, 6

operating humidity, 6

operating temperature, 6

power budget, 6

power connector, 6

weight, 6

System requirements, 17

## T

Termination resistor, 12

TI305, 10

TI405, 10

## W

Windows, 1,16

---