

STRIDE™ INDUSTRIAL ETHERNET FIBER TRANSCEIVERS GIGABIT ETHERNET



Description:

STRIDE Gigabit (1.25GB) Small Form Factor Pluggable (SFP) transceiver module (Transmit/Receive). Hot Swappable. Short or long wavelength of 850nm or 1310nm, dependant on model. Supports data transmission up to 550 meters, 2km, 10 km, or 30 km on a single-mode or multi-mode fiber, dependant on model. LC duplex receptacle, SFP Multi-Source Agreement compliant.

Transmitter Optical characteristics


Parameter (unit)	Minimum	Typical	Maximum
Output optical power (dBm)	SFP-500-GMF	-9.5	-4
	SFP-2K-GMF	-9	-1
	SFP-10K-GSF	-9.5	-3
	SFP-30K-GSF	-2	3
Extinction Ratio (dB)	SFP-500-GMF	9	
	SFP-2K-GMF		
	SFP-10K-GSF		
	SFP-30K-GSF		
Center Wavelength (nm)	SFP-500-GMF	850	860
	SFP-2K-GMF	1270	1355
	SFP-10K-GSF	1285	1343
	SFP-30K-GSF	1270	1355
	SFP-500-GMF		0.85
Spectral width - RMS (nm)	SFP-2K-GMF		4
	SFP-10K-GSF		2.8
	SFP-30K-GSF		1
	SFP-500-GMF		
Rise / Fall Time - 20% - 80% (ps)	SFP-2K-GMF		260
	SFP-10K-GSF		
	SFP-30K-GSF		
	SFP-500-GMF		

Receiver Optical characteristics

Parameter (unit)	Minimum	Maximum
Sensitivity (dBm)	SFP-500-GMF	-17
	SFP-2K-GMF	-19
	SFP-10K-GSF	-20
	SFP-30K-GSF	-23
Operating Wavelength (nm)	SFP-500-GMF	770
	SFP-2K-GMF	1260
	SFP-10K-GSF	1270
	SFP-30K-GSF	1580
	SFP-500-GMF	12
Return Loss (dB)	SFP-2K-GMF	
	SFP-10K-GSF	
	SFP-30K-GSF	
	SFP-500-GMF	
Loss of Signal - Deasserted (dBm)	SFP-2K-GMF	-17.5
	SFP-10K-GSF	-19
	SFP-30K-GSF	-20
	SFP-500-GMF	-23
Loss of Signal - Asserted (dBm)	SFP-2K-GMF	-35
	SFP-10K-GSF	
	SFP-30K-GSF	
	SFP-500-GMF	
Loss of Signal - Hysteresis (dB)	SFP-2K-GMF	0.5
	SFP-10K-GSF	
	SFP-30K-GSF	
	SFP-500-GMF	

General Specifications		
Connector Type	Type LC connector with bail latch	
Operating Temperature range	-40 to +85 °C (-40 to +185 °F)	
Storage temperature range	-40 to +85 °C (-40 to +185 °F)	
Humidity (non-condensing)	5 to 95% RH	
Link Speed	Gigabit Ethernet	
Laser Type	SFP-500-GMF	VCSEL laser diode (Class 1 laser safety standard IEC 60825 compliant)
	SFP-2K-GMF	FP laser diode (Class 1 laser safety standard IEC 60825 compliant)
	SFP-10K-GSF	FP laser diode (Class 1 laser safety standard IEC 60825 compliant)
	SFP-30K-GSF	DFB laser diode (Class 1 laser safety standard IEC 60825 compliant)
Media	SFP-500-GMF	Multi-mode Fiber
	SFP-2K-GMF	
	SFP-10K-GSF	Single-mode Fiber
	SFP-30K-GSF	
Fiber	SFP-500-GMF	50 / 125 μm and 62.5 / 125 μm
	SFP-2K-GMF	
	SFP-10K-GSF	9 / 125 μm
	SFP-30K-GSF	
Code	SFP-500-GMF	SX
	SFP-2K-GMF	SX2
	SFP-10K-GSF	LX
	SFP-30K-GSF	lhx
Distance	SFP-500-GMF	550m
	SFP-2K-GMF	2km
	SFP-10K-GSF	10 km
	SFP-30K-GSF	40 km
Compliances	SFP-500-GMF	1.0625Gbps Fiber Channel FC-PI 100-M5-SN-I compliant 1.0625Gbps Fiber Channel FC-PI 100-M6-SN-I compliant 1.25Gbps IEEE 802.3z 1000BASE-SX compliant 1.25Gbps IEEE 802.3ah 1000BASE-SX compliant
	SFP-2K-GMF	IEEE 802.3 1000BASE-SX+ compliant
	SFP-10K-GSF	1.0625Gbps Fiber Channel FC-PI 100-SM-LC-L compliant 1.25Gbps IEEE 802.3 1000BASE-LX compliant
	SFP-30K-GSF	1.25Gbps Gigabit Ethernet compliant
Inputs / Outputs	AC-coupled differential inputs and outputs	

Dimensions



Safety Standards:



Additional Help and Support

• For additional technical support and questions, call our Technical Support team @ 770-844-4200.

