

Table of Contents

Chapter 1: Introduction

Manual Overview	1-2
Overview of this Manual	1-2
Other Reference Materials	1-2
Who Should Read This Manual	1-2
Technical Support	1-2
Key Topics for Each Chapter	1-3
Ethernet Base Controller Overview	1-4
I/O Values Stored in Cache Memory	1-4
Industry Standard Ethernet	1-5
T1H-EBC/T1H-EBC100	1-5
RS-232C Serial Port	1-5

Chapter 2: Installation and Setup

Installing the Ethernet Base Controller	2-2
Setting the Node Address	2-3
Several Methods for Setting Node Address	2-3
Setting the Node Address Using the Rotary Switches	2-3
Setting Node Address with Software Tool	2-3
10BaseT / 100BaseT Network Cabling	2-4
10BaseT/100BaseTconnections	2-4
Serial Port (RS-232)	2-5
Maximum 10BaseT / 100BaseT Cable Length	2-5
T1H-EBC Ethernet Base Controller Specifications	2-6
T1H-EBC100 Ethernet Base Controller Specifications	2-7
LED Indicators and Hot Swapping I/O Modules	2-8
Check External 24VDC Wiring Before Hot Swapping	2-9
Hot Swap: I/O Module Replacement	2-9
Ethernet Standards	2-10

Chapter 3: Configuring the T1H-EBC(100) Using NetEdit3

NetEdit3 Software	3-2
Installing NetEdit3	3-2
Launching NetEdit3	3-3
The NetEdit3 Screen	3-3
Adding Network Protocol Support to the NetEdit3 PC	3-4

Using NetEdit3	3-5
Ethernet Communication Protocol	3-5
Ethernet Address	3-6
Module Type, IP Address and ID	3-6
Module Info>General Information	3-7
Module Info>Ethernet Stats	3-7
EBC Settings	3-7
EBCSettings>Configuration>General	3-8
IP Address	3-8
EBC Settings>Configuration>Serial Port	3-8
EBC Settings>Utils>Show Base Contents	3-10
EBC Settings>Firmware	3-10
FileMenu>Live Update	3-11
F / B / C Columns	3-11
Locating the MAC Address Label	3-12
MAC Address	3-12

Chapter 4: MODBUS[®] TCP/IP for T1H-EBC100

MODBUS TCP/IP	4-2
Client / Server Model	4-2
Protocol Description	4-2
Supported MODBUS Function Codes	4-4
MODBUS 584/984 Addressing	4-5
MODBUS 584/984 Addressing for Function Code 3 Clients	4-6
T1H-EBC100 System Memory	4-7
Current / Last State Error Codes	4-10
Extended Error Codes	4-10
Analog Input Module Configuration	4-11
Analog Output Module Configuration	4-11

Chapter 5: T1H-EBC100 DHCP & HTML Configuration

T1H-EBC100 DHCP	5-2
Disabling DHCP and Assigning a Static IP Address	5-2
Using HTML Configuration	5-3
Connecting to the T1H-EBC100	5-3

Appendix A: Using the T1H-EBC(100) with Think & DO

Mapping T1H-EBC(100) I/O Points	A-2
Launching Connectivity Center Tool	A-2
Connecting to the EBC	A-2
Mapping I/O Points to Data Items	A-2
Hot Swap Setup	A-3
Hot Swap: Automatic Mode	A-3
Hot Swap: Manual Mode Reset	A-3
Analog I/O Module Configuration	A-4
I/O Module Status Word / Bits	A-4
Using EZTouch/EZText Panel with the RJ-12 Serial Port	A-5
Adding Operator Interface Device	A-5
Using Monitor I/O to Verify Panel Operation	A-6

Appendix B: Using the T1H-EBC(100) with KEPDirect OPC Server

Introduction to KEPDirect	B-2
Introduction to OPC	B-2
DDE Support	B-2
KEPDirect	B-2
KEPDirect Project: Adding and Configuring a Channel	B-4
Running the Server	B-4
Adding a Channel	B-4
Selecting the Device Driver	B-5
Selecting the Network Adapter	B-5
Setting the Server Writes Optimizations	B-6
Saving the New Channel Settings	B-7
Using Multiple Channels in a Project	B-7
KEPDirect Project: Adding and Configuring a Device	B-8
Adding a Device	B-8
Selecting the Device Model	B-8
Setting the Device Timeout Properties	B-9
Automatic OPC Tag Database Generation	B-10
Saving the New Device Settings	B-10
KEPDirect Project: Adding Tags to the Project	B-11
User Defined Tags	B-11
Creating a User Define Tag	B-13
T1H-EBC(100) I/O Addressing	B-14
T1H-EBC(100) I/O Addressing Example	B-14
Analog Output Module Configuration	B-15

Appendix C: Using the KEPDirect OPC Quick Client

Creating a KEPDirect Quick Client Project	C-2
Connecting the Client to the OPC Server	C-2
Creating a Client Group	C-2
Selecting a Group Item	C-3
Item Operations	C-4
Using the RJ12 Serial Port in ASCII Mode	C-5
