


TABLE A

PART NO	LENGTH
ZL-D2-CBL10	0.5m [1.6 ft]
ZL-D2-CBL10-1	1.0m [3.3 ft]
ZL-D2-CBL10-2	2.0m [6.6 ft]



PIN-OUT DIAGRAM

P1		P2	P1		P2
1	BLACK	1	7	ORANGE/WHITE	16
	RED	3		GREEN/WHITE	17
2	ORANGE	4	8	VIOLET/WHITE	18
	GREEN	5		GRAY/BLACK	20
3	VIOLET	6	9	GREEN/BLACK	21
	YELLOW	7		WHITE	22
4	LIGHT GREEN	8	10	RED/BLACK	23
	LIGHT BLUE	10		ORANGE BLACK	24
5	PINK	11 CUT AND INSULATE		BROWN	2
	BLUE	12 CUT AND INSULATE		GRAY	8
6	BROWN/WHITE	14 CUT AND INSULATE		BLACK/WHITE	13
	RED/WHITE	15 CUT AND INSULATE		YELLOW/BLACK	19

NOTES:

- CABLE - 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
- CURRENT - 2A per conductor, 20A maximum cable current
- VOLTAGE -  
240V AC/DC rated operating voltage  
265V AC/DC maximum voltage
- OPERATING TEMPERATURE - 0-60°C (32-140°F)
- P1 CONNECTOR - 10 position terminal block for DL205 PLC, AutomationDirect part # D2-8IOCON
- P2 CONNECTOR - 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025-2400
- MINIMUM BEND RADIUS - 65.6 mm [2.58 in]

ZL-D2-CBL10-n	
Rev: original	Date: 07/2009
Units: mm [inches]	
Scale: .03940	
ZIPLINK DL205 Cable	