

# 78 Series Electromechanical Relay Selection Guide



Specification	781 Series	782 Series	783 Series	784 Series
<b>Coil Voltages</b>	110/120VAC, 220VAC, 12VAC, 12VDC, 24VAC, 24VDC	110/120VAC, 220VAC, 12VAC, 12VDC, 24VAC, 24VDC	110/120VAC, 220VAC, 12VAC, 12VDC, 24VAC, 24VDC	110/120VAC, 220VAC, 12VAC, 12VDC, 24VAC, 24VDC
<b>Configuration</b>	SPDT	DPDT	3PDT	4PDT
<b>Contact Rating</b>	12 to 15A	12 to 15A	12 to 15A	12 to 15A
<b>Base Socket</b>	5 pin spade terminal	8 pin spade terminal	11 pin spade terminal	14 pin spade terminal
<b>Agency Approvals</b>	UL Recognized (E191059), CE, IEC Std 947-4-1 and 947-5-1, CSA 244610	UL Recognized (E191059), CE, IEC Std 947-4-1 and 947-5-1, CSA 244610	UL Recognized (E191059), CE, IEC Std 947-4-1 and 947-5-1, CSA 244610	UL Recognized (E191059), CE, CSA 244610
<b>Prices starting at</b>	<--->	<--->	<--->	<--->



These ice cube style relays are power relays designed for applications demanding high power control in various factory machines and control panels. They are ideal for electrical control panels requiring stable and reliable relays.

## Features

- Small package design
- Silver Cadmium Oxide gold flashed contact
- High open contact dielectric strength (up to 2500V rms)
- High reliability and long life
- High vibration and shock resistance
- LED indicator on all models, so you can easily see if the relay is working properly without using a voltmeter
- Flag indicator shows relay status in manual or powered condition
- A pushbutton allows manual operation of the relay without the need for power to the coil
- Lock-Down door, when activated, holds pushbutton and contacts in the "operate" position, allowing circuits to be analyzed. **This feature is not available on 781 series.**
- SPDT, DPDT, 3PDT and 4PDT models
- Finger grip cover allows easier removal of relays from sockets than conventional relays
- I.D. tag/write labels for identifying relays in multi-relay circuits

## 78 Series Relays Selection Guide

**NOTE: Not recommended for low current switching. Find contacts' Minimum Switching Requirement on following page. For low current switching, please see the QM4N1 and QM4X1 series.**

Part Number	Price	Coil Voltage	Configuration	Dimensions	Relay Socket Part Number	Price	Dimensions
<b>781-1C-12D</b>	<--->	12VDC	SPDT	Figure 1	<b>781-1C-SKT</b>	<--->	Figure 5
<b>781-1C-12A</b>	<--->	12VAC					
<b>781-1C-24D</b>	<--->	24VDC					
<b>781-1C-24A</b>	<--->	24VAC					
<b>781-1C-120A</b>	<--->	120VAC					
<b>781-1C-240A</b>	<--->	240VAC	DPDT	Figure 2	<b>782-2C-SKT</b>	<--->	Figure 6
<b>782-2C-12D</b>	<--->	12VDC					
<b>782-2C-12A</b>	<--->	12VAC					
<b>782-2C-24D</b>	<--->	24VDC					
<b>782-2C-24A</b>	<--->	24VAC					
<b>782-2C-120A</b>	<--->	120VAC	3PDT	Figure 3	<b>783-3C-SKT</b>	<--->	Figure 7
<b>782-2C-240A</b>	<--->	240VAC					
<b>783-3C-12D</b>	<--->	12VDC					
<b>783-3C-12A</b>	<--->	12VAC					
<b>783-3C-24D</b>	<--->	24VDC					
<b>783-3C-24A</b>	<--->	24VAC	4PDT	Figure 4	<b>784-4C-SKT-1</b>	<--->	Figure 8
<b>783-3C-120A</b>	<--->	120VAC					
<b>783-3C-240A</b>	<--->	240VAC					
<b>784-4C-12D</b>	<--->	12VDC					
<b>784-4C-12A</b>	<--->	12VAC					
<b>784-4C-24D</b>	<--->	24VDC					
<b>784-4C-24A</b>	<--->	24VAC					
<b>784-4C-120A</b>	<--->	120VAC					
<b>784-4C-240A</b>	<--->	240VAC					

# 78 Series Electromechanical Relay Specifications

78 Series Relay Specification Table												
Part Numbers	781-1C-12D	781-1C-12A	781-1C-24D	781-1C-24A	781-1C-120A	781-1C-240A	782-2C-12D	782-2C-12A	782-2C-24D	782-2C-24A	782-2C-120A	782-2C-240A
<b>General Specifications</b>												
<b>*Service Life: Mechanical / Electrical Operations</b>	Mechanical: 10,000,000 operations unpowered Electrical: 100,000 operations @ rated resistive load											
<b>Operating Temperature</b>	-40°C to 55°C (-40°F to 131°F)											
<b>Response Time</b>	20 ms											
<b>Ambient Humidity</b>	45% RH to 85% RH											
<b>Vibration Resistance</b>	3 G's, 10 to 55Hz (0.6mm double amplitude)											
<b>Shock Resistance</b>	10 G's											
<b>Weight</b>	29 g (1.02 oz)						36 g (1.27 oz)					
<b>**Agency Approvals and Standards</b>	UL Recognized File E191059, CE, CSA											
<b>Environmental Protection</b>	IEC IP40											
<b>NEMA B300 Pilot Duty Rated</b>	Yes											
<b>Coil Specifications</b>												
<b>Standard</b>	LED Indicator											
<b>Coil Input Voltage</b>	12VDC	12VAC	24VDC	24VAC	120VAC	240VAC	12VDC	12VAC	24VDC	24VAC	120VAC	240VAC
<b>Coil Resistance</b>	188Ω	46Ω	750Ω	180Ω	4.43kΩ	15.72kΩ	160Ω	46Ω	650Ω	180Ω	4.43kΩ	15.7kΩ
<b>Power Consumption</b>	0.7W DC, 0.9VA @ 60Hz AC @ 25°C						0.9W DC, 1.2VA @ 60Hz AC @ 25°C					
<b>Dropout Voltage (% of nominal voltage or more)</b>	10%	15%	Min. 10%	Min. 15%			10%	15%	Min. 10%	Min. 15%		
<b>Pull-in Voltage (% of nominal voltage or less)</b>	80%	85%	80%	85%			80%	85%	80%	85%		
<b>Max. Voltage (Max. continuous voltage)</b>	110% of the rated coil voltage											
<b>Contact Specifications</b>												
<b>Contact Type</b>	SPDT						DPDT					
<b>Contact Material</b>	Silver cadmium oxide, gold flashed											
<b>Minimum Switching Requirement</b>	100mA @ 5VDC											
<b>Max. Contact Rating</b>	Refer to Contact Ratings charts.											
<b>Dielectric Strength Between Contacts</b>	1500V rms											

\*Note: These devices are rated for 1,000 cycles when used in a motor application. (Per Table 45.1, UL 508).

\*\*Note: UL listed when used with sockets 781-1C-SKT, 782-2C-SKT, 783-3C-SKT, 784-4C-SKT, or 784-4C-SKT-1. Current limited to rating of relay or socket, whichever is less.

NEMA Mechanical Switching Ratings and Test Values for AC Control Circuit Contacts											
Contact Rating Designation	Thermal Continuous Test Current (A)	Maximum AC Current, 50/60Hz (A)								Voltamperes	
		120 Volts		240 Volts		480 Volts		600 Volts			
		Make	Break	Make	Break	Make	Break	Make	Break	Make	Break
<b>B300</b>	5	30	3.00	15	1.50	---	---	---	---	3600	360

This chart is provided as a guideline only, and the ratings and values are not guaranteed to be accurate. It is the users' responsibility to properly size their control circuit devices. The chart values are from NEMA Standard ICS 5-2000, Table 1-4-1.

781 Series Contact Ratings (current)				
Resistive				*Motor Load
Voltage	Nominal	UL	CSA	UL
28VDC	12A	12A	12A	---
120VAC	15A	15A	15A	1/2Hp
277VAC	12A	12A	12A	1Hp

782 Series Contact Ratings (current)				
Resistive				*Motor Load
Voltage	Nominal	UL	CSA	UL
28VDC	12A	12A	12A	---
120VAC	15A	15A	15A	1/2Hp
277VAC	12A	12A	12A	1Hp



# 78 Series Electromechanical Relay Specifications

Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/ Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/ Lights

Process

Relays/ Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics

Safety

Appendix

Product Index

Part # Index

78 Series Relay Specification Table														
Part Numbers	783-3C-12D	783-3C-12A	783-3C-24D	783-3C-24A	783-3C-120A	783-3C-240A	784-4C-12D	784-4C-12A	784-4C-24A	784-4C-24A	784-4C-120A	784-4C-240A		
<b>General Specifications</b>														
<b>*Service Life: Mechanical / Electrical Operations</b>	Mechanical: 10,000,000 operations unpowered 200,000 operations @ rated resistive load													
<b>Operating Temperature</b>	-40°C to 55°C (-40°F to 131°F)													
<b>Response Time</b>	20 ms													
<b>Ambient Humidity</b>	45% RH to 85% RH													
<b>Vibration Resistance</b>	3 Gs, 10 to 55Hz (0.6mm double amplitude)													
<b>Shock Resistance</b>	10 Gs													
<b>Weight</b>	60 g. (2.12 oz.)						80 g (2.82 oz)							
<b>**Agency Approvals and Standards</b>	UL Recognized File E191059, CE, CSA													
<b>Environmental Protection</b>	IEC IP40													
<b>NEMA B300 Pilot Duty Rated</b>	Yes													
<b>Coil Specifications</b>														
<b>Standard</b>	LED Indicator													
<b>Coil Input Voltage</b>	12VDC	12VAC	24VDC	24VAC	120VAC	240VAC	12VDC	12VAC	24VDC	24VAC	120VAC	240VAC		
<b>Coil Resistance</b>	100 Ω	25.3Ω	400Ω	103Ω	2.77kΩ	12.1kΩ	96 Ω	21.2Ω	388Ω	84.5Ω	2.22kΩ	9.12kΩ		
<b>Power Consumption</b>	1.4W DC, 1.5VA @ 60Hz AC @ 25°C						1.5W DC, 1.5VA @ 60Hz AC @ 25°C							
<b>Dropout Voltage (% of nominal voltage or more)</b>	10%	15%	10%	15%			10%	15%	Min. 10%	Min. 15%				
<b>Pull-in Voltage (% of nominal voltage or less)</b>	80%	85%	80%	85%			80%	85%	80%	85%				
<b>Max. Voltage (Max. continuous voltage)</b>	110% of the rated coil voltage													
<b>Contact Specifications</b>														
<b>Contact Type</b>	3PDT						4PDT							
<b>Contact Material</b>	Silver cadmium oxide, gold flashed													
<b>Minimum Switching Requirement</b>	100mA @ 5VDC													
<b>Max. Contact Rating</b>	Refer to Contact Ratings charts.													
<b>Dielectric Strength Between Contacts</b>	1500 V rms						2500V rms							

\*Note: These devices are rated for 1,000 cycles when used in a motor application. (Per Table 45.1, UL 508).

\*\*Note: UL listed when used with sockets 781-1C-SKT, 782-2C-SKT, 783-3C-SKT, 784-4C-SKT, or 784-4C-SKT-1. Current limited to rating of relay or socket, whichever is less.

783 Series Contact Ratings (current)				
Resistive				*Motor Load
Voltage	Nominal	UL	CSA	UL
28VDC	12A	12A	12A	---
120VAC	15A	15A	15A	1/2Hp
277VAC	12A	12A	12A	3/4Hp

784 Series Contact Ratings (current)				
Resistive				*Motor Load
Voltage	Nominal	UL	CSA	UL
28VDC	12A	12A	12A	---
120VAC	15A	15A	15A	1/2Hp
277VAC	12A	12A	12A	3/4Hp

\*Note: These devices are rated for 1,000 cycles when applied to a motor application. (Per Table 46.1` UL 508)