


D2-260 Key Features



D2-260: Our most powerful DL205 CPU

Our D2-260 CPU provides all the capabilities of the other DL205 CPUs (as well as our D4-450 CPU), plus several additional features rarely found in a PLC of this size. With such an incredible array of features, you may be able to replace PLCs costing hundreds (or thousands) more.

Release 4.0 or higher of *DirectSOFT* is required to program the D2-260. If you're using a handheld programmer, version 2.10 of the handheld programmer firmware is required. Here are a few key features about the D2-260 CPU:

Local expansion I/O

The D2-260 supports local expansion up to five total bases (one CPU base and four expansion bases). Expansion bases are commonly used when there are not enough slots available in the CPU base, when the base power budget will be exceeded, or when placing an I/O base at a location away from the CPU base (but within the expansion cable limits). All local and expansion I/O points are updated on every CPU scan. Each local expansion base requires the D2-CM module in the CPU slot. The local CPU base requires the D2-EM Expansion Module, as well as each expansion base. For more information on local expansion, refer to the Expansion Modules pages later in this section.

Powerful built-in CPU communications

The D2-260 offers two communications ports that provide a vast array of communication possibilities. The top RJ-12 RS-232 port can be used for connection to a *C-more* or DV-1000 operator interface panel, or as a single K-sequence or *DirectNET* slave. The 15-pin bottom port (port 2) supports RS-232 or RS-422/RS485. This port offers several different protocol options such as:

- K-sequence
- *DirectNET* Master/Slave
- Modbus RTU Master/Slave
- ASCII In/Out Communications


Port 2 can also serve as a remote I/O master. The D2-260 supports the Ethernet Communication module and Data Communication Module for additional communications ports.

16 PID loops with auto-tuning

The D2-260 CPU can process up to 16 PID loops directly in the CPU. You can select from various control modes including automatic, manual, and cascade. There are also a wide variety of alarms including Process Variable, Rate of Change, and Deviation. The loop operation parameters (Process Variable, Setpoint, Setpoint Limits, etc.) are stored in V-memory, which allows easy access from operator interfaces or HMIs. Setup is accomplished with easy-to-use setup menus and monitoring views in *DirectSOFT* programming.

The auto-tuning feature is easy to use and can reduce setup and maintenance time. Basically, the CPU uses the auto-tuning feature to automatically determine near optimum loop settings. See the D2-250-1 CPU section for a PID loop control block diagram.

D2-260 local expansion system



- The D2-260 offers:
- Up to four expansion bases
 - Up to 1,024 inputs and 1,024 outputs
 - Up to 30m (98 ft) total expansion system cable

D2-260 Key Features

Full array of instructions

The right instruction can greatly simplify your programming task and can save hours of programming time.

The D2-260 supports over 280 powerful instructions, such as:

- Four types of drum sequencers
- Leading / trailing edge triggered one-shots
- Bit-of-word manipulation
- Floating point conversions
- Trigonometric functions
- Table instructions
- ASCII IN/OUT instructions



For a complete list of instructions supported by all DL205 CPUs, see the end of this section.

Modbus RTU instructions

The D2-260 CPU supports easy-to-use Modbus Read/Write instructions that expand our existing Modbus network instruction capabilities. The MRX or MWX instructions allow you to enter native Modbus addressing in your ladder program with no need to perform octal-to-decimal conversion. We added Function codes 05, 06 and the ability to read Slave Exception Codes. These flexible instructions allow the user to select the following parameters within one instruction window:

- 584/984 or 484 Modbus data type
- Slave node (0-247)
- Function code
- Modbus starting master / slave memory address
- Number of bits
- Exception code starting address

Examples of MRX and MWX instructions in DirectSOFT



ZIPLink communications adapter modules

ZIPLink cables and communications adapter modules offer fast and convenient screw terminal connection for the bottom port of the D2-260 CPU. The adapter modules are RS232/422/485 compatible and are offered with or without indicating LEDs and surge protection. See the Terminal Blocks and Wiring Solutions section in this catalog for more information.



ZL-CMA15L shown

CPU Status Indicators		
RUN	ON	CPU is in RUN mode
	OFF	CPU is in PROGRAM mode
BATT	ON	Battery backup voltage is low
	OFF	Battery backup voltage is OK or disabled
CPU	ON	CPU internal diagnostics detects error
	OFF	CPU is OK
PWR	ON	CPU power good
	OFF	CPU power failure
Mode Switch		
RUN		Puts CPU into RUN mode
TERM		Allows peripherals (HPP, DirectSOFT) to select the mode of operation
STOP		Forces CPU out of RUN mode
Port 1		
Protocols		K-sequence slave, DirectNET™ slave, Modbus RTU slave
Devices		Can connect w/HPP, DirectSOFT, C-more, DV-1000, O/I panels, or any DirectNET master
Specs.		6P6C phone jack connector RS-232 9,600 baud Fixed address Odd parity only 8 data bits one start, one stop asynchronous, half-duplex, DTE
Port 2		
Protocols		K-sequence slave, DirectNET Master/Slave, Modbus RTU Master/Slave, ASCII IN/OUT, Remote I/O Master
Devices		Can connect w/many devices, such as PCs running DirectSOFT, DSData, HMI packages, C-more, DV-1000, other O/I panels, any DirectNET or Modbus RTU master or slave, or ASCII devices
Specs.		HD15 connector RS-232, RS-422/485* 300/600/1200/2400/4800 9600/19.2K/38.4K baud Odd, even, or no parity Selectable address (1-90, HEX 1 - 5A) 8 data bits, one start, one stop Asynchronous, Half-duplex, DTE
Battery (Optional)		
D2-BAT-1		Coin type, 3.0V Lithium battery, 560mA, battery number CR2354

*Note: Batteries are not needed for program backup. However, you should order a battery if you have parameters in V-memory that must be maintained in case of a power outage.
RS485 for Modbus protocol only

On-board memory

The D2-260 has 15.5K words of flash memory on board for your program plus 14.2K words of data registers. With flash memory, you don't have to worry about losing the program due to a bad battery.

Built-in remote I/O connection

The bottom port on the D2-260 can be used as a master for serial remote I/O networks (see the D2-RSSS later in this section for details).

D2-260 Key Features

ASCII communications instructions

The D2-260 CPU supports several easy-to-use instructions that allow ASCII strings to be read into and written from the PLC communications ports.

Raw ASCII: Port 2 can be used for either reading or writing raw ASCII strings, but not for both.

Embedded ASCII characters: The D2-260 can decipher ASCII embedded within a supported protocol (K-Sequence, *DirectNet*, Modbus, Ethernet) via the CPU ports, H2-ECOM or D2-DCM.


Here's how the D2-260 can receive ASCII input strings:

1. **ASCII IN (AIN)** - This instruction configures port 2 for raw ASCII input strings with parameters such as fixed and variable length ASCII strings, termination characters, byte swapping options, and instruction control bits. Use barcode scanners, weight scales, etc. to write raw ASCII input strings into port 2 based on the (AIN) instruction's parameters.
2. Write embedded ASCII strings directly to V-memory from an external HMI or similar master device via a supported communications protocol using the CPU ports, H2-ECOM or D2-DCM. The AIN instruction is not used in this case.
3. If a D2-260 PLC is a master on a network, the Network Read instruction (RX) can be used to read embedded ASCII data from a slave device via a supported communications protocol using port 2, H2-ECOM or D2-DCM. The RX instruction places the data directly into V-memory.

Here's how the D2-260 can write ASCII output strings:

1. **Print from V-memory (PRINTV)** - Use this instruction to write raw ASCII strings out of port 2 to a display panel or a serial printer, etc. The instruction features the starting V-memory address, string length, byte swapping options, etc. When the instruction's permissive bit is enabled, the string is written to port 2.
2. **Print to V-memory (VPRINT)** - Use this instruction to create pre-coded ASCII strings in the PLC (i.e. alarm messages). When the instruction's permissive bit is enabled, the message is loaded into a pre-defined V-memory address location. Then the (PRINTV) instruction may be used to write the pre-coded ASCII string out of port 2. American, European and Asian Time/Date stamps are supported.
3. **Print Message (PRINT)** - This existing instruction can be used to create pre-coded ASCII strings in the PLC. When the instruction's permissive bit is enabled, the string is written to port 2. The VPRINT/PRINTV instruction combination is more powerful and flexible than the PRINT instruction.
4. If a D2-260 PLC is a master on a network, the Network Write instruction (WX) can be used to write embedded ASCII data to an HMI or slave device directly from V-memory via a supported communications protocol using port 2, H2-ECOM or D2-DCM.

Example AIN instruction in DirectSOFT



Additional instructions that help manage the ASCII strings

The following instructions can be very helpful in managing the ASCII strings within the CPU's V-memory:


ASCII Find (AFIND) - Finds where a specific portion of the ASCII string is located in continuous V-memory addresses. Forward and reverse searches are supported.

ASCII Extract (AEX) - Extracts a specific portion (usually some data value) from the ASCII find location or other known ASCII data location.

Compare V-memory (CMPV) - This instruction is used to compare two blocks of V-memory addresses and is usually used to detect a change in an ASCII string. Compared data types must be of the same format (i.e. BCD, ASCII, etc.).

Swap Bytes (SWAPB) - Usually used to swap V-memory bytes on ASCII data that was written directly to V-memory from an external HMI or similar master device via a communications protocol. The AIN and AEX instructions have a built-in byte swap feature.

Example of VPRINT instruction in DirectSOFT





Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/ Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/ Lights

Process

Relays/ Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics

Safety

Appendix

Product Index

Part # Index

DL205 CPU Specifications

DL205 CPU Comparison				
System Capacity	D2-230	D2-240	D2-250-1	D2-260
Total memory available (words)	2.4K	3.8K	14.8K	30.4
Ladder memory (words)	2048 EEPROM	2560 EEPROM	7680 Flash	15872 Flash
V-memory (words)	256	1024	7168	14592
Battery backup	Yes	Yes	Yes	Yes
Total CPU memory I/O pts. available (<i>actual I/O pts. depend on I/O configuration method selected</i>)	256	896 (320 X + 320 Y + 256 CR)	2048 (512 X + 512 Y + 1024 CR)	8192 (1024 X + 1024 Y + 2048 CR + 2048 GX + 2048 GY)
Local I/O (pts.)	256	256	256	256
Local Expansion I/O (pts.)	none	none	768 (2 exp. bases max) (Including local I/O)	1280 (4 exp. bases max.) (Including local I/O)
Serial Remote I/O (pts.)	N/A	896 max. (Including local I/O)	2048 max. (Including local and exp. I/O)	8192 max. (Including local & exp. I/O)
Remote I/O channels	N/A	2	8 (7+1 CPU port)	8 (7+1 CPU port)
I/O per remote channel	N/A	2048 (limited to 896)	2048	2048
Ethernet Remote I/O	N/A	Yes	Yes	Yes
Discrete I/O pts.	N/A	896 max. (Including local I/O)	2048 max. (Including local and exp. I/O)	8192 (Including local and exp. I/O)
Analog I/O channels	N/A	Map into V-memory	Map into V-memory	Map into V-memory
Remote I/O channels	N/A	Limited by power budget	Limited by power budget	Limited by power budget
I/O per remote channel	N/A	16,384 (limited to 896)	16,384 (16 fully expanded H4-EBC slaves using V-memory and bit-of-word instructions)	16,384 (16 fully expanded H4-EBC slaves using V-memory and bit-of-word instructions)
Performance				
Contact execution (Boolean)	3.3µs	1.4µs	0.61µs	0.61µs
Typical scan (1K Boolean)	4-6ms	10-12ms	1.9ms	1.9ms
Programming and Diagnostics				
RLL Ladder Style	Yes	Yes	Yes	Yes
RLL ^{PLUS} /Flowchart Style (Stages)	Yes/256	Yes/512	Yes/1024	Yes/1024
Run time editing	Yes	Yes	Yes	Yes
Supports Overrides	No	Yes	Yes	Yes
Variable/fixed scan	Variable	Variable	Variable	Variable
Instructions	113	129	174	231
Control relays	256	256	1024	2048
Timers	64	128	256	256
Counters	64	128	128	256
Immediate I/O	Yes	Yes	Yes	Yes
Subroutines	No	Yes	Yes	Yes
For/Next loops	No	Yes	Yes	Yes
Timed Interrupt	No	Yes	Yes	Yes
Integer Math	Yes	Yes	Yes	Yes
Floating-point Math	No	No	Yes	Yes
Trigonometric functions	No	No	No	Yes
Table Instructions	No	No	No	Yes
PID	No	No	Yes, 4 loops	Yes, 16 loops
Drum Sequencers	No	No	Yes	Yes
Bit of Word	No	No	Yes	Yes
ASCII Print	No	No	Yes	Yes
Real-time clock/calender	No	Yes	Yes	Yes
Internal diagnostics	Yes	Yes	Yes	Yes
Password security	Yes	Multi-level	Multi-level	Multi-level
System and user error log	No	No	Yes	Yes
Communications				
Built-in ports	Port 1 RS-232	Port 1 RS-232 and Port 2 RS-232	Port 1 RS-232 and Port 2 RS-232/422	Port 1 RS-232 and Port 2 RS-232/422/485)
K-sequence (proprietary protocol)	Yes	Yes	Yes	Yes
DirectNET™	No	Yes	Yes	Yes
Modbus RTU master/slave	No	No	Yes	Yes
ASCII communications	No	No	OUT	IN/OUT
Maximum baud rate	9600	19.2K port 2	38.4K port 2	38.4K port 2