

# Wiring Accessories – Crimping Tools

## Crimping Tools Overview

Our high-quality industrial crimping tools are designed to crimp a wide range of insulated and non-insulated crimping terminals, ferrules, and connectors. They feature ergonomic handles and

controlled-cycle ratcheting mechanisms to guarantee a uniform crimp every time. Choose from fixed or interchangeable die tools, or tool/die sets with multiple dies.

Fixed-Die Crimping Tools				
Part #	Description	Fig.	Pcs/Pkg	Price/Pkg
<b>BM-537</b>	Ferrule crimping tool: 22 to 12 AWG for ferrules 0.5-4 mm <sup>2</sup>	1	1	<--->
<b>BM-539</b>	Ferrule crimping tool: 10 to 6 AWG for ferrules 6-16 mm <sup>2</sup>	2	1	<--->
<b>BM-533</b>	Ferrule crimping tool: 8 to 2 AWG for ferrules 10-35 mm <sup>2</sup>	3	1	<--->
<b>BM-534</b>	Connector crimping tool: 22 to 10 AWG, for ring, spade, and disconnect terminals	4	1	<--->
<b>BM-5345</b>	Crimping tool & Die set; includes crimping tool, case, and 5 die sets. (BM-537, BM-539, BM-535, BM-534 and BM-531 (Fig. 5) See below for descriptions.	N/A	1	<--->



**BM-53x Crimping Tool**




**BM-5345 Crimping tool and die set**




**Fig. 1 (BM-537)**  
End Sleeve Terminals 22-12 AWG (0.5-4 mm<sup>2</sup>)




**Fig. 2 (BM-539)**  
End Sleeve Terminals 10-6 AWG (6-16mm<sup>2</sup>)



**Fig. 3 (BM-535)**  
Uninsulated Copper Terminals 20-8 AWG (0.5-10 mm<sup>2</sup>)



**Fig. 4 (BM-534)**  
Insulated Terminals 22-10 AWG (0.25-6 mm<sup>2</sup>)



**Fig. 5 (BM-531)**  
Barrel Open Terminals 20-10 AWG (0.5-6 mm<sup>2</sup>)

Interchangeable-Die Crimping Tools			
Part #	Description *	Pcs /Pkg	Price Each
<b>DN-CT-HDL</b>	Crimping tool handle for DN-CT-Dx dies (dies NOT included) Approximate dimensions: 9.75 x 2.52 x 0.95 in (234 x 64 x 24 mm); 16.2 oz (460g)	1	<--->
<b>DN-CT-D1</b>	Die set for DN-CT-HDL; 26-22 & 12-10 AWG (0.1-0.4 & 4-6 mm <sup>2</sup> ) green & yellow insulated terminals	1	<--->
<b>DN-CT-D2</b>	Die set for DN-CT-HDL; 22-14 AWG (0.5-2.5 mm <sup>2</sup> ) red & blue insulated terminals	1	<--->
<b>DN-CT-D3</b>	Die set for DN-CT-HDL; 22-10 AWG (0.5-6 mm <sup>2</sup> ) non-insulated terminals	1	<--->
<b>DN-CT-D4</b>	Die set for DN-CT-HDL; 24-8 AWG (0.25-10 mm <sup>2</sup> ) wire ferrules	1	<--->
<b>DN-CT-D5</b>	Die set for DN-CT-HDL; 6-4 AWG (16-25 mm <sup>2</sup> ) wire ferrules	1	<--->
<b>DN-CT-D6</b>	Die set for DN-CT-HDL; 2-1/0 AWG (35-50 mm <sup>2</sup> ) wire ferrules	1	<--->
<b>DN-CT-D7</b>	Die set for DN-CT-HDL; 22-10 AWG (0.5-6 mm <sup>2</sup> ) open barrel non-insulated terminals	1	<--->
<b>DN-CT-D8</b>	Die set for DN-CT-HDL; 8-pin (RJ45) modular plugs	1	<--->
<b>DN-CT-D9</b>	Die set for DN-CT-HDL; 6-pin (RJ11/RJ12) modular plugs	1	<--->
<b>DN-CT-SET</b>	Crimping tool modular system; includes handle and three die sets (DN-CT-HDL + DN-CT-D2 + DN-CT-D4 + DN-CT-D5) The die pairs are held together for easy handling, and interchange without separate tools.	1	<--->

\* The DN-CT-xx series features a crimping tool with multiple interchangeable dies separately available. The die pairs are held together for easy handling, and can be interchanged without separate tools.



**DN-CT-HDL Crimping Tool**



**DN-CT-SET Crimping Tool & Die Set**

# Wiring Accessories – Crimping Tool

## DN-CT-Dx Interchangeable Crimping Dies (for DN-CT-xxx crimping tool only)

*These dies are held together for easy handling, and can be interchanged without additional tools. All DN-CT-Dx dies have been tested on leading brands of connectors to ensure quality connections. Dies come in modular holders that can be connected together when not in use.*



DN-CT-Dx die & holder



**DN-CT-D1** (4300-3128)  
Insulated Terminals & Connectors  
26–22 AWG & 12–10 AWG  
[Green & Yellow] (0.1–0.4 & 4–6 mm<sup>2</sup>)



**DN-CT-D2** (4300-3129)  
Insulated Terminals & Connectors  
22–14 AWG  
[Red & Blue] (0.5–2.5 mm<sup>2</sup>)



**DN-CT-D3** (4300-3142)  
Non-Insulated Terminals & Connectors  
22–10 AWG (0.5–6 mm<sup>2</sup>)



**DN-CT-D4** (4300-3127)  
Wire Ferrules  
24–8 AWG (0.25–10 mm<sup>2</sup>)



**DN-CT-D5** (4300-3153)  
Wire Ferrules  
6–4 AWG (16–25 mm<sup>2</sup>)



**DN-CT-D6** (4300-3154)  
Wire Ferrules  
2–1/0 AWG (35–50 mm<sup>2</sup>)




**DN-CT-D7** (4300-3146)  
Non-Insulated Open-Barrel Terminals  
22–10 AWG (0.5–6 mm<sup>2</sup>)



**DN-CT-D8** (4300-3144)  
8-pin Modular Plugs  
RJ45



**DN-CT-D9** (4300-3132)  
6-pin Modular Plugs  
RJ11/RJ12



DN-CT-Dx Die Interchange Procedure