



# Disconnect Terminal Blocks




Both the DN-DIS10 and the DN-KBD12 allow fast circuit disconnection without rewiring. The DN-DIS10 is supplied with a copper disconnect bar installed in the fuse holder. The DN-KBD12 offers circuit disconnection capability by means of a pivoting, insulated “knife blade”.



## DN-DIS10



## DN-KBD12



## DN-ECKBD



	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg
<b>Gray Disconnect Block</b>	DN-DIS10	50	<--->	DN-KBD12	50	<--->
<b>Disconnect Terminal Blocks Specifications</b>						
<b>UL Approval*</b>	300V	30A	24-10AWG	600V	20A	22-12AWG
<b>CSA Approval</b>	300V	25A	18-12 AWG	600V	16A	18-12AWG
<b>VDE Approval</b>	500V	25A	4mm <sup>2</sup>	600V	16A	2.5mm <sup>2</sup>
<b>CE Conformity</b>	CE 23/20, CE 23/21			CE 23/20, CE 23/21		
<b>Agency File#</b>	E179129, LR84816			E179129, LR84816		
<b>Wire Strip Length</b>	0.39" (10mm)			0.39" (10mm)		
<b>Tightening Torque</b>	5.5 lb-in. (0.6Nm)			4.5 lb-in. (0.5Nm)		
<b>Density</b>	30 pcs./ft. (125/m)			60 pcs./ft. (200/m)		
<b>Disconnect Type</b>	Copper bar			Copper blade		
<b>Operating Temperature</b>	Ambient air temperature: -13°F to 104°F (-25°C to 40°C) Relative humidity: 50% max at 104°F (40°C); 90% max at 68°F (20°C)					

<b>Accessories</b>						
	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg
<b>35 mm DIN Rail</b>	Part No. DN-R35S1 (7.5 mm) or DN-R35HS1 (15 mm)				10	various
<b>End Bracket</b>					50	<--->
	DN-EB35				20	<--->
	DN-EB35MN				50	<--->
	DN-EB35-A				50	<--->
	DN-QEB35				50	<--->
<b>End Cover</b>	Included	-	-	DN-ECKBD	100	<--->
<b>Marking Tags</b>	DN-L/DN-LT series	500/100	various	DN-LA /DN-LT series	500/100	various
<b>Angled Support Bracket</b>	DN-ASB1				50	<--->
<i>*Note: For copper wire only</i>						

For more information on accessories, see the “DINnectors Accessories” section of this chapter.