


DINnectors Accessories

Terminal Plugs



DN-xxPLUG




Accessories – Terminal Plugs				
Plugs* Part Number	Number of Poles	Length	Pcs/Pkg	Price/Pkg
DN-2PLUG	2	L = 0.40 in [10.2 mm]	200	<--->
DN-3PLUG	3	L = 0.60 in [15.2 mm]	200	<--->
DN-4PLUG	4	L = 0.80 in [20.3 mm]	100	<--->
DN-5PLUG	5	L = 1.00 in [25.4 mm]	100	<--->
DN-6PLUG	6	L = 1.20 in [30.5 mm]	100	<--->
DN-7PLUG	7	L = 1.40 in [35.6 mm]	50	<--->
DN-8PLUG	8	L = 1.60 in [40.6 mm]	50	<--->
DN-9PLUG	9	L = 1.80 in [45.7 mm]	50	<--->
DN-10PLUG	10	L = 2.00 in [50.8 mm]	50	<--->
DN-11PLUG	11	L = 2.20 in [55.9 mm]	50	<--->
DN-12PLUG	12	L = 2.40 in [61.0 mm]	50	<--->

Terminal Plugs Ratings	
Voltage/Current	300V, 12A
Wire Gauge	14–22 AWG, CU only
Torque	Tightening Torque: 4.5 lb-in [0.51 Nm]
Operating Temperature	Operating Temperature: -13°F to 104°F (-25°C to 40°C) Relative humidity: 50% max at 104°F (40°C); 90% max at 68°F (20°C)
Agency Approvals	UL file #: E179129

* DN-xxPLUGs fit all DN-EMxx & DN-QEMxx plug-in terminal blocks

Disconnect blade



DN-DIS-BLADE


Disconnect Blade			
Part Number	Description	Pcs/Pkg	Price
DN-DIS-BLADE	Use instead of DN-SUPP-x for DN-FE or as replacement for DN-DIS.	50	<--->

Note: Dimensions are in mm [inches]

End Brackets



End Brackets			
Part Number	Description	Pcs/Pkg	Price/Pkg
DN-EB15	Terminal block end stop 7mm width screw clamping. Gray	100	<--->
DN-EB15MN		20	<--->
DN-EB35	Terminal block end stop 9mm width screw clamping. Gray	50	<--->
DN-EB35MN		20	<--->
DN-EB35-A	Terminal block end stop 6mm width screw clamping. Black	50	<--->
DN-EB35-A-10		10	<--->
DN-QEB35	Terminal block end stop 6mm width screwless clamping. Black	50	<--->
DN-QEB35-10		10	<--->



For more information on accessories, see the "DINnectors Accessories" section of this chapter.

DINnectors Accessories

End Covers

Certain end covers can be used with multiple terminal block parts to cover and insulate the open side, or to put more space between adjacent blocks.

DINnector End Covers				
Part Number	Description	Works with terminal block series	Pcs/Pkg	Price
DN-EC1210	Covers open side of DN-T12-A and DN-T10-A series terminal blocks	DN-T10-A, DN-T12-A	100	<-->
DN-EC1210MN			25	<-->
DN-EC86	Covers open side of DN-T8 and DN-T6 series terminal blocks	DN-T8, DN-T6	100	<-->
DN-EC86MN			25	<-->
DN-EC4	Covers open side of DN-T4 series terminal blocks	DN-T4	50	<-->
DN-EC1/0	Covers open side of DN-T1/0 series terminal blocks	DN-T1/0	50	<-->
DN-DEC10	Covers open side of DN-D10 series double-level terminal blocks	DN-D10	100	<-->
DN-EC14	Covers open side of DN-TL14-A series terminal blocks	DN-TL14-A	25	<-->
DN-EC14S	Covers open side of DN-TL14S-A series terminal blocks	DN-TL14S-A	25	<-->
DN-ECM10	Covers open side of DN-M10-A series terminal blocks	DN-M10-A DN-M10B-A	100	<-->
DN-ECM10MN			25	<-->
DN-ECKBD	Covers open side of DN-KBD12 series disconnect blocks	DN-KBD12	100	<-->
DN-EMXM1EC1	Covers open side of DN-EMXM1 and DN-QEMXM1 terminal blocks	DN-EMXM1	25	<-->
DN-EMXM1EC2	Covers closed side of DN-EMXM1 and DN-QEMXM1 terminal blocks	DN-QEMXM1	25	<-->
DN-EMXDVEC1	Covers open side of DN-EMXDV and DN-QEMXDV terminal blocks	DN-EMXDV	25	<-->
DN-EMXDVEC2	Covers closed side of DN-EMXDV and DN-QEMXDV terminal blocks	DN-QEMXDV	25	<-->
DN-FESEP	Covers closed side of DN-FE sockets and DN-DIS disconnects	DN-FE, DN-DIS	50	<-->
DN-FESEP-10			10	<-->
DN-QEC12	Covers open side of DN-Q12-A or DN-QG12-A series screwless terminal blocks	DN-Q12-A	50	<-->
DN-QEC10	Covers open side of DN-Q10-A or DN-QG10-A series screwless terminal blocks	DN-Q10-A	50	<-->
DN-QEC8	Covers open side of DN-Q8-A or DN-QG8-A series screwless terminal blocks	DN-Q8-A	50	<-->
DN-QEC12-1-2	Covers open side of DN-Q12-1-2-A and DN-QKBD12-A series screwless terminal blocks	DN-Q12-1-2-A DN-QKBD12	25	<-->
DN-QEC12-2-2	Covers open side of DN-Q12-2-2-A series screwless terminal blocks	DN-Q12-2-2-A	25	<-->
DN-QDEC12	Covers open side of DN-QD12-A series screwless terminal blocks	DN-QD12-A	25	<-->

Spacers

Spacers are used to put more space between adjacent blocks.

DINnector Spacers				
Part Number	Description	Works with terminal block series	Pcs/Pkg	Price
DN-S1210	Spacer for DN-T12-A and DN-T10-A series terminal blocks	DN-T10-A, DN-T12-A	100	<-->
DN-S1210MN			25	<-->
DN-S86	Spacer for DN-T8 and DN-T6 series terminal blocks	DN-T8, DN-T6	100	<-->
DN-EMXM1SPA1	Spacer for single-level plug-in terminal blocks	DN-EMXM1, DN-QEMXM1	25	<-->
DN-EMXDVSPA1	Spacer for double-level plug-in terminal blocks	DN-EMXDV, DN-QEMXDV	25	<-->
DN-FESPA	Spacer for DN-FE sockets and DN-DIS disconnects	DN-FE, DN-DIS	50	<-->
DN-FESPA-10			10	<-->

DINnectors Accessories

- Company Information
- Systems Overview
- Programmable Controllers
- Field I/O
- Software
- C-more & other HMI
- Drives
- Soft Starters
- Motors & Gearbox
- Steppers/ Servos
- Motor Controls
- Proximity Sensors
- Photo Sensors
- Limit Switches
- Encoders
- Current Sensors
- Pressure Sensors
- Temperature Sensors
- Pushbuttons/ Lights
- Process
- Relays/ Timers
- Comm.
- Terminal Blocks & Wiring
- Power
- Circuit Protection
- Enclosures
- Tools
- Pneumatics
- Safety
- Appendix
- Product Index
- Part # Index

DINnector End Covers and Spacers Dimensions			
Part Number	Length	Height	Thickness
DN-EC1210	44 mm [1.73 in]	35 mm [1.38 in]	1.5 mm [0.06 in]
DN-EC1210MN			
DN-S1210	55 mm [2.17 in]	44 mm [1.73 in]	
DN-S1210MN			
DN-EC86	50 mm [1.97 in]	43 mm [1.69 in]	
DN-EC86MN			
DN-S86	55 mm [2.17 in]	49 mm [1.93 in]	
DN-EC4			
DN-EC1/0	62 mm [2.44 in]	60 mm [2.36 in]	
DN-DEC10			
DN-EC14	78 mm [3.08 in]	55 mm [2.17 in]	
DN-EC14S			
DN-ECM10	32 mm [1.26 in]	27 mm [1.06 in]	
DN-ECM10MN			
DN-ECKBD	52 mm [2.05 in]	34.5 mm [1.36 in]	
DN-EMXM1EC1	as shown		
DN-EMXM1EC2			
DN-EMXDVEC1			
DN-EMXDVEC2			
DN-EMXDVSPA1			
DN-EMXM1SPA1			
DN-FESPA			
DN-FESPA-10			
DN-FESEP			
DN-FESEP-10			
DN-QEC12	50 mm [1.97 in]	23 mm [0.9 in]	1.5 mm [0.06 in]
DN-QEC10	57.4 mm [2.26 in]	33.6 mm [1.32 in]	
DN-QEC8	63 mm [2.48 in]	38.5 mm [1.52 in]	
DN-QEC12-1-2	68.5 mm [2.70 in]	28.5 mm [1.12 in]	
DN-QEC12-2-2	87.5 mm [3.44 in]	28.5 mm [1.12 in]	
DN-QDEC12	98 mm [3.86 in]	37 mm [1.46 in]	

DN-EC1210, DN-EC1210MN DN-EC86, DN-EC86MN DN-EC4, DN-EC1/0, DN-ECKBD, DN-S1210, DN-S1210MN, DN-S86

