



Direct Mount Terminal Blocks

Direct mount terminal blocks do not require the use of a DIN rail to mount. By utilizing two mounting screws, they can be mounted to any backplane. They are supplied with or without wire protectors and can easily be cut to length with ordinary hand tools.


BM-M092CS




BM-M093CS



BM-M094CS



	Part#	Pcs/ Pkg	Price/ Pkg	Part#	Pcs/ Pkg	Price/ Pkg	Part#	Pcs/ Pkg	Price/ Pkg
12 Pole, Without Wire Protector	BM-M092	50	<-->	BM-M093	50	<-->	BM-M094	50	<-->
12 Pole, With Wire Protector	BM-M092CS	50	<-->	BM-M093CS	50	<-->	BM-M094CS	50	<-->
Direct Mount Terminal Blocks Specifications									
UL Approval, Field Wiring	600V/ 250V**	10A	20-16 AWG	600V/ 250V**	20A	18-12 AWG	600V/ 250V**	30A	18-10 AWG
UL Approval, Factory Wiring	600V/ 250V**	15A	20-16 AWG	600V/ 250V**	30A	18-12 AWG	600V/ 250V**	40A	18-10 AWG
CSA Approval	150V/ 300V**	20A	18-16 AWG	150V/ 300V**	30A	18-14 AWG	150V/ 300V**	30A	18-10 AWG
CE Conformity	CE 93/68/EEC								
Agency File #	UL E70156, CSA LR 44081-9			UL E70156, CSA LR 44081-11			UL E70156, CSA LR 44081-12		
Wire Strip Length	0.39" (10mm)			0.39" (10mm)			0.39" (10mm)		
Tightening Torque	4.4 lb-in(0.5Nm)			7 lb-in			7 lb-in		
* UL Temperature Rating: 105° ** Commercial Use									



Wire protectors are metallic strips that physically isolate the conductor from the terminal screw. The protectors prevent cutting or nicking softer conductors.