

DINnectors Accessories

Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/ Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/ Lights

Process

Relays/ Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics

Safety

Appendix

Product Index

Part # Index

DIN rail

35 mm wide

These quality DIN rails are provided in one-meter lengths and two heights, 7.5 mm and 15 mm. The 7.5 mm-high rails are primarily used to mount terminal blocks, relays, timers and small PLCs such as the DL05, DL06, DL105, DL205, CLICK, and Productivity3000.

The 15 mm-high rails are for mounting larger and heavier components such as contactors and larger PLCs.







15 mm wide

The one-meter-long type DN-R15S1 DIN rail is used exclusively for mounting mini terminal blocks such as the DN-M10-A.



	Part Number	Pcs/Pkg	Price/Pkg	Part#	Pcs/Pkg	Price/Pkg	Part Number	Pcs/Pkg	Price/Pkg
DIN Rail	DN-R35S1	10	<-->	DN-R35HS1	10	<-->	DN-R15S1	10	<-->
	DN-R35S1-2	2	<-->	DN-R35HS1-2	2	<-->	DN-R15S1-2	2	<-->
DINnectors Accessories Specifications									
Description	Steel, slotted, 3'3" (1m) length, 7.5mm high			Steel, slotted, 3'3" (1m) length, 15mm high			Steel, slotted, 3'3" (1m) length, 5.5mm high		
Plating	silver-colored plating								
International Standards	CENELEC EN 50022, DIN 46277/3, RoHS			RoHS			CENELEC EN 50045, DIN 46277/2, RoHS		
Approximate Ampacity	65 Amps			125 Amps			35 Amps		
Suggested Mounting Screw Type	M6			M6			M4		

Dimensions mm [inches]



Angled support bracket

DN-ASB1 plated steel support brackets raise and tilt mounting rails for easier wiring.

Part Number	Pcs/Pkg	Price Each
DN-ASB1	50	<-->
*Uses M6x1 metric fixing screw for mounting DIN rail to bracket; additional 5 mm unthreaded mounting hole available.		

DN-ASB1

