

Floor Stand Kit



Applications

Kits are easily installed on most wall-mounted Wiegmann enclosures. Kits can also be used to elevate Wiegmann free-standing enclosures. To install, drill holes in bottom of existing enclosure and bolt in place. Each kit includes two stands and mounting bolts and nuts.



SSFK1216

Construction

- Steel floor stand has a ANSI 61 gray polyester powder finish over phosphatized surfaces
- Stainless steel floor stand is type 304, 10 gauge stainless with a grained finish





FK0608

Steel Floor Kit	Price	Stainless Steel Floor Kit	Price	Floor Stand Height "H"	Enclosure Size "D"
FK0608	<--->	SSFK0608	<--->	6 (152)	8 (203)
FK0610	<--->	SSFK0610	<--->	6 (152)	10 (254)
FK0612	<--->	SSFK0612	<--->	6 (152)	12 (305)
FK0618	<--->	SSFK0618	<--->	6 (152)	18 (457)
FK0624	<--->	SSFK0624	<--->	6 (152)	24 (610)
FK1208	<--->	SSFK1208	<--->	12 (305)	8 (203)
FK1210	<--->	SSFK1210	<--->	12 (305)	10 (254)
FK1212	<--->	SSFK1212	<--->	12 (305)	12 (305)
FK1216	<--->	SSFK1216	<--->	12 (305)	16 (406)
FK1218	<--->	SSFK1218	<--->	12 (305)	18 (457)
FK1220	<--->	SSFK1220	<--->	12 (305)	20 (508)
FK1224	<--->	SSFK1224	<--->	12 (305)	24 (610)
FK1808	<--->	---	<--->	18 (457)	8 (203)
FK1810	<--->	---	<--->	18 (457)	10 (254)
FK1812	<--->	---	<--->	18 (457)	12 (305)
FK1816	<--->	---	<--->	18 (457)	16 (406)
FK2408	<--->	---	<--->	24 (610)	8 (203)
FK2410	<--->	SSFK2410	<--->	24 (610)	10 (254)
FK2412	<--->	SSFK2412	<--->	24 (610)	12 (305)

Note: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.

Dimensions



Enclosure Shipping Schedule		
Same day	1 - 7 days	1 -10 days

Color indicates shipping lead time in business days.