

DL05/06 CoProcessor Module

Triple-port BASIC CoProcessor F0-CP128 <--->



Overview

The BASIC CoProcessor Module interfaces the DL05/06 family of programmable controllers with bar code readers, operator interface terminals, instrumentation equipment, computers and other serial devices.

BASIC CoProcessor applications

BASIC CoProcessors are designed for use with intelligent devices such as:

- Bar code readers
- Welders
- Board level controllers
- Serial printers
- Intelligent sensors
- Almost any device with an RS-232 or RS-485 port

They are also good solutions for applications requiring complex math, such as floating point math, sine, cosine, tangent, exponential, square roots, etc.

Features

- FACTS Extended BASIC and ABM Commander for Windows software for IBM PCs makes program development fast and simple. (The software is included with the CoPro module on CD-ROM). It allows online, full-screen BASIC program editing and the ability to upload/download programs on disk. The included CD has Modbus master and slave BASIC programs and other application examples.
- Non-volatile memory of up to 128K allows multiple program storage and execution, DL05/06 register expansion, and retentive data storage and retrieval.
- 100 MHz BASIC CoProcessor provides fast program execution independent of the CPU scan.
- Three buffered ports permit communication from the module to three external devices.
- The module is programmable from port 1 or 3 for complete serial port utilization without switching cables.
- A real-time clock/calendar maintains time/date with battery backup when power outages occur.
- Programmable time based BASIC interrupts to 5 ms.

- Direct access of up to 256 bytes of DL05/06 CPU memory per scan is possible. No supporting ladder logic is required.
- Floating point math solves complex formulas to eight significant digits.
- An RJ12 Port 1 and Port 3 splitter, included with the module, provides easy connection of RS-232 cables to both Port 1 and Port 3. (If you are using RTS1 and CTS1 for port 1, then port 3 is not available.)

Included with CoPro

The following items are included with the F0-CP128 module:



- ABM Commander CD-ROM
- 7 ft. 6P6C-to-6P6C cable (phone-style RJ12 connectors)
- 9-pin D-sub connector (9-pin female to RJ12) to adapt to PC comm port
- RJ12 port splitter



DL06 PLC with multiple F0-CP128 modules

DL05/06 CoProcessor Module

PLC
Overview

DL05/06
PLC

DL105
PLC

DL205
PLC

DL305
PLC

DL405
PLC

Field I/O

Software

C-more
HMIs

Other HMI

AC Drives

Motors

Steppers/
Servos

Motor
Controls

Proximity
Sensors

Photo
Sensors

Limit
Switches

Encoders

Current
Sensors

Pushbuttons/
Lights

Process

Relays/
Timers

Comm.

TB's &
Wiring

Power

Circuit
Protection

Enclosures

Appendix

Part Index

Triple-Port BASIC CoProcessor Module Specifications	
Module Type	CoProcessor™, Intelligent
Modules per CPU	DL05: one; DL06: up to four
Communication	256 character type-ahead input buffer on all ports. Ports are independently programmed by software. Seven or eight data bits, one or two stop bits, even, odd, or no parity. XON/XOFF software flow control and RTS/CTS handshake.
Clock Speed	100MHz
User Memory	128K total (64K data, 64K program) non-volatile; Real time battery backed calendar/clock
F0-CP128 Ports	Port 1: RS-232 512K baud maximum Port 2: RS-485, 512K baud maximum Port3*: RS-232, 115.2K baud max. * Port 3 physically located in the same RJ12 jack as Port 1 (RS-232). Port 3 uses the RTS1/CTS1 pins on that jack. If you use these lines for other purposes (e.g. hardware handshaking on Port 1), then Port 3 cannot be used.
ABM Commander for Windows (CD included with module)	Standard programming/documentation software for IBM PCs is shipped with each coprocessor module Key features include: <ul style="list-style-type: none"> • Runs under Windows 98/ME/2000/XP • On-line full-screen BASIC program editing (similar to GW Basic, with industrial application enhancements added for easier programming) • Internal Editor for block copy, block move, search and replace • Text upload and download BASIC programs on disk • Binary upload and download BASIC programs and data on disk • Download control statement allows multiple programs to be downloaded and saved with one download file. • CD includes Modbus master and slave BASIC programs and other application examples
Field Termination	One RJ12 jack: Port 1 and 3 RS-232; One three-position removable terminal block: Port 2 RS-485
Indicator LEDs	RX1, TX1, RX2, TX2, RX3 (CTS1), TX3 (RTS1)
Power Consumption	150mA @ 5VDC
Operating Environment	0°C - 60°C (32°F - 140°F), 5% to 95% humidity (non-condensing)
Manufacturer	FACTS Engineering

CPU	Firmware Required	DirectSOFT Required
DL05	Version 5.00 or later	Version 3.0c or later
DL06	Version 1.90 or later	Version 4.0, Build 16 or later