

# PSL Series 30.5 mm Pushbutton NEMA 12 Wall Mount



## Applications

Designed to hold all standard 30.5mm brands of pushbuttons, switches and pilot lights. Provides protection from dirt, dust, oil and water. This slimline model is designed for conditions where enclosures must fit within very limited areas.

- Standard “4-way” pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Grounding provisions provided

## Construction

- Fabricated from 14 gauge steel
- Closed cell oil-resistant neoprene gasket
- Continuously welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells



## Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces


## Listings

- UL 508, Types 12 & 13
- UL File E64791
- CSA Certified, Type 12 & 13
- CSA File LL66078
- NEMA/EEMAC Types 12 & 13
- JIC EL-1-71

## Dimensions



PSL Hole Arrangements



Enclosure Shipping Schedule		
Same day	1 - 7 days	1 - 10 days
Color indicates shipping lead time in business days.		

Part Number	Price	Body/Door	Size HxWxD	Mounting CxE	Overall LxM	F	I
<b>PSL1</b>	<--->	14/14	4x2.5x2.5 (102x64x64)	1.63x4.5 (41x114)	5x2.81 (127x71)	2.25 (57)	2.09 (53)
<b>PSL2</b>	<--->	14/14	6.25x2.5x2.5 (159x64x64)	1.63x6.75 (41x171)	7.25x2.81 (184x71)	2.25 (57)	2.09 (53)
<b>PSL3</b>	<--->	14/14	8.5x2.5x2.5 (216x64x64)	1.63x9 (41x229)	9.5x2.81 (241x71)	2.25 (57)	2.09 (53)
<b>PSL4</b>	<--->	14/14	10.75x2.5x2.5 (273x64x64)	1.63x11.25 (41x286)	11.75x2.81 (298x71)	2.25 (57)	2.09 (53)

Note: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.