

WC12 NEMA 12 Operator Consoles



Applications

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc. can be mounted on sloping control surfaces. Interior components can be mounted on subpanel and terminal straps. Heavy duty construction provides protection from dirt, dust, oil and water.

Construction

Body

- Bodies and doors fabricated from 14 gauge steel
- Seams are continuously welded and ground smooth
- 3-point keylocking handle is provided on front main door
- Double overlapping doors are provided on two door consoles
- Main hinged doors are flush
- Large sloping control panels are hinged along bottom edge
- Control panels have captivated screws threaded into sealed wells
- Door stops provided to hold control panel open
- Print pocket is provided
- Closed cell neoprene gasket
- Removable subpanel is included with console
- Grounding provisions provided
- Studs are welded to inside of console for mounting subpanel
- An inclined body rail is welded to each side of 24" wide and 36" wide consoles for support of terminal straps



Top

- Fabricated from 14 gauge steel
- Top has a sloped front surface
- Four holes are provided for mounting to body
- Seams are continuously welded and ground smooth
- Instrument and access panels have captivated screws which thread into sealed wells
- Closed cell neoprene gasket
- Instrument panels and access panels are removable

Writing desk

- Fabricated from 14-gauge steel
- Seams are continuously welded and ground smooth
- Desks are removable and attach easily to console front

Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces
- Included subpanel is white polyester powder over phosphatized surfaces

Listings

- UL 508, Types 12 & 13
- UL File E64791
- CSA Certified, Type 12 & 13
- CSA File LL66078
- NEMA/EEMAC Types 12 & 13

Enclosure Shipping Schedule		
Same day	1 - 7 days	1 -10 days
Color indicates shipping lead time in business days.		



Console Part Number	Price	Body/Door	Console /Body Only	Console Top P/N	Price	Writing Desk P/N	Price	Caster Kit P/N	Price	Subpanel Size HxW
WC1224B	<--->	14 /14	Console body only 24" wide (610)	WC1224T	<--->	WC1224W	<--->	WC12C	<--->	32x18 (813x457)
WC12B	<--->	14 /14	Console body only 36" wide (914)	WC12T	<--->	WC12W	<--->	WC12C	<--->	32x30 (813x762)
WC1248BD	<--->	14 /14	Console body only 48" wide (1219)	WC1248T	<--->	WC1248W	<--->	WC12C	<--->	32x42 (813x1067)

Note: Dimensions in inches (millimeters). Subpanels included. Tops, writing desk, etc. must be ordered separately.

WC12 NEMA 12 Operator Consoles


Dimensions

WC1224B & WC12B



RIGHT VIEW
(APPLICABLE TO ALL)

WC1248BD



Notes:

1. Access doors open 180 degrees.
2. One 8X10 Print Pocket is provided.
3. 3-point key-locking handles are provided on main doors.
4. Writing desk is provided with mounting hardware.