

WC9 NEMA 12 Operator Consoles



Applications

Designed to house electrical and electronic controls, instruments and components. Heavy duty construction provides protection from dirt, dust, oil and water. Sloping front control panel provides an ideal surface for mounting pushbuttons, pilot lights, meters and switches. Interior components can be mounted on panels located on the sides and back of the enclosure. (Subpanels are optional.)

Construction

- Bodies and doors fabricated from 14 gauge steel
- Continuously welded seams ground smooth, without knockouts or holes
- Control panel attached with continuous hinge along bottom edge and secured with captive screws, threaded into sealed wells
- Door stops provided to hold control panel open
- Print pocket is provided
- Closed cell neoprene gasket
- Collar studs provided for mounting one, two or three optional panels
- Grounding provisions provided
- 3-point keylocking handle is provided on the front access door

Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces
- Optional side and back panels are white polyester powder over phosphatized surfaces
- Optional castor kits can be used on any enclosure to provide mobility.
- Castor kit includes two swivel casters and two stationary casters along with all necessary hardware

Listings

- UL 508, Types 12 & 13
- UL File E64791
- CSA Certified, Type 12 & 13
- CSA File LL66078
- NEMA/EEMAC Types 12 & 13

NOTE: Do NOT use NPxxxxC subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures. For example: Subpanel NP1612C will not fit enclosure WA161206FM (NP1612 is the correct subpanel). Only use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures.

Enclosure Shipping Schedule

Same day	1 - 7 days	1 -10 days
----------	------------	------------


Color indicates shipping lead time in business days.

Part Number	Price	Body/Door	Console Size	Subpanel P/N*	Price	Subpanel Size HxW	Side Panel P/N*	Price	Side Panel Size HxW	Caster Kit P/N*	Price
WC924B	<--->	14/14	Console body 24" (610) wide	NP3020	<--->	27x17 (686x432)	NP3020	<--->	27x17 (686x432)	WC10C	<--->
WC936B	<--->	14/14	Console body 36" (914) wide	NP3030	<--->	27x27 (686x686)	NP3020	<--->	27x17 (686x432)	WC10C	<--->

Notes: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.. * Subpanels, side panels and caster kits must be ordered separately.

WC9 NEMA 12 Operator Consoles

Dimensions



Notes:

1. One 8X10 Print Pocket is provided.
2. 3-point key-locking handles are provided on main doors.
3. Subpanels and side panels are optional.