

STABLE AC Motor Slide Bases

Mounting Slide Bases for 56 to 449T NEMA Motors

Features


- Allows adjustment of motor mounting position
- Double adjusting screws for frames 182T - 449T
- Manufactured to precise dimensional standards
- Dimensionally interchangeable with existing major makes
- Heavy-duty steel construction
- Painted with oven-baked primer for better adhesion of customer's paint
- All "D" bolts (motor mounting bolts) are fixed to the exact motor foot pattern
- All "D" bolts are welded into position to prevent spinning and dropping from slots
- Bases are provided with washers




Motor Slide Bases											
Part Number	Price	Fits Frame Type	Shipping Weight (lb)	Fits Motor							
				IronHorse	Marathon micro -MAX	Marathon Black Max 230/460V	Marathon Black Max 575V	Marathon Blue Max	Marathon NEMA Premium XRI	Marathon Blue Chip XRI 230/460V	Marathon Blue Chip XRI 575V
MTA-BASE-W56	<-->	56	3.5	MTR-xxx-1AB18 MTR-xxx-3BD18 MTR-xxx-3BD36	Y500 Y360 Y364	Y592(-A772) Y534(-A772) Y535(-A772)	Y555(-A772) Y556(-A772)	-	E2000	-	-
MTA-BASE-W143T	<-->	143T/TC	5.0	MTC-001-3BD18(CK) MTC-1P5-3BD36	-	Y536(-A772)	-	-	E2001 E2003	-	-
MTA-BASE-W145T	<-->	145T/TC	5.6	MTC-001-3BD12 MTC-1P5-3BD18(CK) MTC-002-3BD18(CK) MTC-002-3BD36	Y368	Y537(-A772) Y538(-A772) Y551(-A772)	Y557(-A772)	-	E2002 E2004 E2006 E2007	-	-
MTA-BASE-W182T	<-->	182T/TC	10	MTC-1P5-3BD12 MTC-003-3BD18(CK) MTC-003-3BD36	Y999	Y541(-A772)	Y558(-A772)	-	E2005 E2009 E2010	-	-
MTA-BASE-W184T	<-->	184T/TC	10	MTC-002-3BD12 MTC-005-3BD18(CK) MTC-005-3BD36	Y372	Y540(-A772) Y543(-A772)	Y559(-A772)	-	E2008 E2012 E2013	-	-
MTA-BASE-W213T	<-->	213T/TC	15	MTC-003-3BD12 MTC-7P5-3BD18(CK) MTC-7P5-3BD36	Y994	Y542(-A772) Y545(-A772)	Y560(-A772)	-	E2011 E2015 E2016	-	-
MTA-BASE-W215T	<-->	215T/TC	16	MTC-005-3BD12 MTC-010-3BD18(CK) MTC-010-3BD36	Y996	Y544(-A772) Y547(-A772)	Y561(-A772)	-	E2014 E2018 E2019	-	-
MTA-BASE-W254T	<-->	254T/TC	20	MTC-7P5-3BD12 MTC-015-3BD18(CK)	-	Y546(-A772) Y549(-A772)	Y562(-A772)	-	-	E205	E307
MTA-BASE-W256T	<-->	256T/TC	21	MTC-010-3BD12 MTC-020-3BD18(CK)	-	Y548(-A772) Y552(-A772)	Y563(-A772)	-	-	E206	E308
MTA-BASE-W284T	<-->	284T/TC	23	MTC-025-3BD18(CK)	-	Y553(-A772)	Y567(-A772)	-	-	E207	E309
MTA-BASE-W286T	<-->	286T/TC	24	MTC-030-3BD18(CK)	-	Y393(-A772)	Y394(-A772)	-	-	E208	E310
MTA-BASE-W324T	<-->	324T/TC	33	MTC-040-3BD18(CK)	-	-	-	Y571(-A774) Y513(-A775)	-	E209	E311
MTA-BASE-W326T	<-->	326T/TC	35	MTC-050-3BD18(CK)	-	-	-	Y572(-A774) Y514(-A775)	-	E210	E312
MTA-BASE-W364T	<-->	364T/TC	46	MTC-060-3BD18(CK)	-	-	-	Y573(-A774) Y515(-A775)	-	E211	E313
MTA-BASE-W365T	<-->	365T/TC	47	MTC-075-3BD18(CK)	-	-	-	Y574(-A774) Y516(-A775)	-	E212	E315
MTA-BASE-W404T	<-->	404T/TC	64	-	-	-	-	-	-	-	-
MTA-BASE-W405T	<-->	405T/TC	65	MTC-100-3BD18(CK)	-	-	-	Y575(-A774) Y517(-A775)	-	E213	E314
MTA-BASE-W444T	<-->	444T	69	MTC-125-3BD18	-	-	-	-	-	-	-
MTA-BASE-W445T	<-->	445T	70	MTC-150-3BD18	-	-	-	-	-	-	-
MTA-BASE-W447T	<-->	445/7T 447T	92	MTC-200-3BD18	-	-	-	-	-	-	-
MTA-BASE-W449T	<-->	449T	98	MTC-250-3BD18 MTC-300-3BD18	-	-	-	-	-	-	-

STABLE AC Motor Slide Bases

Dimensions – Mounting Slide Bases for NEMA Motors



W56 - W145T Motor Slide Base Dimensions



W182T - W449T Motor Slide Base Dimensions
(W182T-W215T bases have one-piece top plates, similar to W56-W145T)

Dimensions [inches, except as noted] - STABLE Motor Slide Bases

MTA-BASE-Wxxx	A	B	C	D	E	F	G	H	I	J	K(mm)	L	M	N	W
56	10-5/8	6-1/2	1-1/8	4-1/2	2-7/16	1-1/2	3-13/16	2-7/8	3/8	3	2 mm	7/8	5/16 x 1	3/8 x 4	n/a
143T	10-1/2	7-1/2	1-1/8	5-1/2	2-3/4	2	3-3/4	3-3/8	3/8	3	3 mm	13/16	5/16 x 1	3/8 x 4	n/a
145T	10-1/2	8-1/2	1-1/8	6-1/2	2-3/4	2-1/2	3-3/4	3-7/8	3/8	3	3 mm	13/16	5/16 x 1	3/8 x 4	n/a
182T	12-3/4	9-1/2	1-1/2	6-1/2	3-3/4	2-1/4	4-1/2	4-1/4	1/2	3	3.5 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	4-1/2
184T	12-3/4	10-1/2	1-1/2	7-1/2	3-3/4	2-3/4	4-1/2	4-3/4	1/2	3	3.5 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	5-1/2
213T	15	11	1-3/4	7-1/2	4-1/4	2-3/4	5-1/4	4-3/4	1/2	3-1/2	3.8 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	5-1/2
215T	15	12-1/2	1-3/4	9	4-1/4	3-1/2	5-1/4	5-1/2	1/2	3-1/2	3.8 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	7
254T	17-3/4	15-1/8	2	10-3/4	5	4-1/8	6-1/4	6-5/8	5/8	4	4.6 mm	1-7/16	1/2 x 1-3/4	5/8 x 6	5-5/16
256T	17-3/4	16-7/8	2	12-1/2	5	5	6-1/4	7-1/2	5/8	4	4.6 mm	1-7/16	1/2 x 1-3/4	5/8 x 6	7
284T	19-3/4	16-7/8	2	12-1/2	5-1/2	4-3/4	7	7-1/2	5/8	4-1/2	4.6 mm	1-11/16	1/2 x 2	5/8 x 6	7
286T	19-3/4	18-3/8	2	14	5-1/2	5-1/2	7	8-1/4	5/8	4-1/2	4.6 mm	1-11/16	1/2 x 2	5/8 x 6	8
324T	22-3/4	19-1/4	2-1/2	14	6-1/4	5-1/4	8	8-1/2	3/4	5-1/4	4.6 mm	2-3/16	5/8 x 2-1/2	3/4 x 9	7
326T	22-3/4	20-3/4	2-1/2	15-1/2	6-1/4	6	8	9-1/4	3/4	5-1/4	4.6 mm	2-3/16	5/8 x 2-1/2	3/4 x 9	8-1/2
364T	25-1/2	20-1/2	2-1/2	15-1/2	7	5-5/8	9	9-1/8	3/4	6	5.8 mm	2-1/16	5/8 x 2-1/2	3/4 x 9	7-3/4
365T	25-1/2	21-1/2	2-1/2	16-1/2	7	6-1/8	9	9-5/8	3/4	6	5.8 mm	2-1/16	5/8 x 2-1/2	3/4 x 9	8-3/4
404T	28-3/4	22-3/8	3	16-1/2	8	6-1/8	10	9-7/8	7/8	7	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	8-3/4
405T	28-3/4	23-7/8	3	18	8	6-7/8	10	10-5/8	7/8	7	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	10-1/4
444T	31-1/4	24-5/8	3	19-1/4	9	7-1/4	11	11	7/8	7-1/2	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	11
445T	31-1/4	26-5/8	3	21-1/4	9	8-1/4	11	12	7/8	7-1/2	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	13
447T	31-1/4	30-1/8	3	24-3/4	9	10	11	13-3/4	7/8	7-1/2	8 mm	3	3/4 x 3-1/2	3/4 x 11	16-1/2
449T	31-1/4	35-1/8	3	29-3/4	9	12-1/2	11	16-1/4	7/8	7-1/2	8 mm	3	3/4 x 3-1/2	3/4 x 11	21-1/2