

# NEMA 12 JIC Hinged Screw Cover Wall Mount



## Applications

Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection from dirt, dust, oil and water.

## Construction

- Bodies and doors fabricated from 14 gauge steel
- Lids are sealed with closed cell oil resistant neoprene gasket
- Continuously welded seams ground smooth, less knockouts of holes
- Captivated door screws thread into sealed wells
- Grounding provisions provided
- Weldnuts are provided for mounting optional subpanel
- No mounting feet or mounting holes are provided

## Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces
- Optional subpanels are white polyester powder over phosphatized surfaces

## Listings

- UL 50, Types 12 & 13
- UL File E6924
- CSA Certified, Type 12
- CSA File LL66078
- NEMA/EEMAC Types 12 & 13
- JIC EL-1-71

Enclosure Shipping Schedule		
Same day	1 - 7 days	1 -10 days
Color indicates shipping lead time in business days.		

Part Number	Price	Body/Door	Enclosure Size HxWxD	Subpanel P/N	Price	Subpanel Size AxB	Overall LxM	F	J	N	O	P
<b>WA060604GIE</b>	<--->	14/14	6x6x4 (152x152x102)	<b>N1P0606</b>	<--->	4.25x4.25 (108x108)	6.31x6.31 (160x160)	3.53 (90)	0.875 (22)	2.78 (71)	3.59 (91)	0.56 (14)
<b>WA080604GIE</b>	<--->	14/14	8x6x4 (203x152x102)	<b>N1P0608</b>	<--->	6.25x4.25 (159x108)	8.31x6.31 (211x160)	3.53 (90)	0.875 (22)	2.78 (71)	3.59 (91)	0.56 (14)
<b>WA080804GIE</b>	<--->	14/14	8x8x4 (203x203x102)	<b>N1P0808</b>	<--->	6.25x6.25 (159x159)	8.31x8.31 (211x211)	3.53 (90)	0.875 (22)	2.78 (71)	3.59 (91)	0.56 (14)
<b>WA080806GIE</b>	<--->	14/14	8x8x6 (203x203x152)	<b>N1P0808</b>	<--->	6.25x6.25 (159x159)	8.31x8.31 (211x211)	5.53 (141)	0.875 (22)	4.78 (121)	5.59 (142)	0.56 (14)
<b>WA100804GIE</b>	<--->	14/14	10x8x4 (254x203x102)	<b>N1P0810</b>	<--->	8.25x6.25 (210x159)	10.31x8.31 (262x211)	3.53 (90)	0.875 (22)	2.78 (71)	3.59 (91)	0.56 (14)
<b>WA100806GIE</b>	<--->	14/14	10x8x6 (254x203x152)	<b>N1P0810</b>	<--->	8.25x6.25 (210x159)	10.31x8.31 (262x211)	5.53 (141)	0.875 (22)	4.78 (121)	5.59 (142)	0.56 (14)
<b>WA101006GIE</b>	<--->	14/14	10x10x6 (254x254x152)	<b>N1P1010</b>	<--->	8.25x8.25 (210x210)	10.31x10.31 (262x262)	5.53 (141)	0.875 (22)	4.78 (121)	5.59 (142)	0.56 (14)
<b>WA121004GIE</b>	<--->	14/14	12x10x4 (305x254x102)	<b>N1P1012</b>	<--->	10.25x8.25 (260x210)	12.31x10.31 (313x262)	3.53 (90)	0.875 (22)	2.78 (71)	3.59 (91)	0.56 (14)
<b>WA121006GIE</b>	<--->	14/14	12x10x6 (305x254x152)	<b>N1P1012</b>	<--->	10.25x8.25 (260x210)	12.31x10.31 (313x262)	5.53 (141)	0.875 (22)	4.78 (121)	5.59 (142)	0.56 (14)
<b>WA121206GIE</b>	<--->	14/14	12x12x6 (305x305x152)	<b>N1P1212</b>	<--->	10.25x10.25 (260x260)	12.31x12.31 (313x313)	5.53 (141)	0.875 (22)	4.78 (121)	5.59 (142)	0.56 (14)
<b>WA141206GIE</b>	<--->	14/14	14x12x6 (356x305x152)	<b>N1P1214</b>	<--->	12.25x10.25 (311x260)	14.31x12.31 (364x313)	5.53 (141)	0.875 (22)	4.78 (121)	5.59 (142)	0.56 (14)

Note: Subpanels must be ordered separately. Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.

# NEMA 12 JIC Hinged Screw Cover Wall Mount

Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/ Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/ Lights

Process

Relays/ Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics

Safety

Appendix

Product Index

Part # Index

## Dimensions

