

# WC10 NEMA 12 Operator Consoles



## Applications

Designed to hold electrical and electronic controls and instruments. Heavy duty construction provides protection from dirt, dust, oil and water. Pushbuttons, pilot lights, meters, switches, etc. can be mounted on sloping control surfaces. Interior components can be mounted on subpanel and terminal straps.

## Construction

### Body

- Fabricated from 14 gauge steel
- Seams are continuously welded and ground smooth
- 3-point keylocking handle is provided on front, main door
- Flush main door
- Control panels are hinged along bottom edge
- Control panels have captivated screws threaded into sealed wells
- Door stops provided to hold control panel open
- Print pocket is provided
- Standard closed cell neoprene gasket
- Removable subpanel is included with enclosure
- Grounding provisions provided

### Top

- Fabricated from 14 gauge steel
- Seams are continuously welded and ground smooth
- Instrument and access panels have captivated screws that thread into sealed wells
- Closed cell neoprene gasket

### Writing desk

- Fabricated from 14-gauge steel
- Seams are continuously welded and ground smooth
- Desks are removable and attach easily to console front

### Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces
- Included subpanel is white polyester powder over phosphatized surfaces

### Listings

- UL 508, Types 12 and 13
- UL File E64791
- CSA Certified, Type 12 & 13
- CSA File LL66078
- NEMA/EEMAC Types 12 & 13



### Enclosure Shipping Schedule

Same day	1 - 7 days	1 -10 days
----------	------------	------------


Color indicates shipping lead time in business days.

Part Number	Price	Body/Door	Description
<b>WC10B*</b>	<--->	14 /14	Console body only, 24" (610) wide
<b>WC10T</b>	<--->	14 /14	Top for WC10B
<b>WC10W</b>	<--->	14 /14	Writing desk for WC10B
<b>WC10C</b>	<--->	14 /14	Caster kit: Set of 4 castors, 2 mounting plate and hardware

Note: Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.\* UL Listed. Subpanels are included with console. Note: Tops, writing desks and caster kits must be ordered separately.

# WC10 NEMA 12 Operator Consoles

## Dimensions



### Notes:

1. Access doors open 180 degrees.
2. One 8"x10" Print Pocket is provided.
3. 3-point key-locking handles are provided on main doors.
4. Writing desk is provided with mounting hardware.
5. 27.25 x 18.75 subpanel included.