

Pressure Units Conversion Chart

Pressure Conversion Table: Multiplication Factors										
Desired Units	Known Units									
		Atmos	Bars	In of Hg (0°C)	In of H ₂ O (4°C)	K grams/meter ²	Lb/in ² (psi)	Lb/ft ²	mm of Hg torr	Pascals
	Atmos	1	9.86923 x 10 ⁻¹	3.34207 x 10 ⁻²	2.458 x 10 ⁻³	9.678 x 10 ⁻⁵	0.068046	4.7254 x 10 ⁻⁴	1.316 x 10 ⁻³	9.869 x 10 ⁻⁶
	Bars	1.01325	1	3.3864 x 10 ⁻²	2.491 x 10 ⁻³	9.8067 x 10 ⁻⁵	6.8948 x 10 ⁻²	4.788 x 10 ⁻⁴	1.333 x 10 ⁻³	10 ⁻⁵
	In of Hg (0°C)	29.9213	29.53	1	7.355 x 10 ⁻²	2.896 x 10 ⁻³	2.036	0.014139	3.937 x 10 ⁻²	2.953 x 10 ⁻⁴
	In of H ₂ O (4°C)	406.8	401.46	13.60	1	3.937 x 10 ⁻²	27.68	0.1922	0.5354	4.014 x 10 ⁻³
	K grams/meter ²	1.033227 x 10 ⁴	1.0197 x 10 ⁴	345.3	25.40	1	7.0306 x 10 ²	4.882	13.59	1.019 x 10 ⁻¹
	Lb/in ² (psi)	14.695595	14.504	0.4912	3.6126 x 10 ⁻²	1.423 x 10 ⁻³	1	6.9444 x 10 ⁻³	1.934 x 10 ⁻²	1.450 x 10 ⁻⁴
	Lb/ft ²	2116.22	2088.5	70.726	5.202	0.2048	144.0	1	2.7844	2.089 x 10 ⁻²
	mm of Hg torr	760	750.06	25.400	1.868	7.3558 x 10 ⁻²	51.715	0.35913	1	7.502 x 10 ⁻³
Pascals	1.01325 x 10 ⁵	1 x 10 ⁵	3.386 x 10 ³	2.491 x 10 ²	9.8067	6.8948 x 10 ³	4.788 x 10 ¹	1.333 x 10 ²	1	

Example: To convert from 50 psi to "In of H₂O", (50 psi) (27.68) = 1384 In of H₂O

PLC Overview

DL05/06 PLC

DL105 PLC

DL205 PLC

DL305 PLC

DL405 PLC

Field I/O

Software

C-more HMIs

Other HMI

AC Drives

Motors

Steppers/Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pushbuttons/Lights

Process

Relays/Timers

Comm.

TB's & Wiring

Power

Circuit Protection

Enclosures

Appendix

Part Index