



# PS Series 12 VDC and 24 VDC Power Supplies

## Switching power supplies at linear supply prices

The PS Series power supplies give you consistent, reliable, switched DC power at linear power supply prices.


These power supplies use efficient switching technology to produce the most power in the smallest space, while generating a minimum amount of heat. The constant-current short circuit protection limits the output current as the voltage is reduced to safely protect your control components from direct shorts and device failures. Once the short is corrected, the PS Series power supplies automatically resume supplying full-voltage power. Precisely regulated output power is suitable for battery charging applications. Extra-sturdy DIN rail mounts and removable plug connections make installation a breeze.

Meeting UL/cUL 60950, 508 and 1604\* (Class I, Div. 2), our PS-D (DIN-rail mounted) power supplies meet the standards required for practically any industrial control application.

### Features

- 2A - 24A at 24 VDC, 3.5A at 12 VDC
- Regulated switch mode type
- Low profile case
- Easy DIN-rail mounting
- Constant-current short circuit protection
- Low ripple and noise
- Selectable input voltage (115/230 VAC)
- High EMC immunity
- EMI meets EN 55011-B and FCC Part 15, Level B
- Worldwide safety approvals: UL/cUL 508, 60950 and 1604 Class I, Div. 2, CE

\* (PS12-050D, PS24-050D and PS24-500D do not meet UL 1604 Class I Div 2),




**Constant current protection with auto-recovery:**  
• No current spikes to damage powered devices due to improper wiring or a powered device failure

**Efficient switching technology:**  
• Smaller size and less heat generated results in less wasted space and energy

## Part numbering system

### PS12-050D



Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/Lights

Process

Relays/Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics

Appendix

Product Index

Part # Index

# PS Series Power Supplies Specifications



PS12-050D  
PS24-050D



PS12-075D  
PS24-075D



PS24-150D



PS24-300D



PS24-500D



PS24-600D

General Specifications	
<b>Temperature</b>	<b>Operating (ambient):</b> -25°C to +70°C (-13°F to 158°F) max, Derating above 50°C 2%/C <b>Storage (non-operating):</b> -25°C to +85°C (-13°F to 185°F) max, <b>Temperature drift:</b> 0.02%/C
<b>Humidity</b>	95% (non-condensing) relative humidity max
<b>Switching Frequency</b>	80 kHz typical (PWM)
<b>Isolation</b>	According to IEC/EN 60950, UL 60950, UL 508
<b>Output Regulation</b>	Input variation: ± 0.2% max Load variation: 50 W, 75 W, 150 W models: ± 1% max ..... 300 W, 500 W, 600 W models: ± 0.3% max
<b>Output Voltage Ripple</b>	< 50 mV peak to peak (20 MHz bandwidth)
<b>Output Protection</b>	Current limit: 110% maximum output rating, Voltage limit: 140% Vout nom
<b>Vibration</b>	1gn 20 sweeps each axis
<b>Shock</b>	15gn, 11ms each axis
<b>Enclosure Rating</b>	IP 20
<b>Enclosure Material</b>	Aluminum (chassis) / stainless steel (cover)
<b>Mounting</b>	Snap-on with self-locking spring for 35mm DIN rails
<b>Connection</b>	Removable screw terminals for 22-10 AWG
<b>Agency Approvals</b>	UL/cUL 60950 recognized, file E198298, UL/cUL 508 listed File E197592, UL/cUL 1604 listed (Class I, Div 2, groups A,B,C, and D hazardous locations), File E197886, <b>except PSxx-050D and PS24-500D</b> , which are not UL/cUL1604 listed. CE

*Note: All specifications are valid at nominal input voltage, full load and +25°C after warm-up time, unless otherwise stated.*

Input Specifications								
Part Number	Input Voltage Range	Input Frequency Range	Input Current (Typical)		Inrush Current (<2mS)		Efficiency (Typ.)	C-Curve Circuit Breaker or Slow-blow Fuse
			115 VAC	230 VAC	115 VAC	230 VAC		
PS12-050D	93-264 VAC	47-63 Hz	1.2 A	0.7 A	<15 A	<30 A	84%	5.0 A
PS24-050D	93-264 VAC		1.2 A	0.7 A			87%	
PS12-075D	93-132 VAC 187-264 VAC (switch selectable)		1.7 A	0.9 A	<16.5 A	<33 A	83%	
PS24-075D			1.7 A	0.9 A			85%	
PS24-150D	93-132 VAC 187-264 VAC (switch selectable)		3.0 A	1.7 A	<35 A	<70 A	84%	10.0 A
PS24-300D	93-132 VAC		5.4 A	3.3 A	<35 A	<70 A	87%	15.0 A
PS24-500D	93-132 VAC		9.5 A	N/A	<50 A	N/A	87%	
PS24-600D	93-132 VAC 187-264 VAC (switch selectable)		10.5 A	6.4 A	<70 A	<80 A	88%	20.0 A

Output Specifications									
Part Number	Price	Output Voltage	Output Voltage Adj. Range	Output Current (Max.)	Output Power (Max.)	Output Voltage Regulation*	Hold-Up Time		MTBF (IEC 1709 @ 25°C)
							115 VAC	230 VAC	
PS12-050D	<--->	12 VDC	12-14 VDC	3.5 A	50 W	1%	25 mS	30 mS	2,992,000 hours
PS24-050D	<--->	24 VDC	24-28 VDC	2.0 A	50 W				
PS12-075D	<--->	12 VDC	12-14 VDC	6.0 A	75 W				
PS24-075D	<--->	24 VDC	24-28 VDC	3.0 A	75 W				
PS24-150D	<--->	24 VDC	24-28 VDC	6.0 A	150 W	0.3%	20 mS	N/A	1,800,000 hours
PS24-300D	<--->	24 VDC	24-28 VDC	12.0 A	300 W				
PS24-500D	<--->	24 VDC	24-28 VDC	20.0 A	500 W				
PS24-600D	<--->	24 VDC	24-28 VDC	24.0 A	600 W				

\*Load variation (10-90%)

**Notes: Output current characteristic suitable for battery charging applications. Not recommended for redundancy or parallel operation.**

Replacement terminal blocks are available. See price list.



Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/ Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/ Lights

Process

Relays/ Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics


Appendix

Product Index

Part # Index


# PS Series Power Supplies Dimensions

## PS12-050D, PS24-050D




## PS24-300D


Note: All dimensions are in millimeters (inches). Tolerances ±0.5mm




## PS12-075D, PS24-075D



## PS24-500D



## PS24-150D



## PS24-600D

