

PS Series 12 VDC and 24 VDC Power Supplies

Switching power supplies at linear supply prices

The PS Series power supplies give you consistent, reliable, switched DC power at linear power supply prices.

These power supplies use efficient switching technology to produce the most power in the smallest space, while generating a minimum amount of heat. The constant-current short circuit protection limits the output current as the voltage is reduced to safely protect your control components from direct shorts and device failures. Once the short is corrected, the PS Series power supplies automatically resume supplying full-voltage power. Precisely regulated output power is suitable for battery charging applications. Extra-sturdy DIN rail mounts and removable plug connections make installation a breeze.

Meeting UL/cUL 60950, 508 and 1604* (Class I, Div. 2), our PS-D (DIN-rail mounted) power supplies meet the standards required for practically any industrial control application.

Features

- 2A - 24A at 24 VDC, 3.5A at 12 VDC
- Regulated switch mode type
- Low profile case
- Easy DIN-rail mounting
- Constant-current short circuit protection
- Low ripple and noise
- Selectable input voltage (115/230 VAC)
- High EMC immunity
- EMI meets EN 55011-B and FCC Part 15, Level B
- Worldwide safety approvals: UL/cUL 508, 60950 and 1604 Class I, Div. 2, CE

* (PS12-050D, PS24-050D and PS24-500D do not meet UL 1604 Class I Div 2),

Removable plug terminals:

- Easy to install and disconnect wiring

Sturdy DIN-rail mounting:

- Easy to mount and remove, but still secure

Power ON LED:

- Quick visual check for troubleshooting

Durable metal case:

- A reliable industrial duty package


Constant current protection with auto-recovery:

- No current spikes to damage powered devices due to improper wiring or a powered device failure

Efficient switching technology:

- Smaller size and less heat generated results in less wasted space and energy

Part numbering system



PS Series Power Supplies Specifications



PS12-050D
PS24-050D



PS12-075D
PS24-075D



PS24-150D



PS24-300D



PS24-500D



PS24-600D

General Specifications	
Temperature	Operating (ambient): -25°C to +70°C (-13°F to 158°F) max, Derating above 50°C 2%/C Storage (non-operating): -25°C to +85°C (-13°F to 185°F) max, Temperature drift: 0.02%/C
Humidity	95% (non-condensing) relative humidity max
Switching Frequency	80 kHz typical (PWM)
Isolation	According to IEC/EN 60950, UL 60950, UL 508
Output Regulation	Input variation: ± 0.2% max Load variation: 50 W, 75 W, 150 W models: ± 1% max 300 W, 500 W, 600 W models: ± 0.3% max
Output Voltage Ripple	< 50 mV peak to peak (20 MHz bandwidth)
Output Protection	Current limit: 110% maximum output rating. Voltage limit: 140% Vout nom
Vibration	1gn 20 sweeps each axis
Shock	15gn, 11mS each axis
Enclosure Rating	IP 20
Enclosure Material	Aluminum (chassis) / stainless steel (cover)
Mounting	Snap-on with self-locking spring for 35mm DIN rails
Connection	Removable screw terminals for 22-10 AWG
Agency Approvals	UL/cUL 60950 recognized, file E198298, UL/cUL 508 listed File E197592, UL/cUL 1604 listed (Class I, Div 2, groups A,B,C, and D hazardous locations), File E197886, except PSxx-050D and PS24-500D , which are not UL/cUL1604 listed. CE
<i>Note: All specifications are valid at nominal input voltage, full load and +25°C after warm-up time, unless otherwise stated.</i>	


Input Specifications								
Part Number	Input Voltage Range	Input Frequency Range	Input Current (Typical)		Inrush Current (<2mS)		Efficiency (Typ.)	C-Curve Circuit Breaker or Slow-blow Fuse
			115 VAC	230 VAC	115 VAC	230 VAC		
PS12-050D	93-264 VAC	47-63 Hz	1.2 A	0.7 A	<15 A	<30 A	84%	5.0 A
PS24-050D	93-264 VAC		1.2 A	0.7 A			87%	
PS12-075D	93-132 VAC 187-264 VAC (switch selectable)		1.7 A	0.9 A	<16.5 A	<33 A	83%	
PS24-075D			1.7A	0.9 A			85%	
PS24-150D	3.0 A		1.7 A	<35 A	<70 A	84%	10.0 A	
PS24-300D	5.4 A		3.3 A			87%		
PS24-500D	9.5 A		N/A	<50 A	N/A	87%	15.0 A	
PS24-600D	10.5 A		6.4 A	<70 A	<80 A	88%	20.0 A	

Output Specifications									
Part Number	Price	Output Voltage	Output Voltage Adj. Range	Output Current (Max.)	Output Power (Max.)	Output Voltage Regulation*	Hold-Up Time		MTBF (IEC 1709 @ 25°C)
							115 VAC	230 VAC	
PS12-050D	<-->	12 VDC	12-14 VDC	3.5 A	50 W	1%	25 mS	30 mS	2,992,000 hours
PS24-050D	<-->	24 VDC	24-28 VDC	2.0 A	50 W				
PS12-075D	<-->	12 VDC	12-14 VDC	6.0 A	75 W				1,800,000 hours
PS24-075D	<-->			3.0 A	75 W				
PS24-150D	<-->	24 VDC	24-28 VDC	6.0 A	150 W	1,939,000 hours			
PS24-300D	<-->			12.0 A	300 W		1,913,000 hours		
PS24-500D	<-->			20.0 A	500 W	0.3%	20 mS	N/A	1,467,000 hours
PS24-600D	<-->			24.0 A	600 W	15 mS	25 mS	1,434,000 hours	
*Load variation (10-90%)					Notes: Output current characteristic suitable for battery charging applications. Not recommended for redundancy or parallel operation.				


Replacement terminal blocks are available. See price list.

PS Series Power Supplies Dimensions

PS12-050D, PS24-050D




PS24-300D




Note: All dimensions are in millimeters (inches). Tolerances ±0.5mm


PS12-075D, PS24-075D



PS24-500D



PS24-150D



PS24-600D

