ACSN100 Series AC Current Switch



ACSN100 series compact case current sensing switch is a compact, inexpensive, easy-to-use ring which slips onto a conductor to give a solid-state contact for indication of current flow. Ideal for use in control panels or wherever confirmation of current flow is desired, the ACSN100 current sensing switch is a cost-effective way to detect live conductors and see current flow to fans, heaters, pumps, lighting or other AC powered devices.

Applications

Electronic proof of flow

· Current sensing switches eliminate the need for multiple pipe or duct penetrations and is more reliable than electromechanical pressure or flow switches.

Electric Motors

• Quick reporting of load status.

Electrical Heaters

• Faster response than temperature sensors.

Lighting Circuits

• Easier to install and more accurate than photocells.

Features

- N.O. solid-state switch for control circuits up to 120 VAC/VDC.
- · No adjustment needed for "Go/No Go" status indication.
- · Detects currents as low as 0.5 A with a single conductor pass, eliminates the need to wrap conductors multiple times to increase sensitivity.
- No moving parts provide a nearly unlimited number of operations, and powered from the monitored circuit.
- Normally open connection. Connect the 24 inch leads to a local controller or to a terminal block for remote operation.
- · Five-year warranty








	ACSN100 AC Current Switch						
Part Number		Description	Pcs/Pkg	Wt (lb)	Price		
ACSN100-AE-F	AcuAMP AC curre range, 0.5A non-acoutput, 0.15A @ 1	1	0.07	\$42.00			
	18						
Monitored	Circuit	0-100A, 600VAC line-to-line max					
Frequency	Range	50-400 Hz					
Output Si	witch	Solid-state, normally open, 150mA, 120 VAC/DC (not polarity sensitive)					
Off State Le	eakage	<10µA					
Setpoint (Trip Point)		Non-adjustable, 0.5 A (reset point ~0.475 A)					
Sensing Ap	perture	0.30" ID					
Case UL94V-0 Flammability Rating							
Mounti	unting Slides directly onto monitored conductor						
Isolation Voltage 3kV (monitored line to output)							
Environmental		Operating temperature: -4 to 122°F [-20 to 50°C]					
		Relative humidity: 0-95% RH, Non-condensing					
		Pollution Degree 2					
		Altitude to 2000 meters					
Certifica	tions	cULus listed (E222847), CE					

Sensed Current Limits					
Continuous	6 Sec.	1 Sec.			
100	400	1000			


Dimensions

Inches [mm]



See our website www.AutomationDirect.com for complete Engineering drawings.

Application Example



Current Sensors

AC Current Switches, Transducers and Indicators

Overview

The AcuAMP series of AC current sensors is a family of high-performance current sensors offering outstanding features, flexibility, and durability at an incredible Price. Choose from a wide selection of current transducers, switches and indicators, all designed in a rugged industry-standard feed-through package, including both fixed core and split core models.

AcuAMP current sensors are available with a broad selection of input sensing ranges for maximum flexibility across many current ratings. The current transducer output choices include 4-20 mA, 24VDC looppowered, and 0 to 10 volt self-powered analog outputs. The Current Switch outputs include isolated solid state switches available in Normally Open and Normally Closed configurations or SPDT relays.

Models with output time delay are also offered in the Current Switch series. The ACL1 Current Indicator senses AC current ranging from 0.5 to 100A and requires no power for the indicating LED.

These current sensors can be mounted in a panel or attached to the monitored conductor with a wire tie. Use the Selection Guide below to find the best sensor for your requirements.



AcuAMP AC Current Transducer Selection Guide							
Specifications	Single-Phase Transducer	Single-Phase Transducer (True RMS)	3-Phase Transducer	3-Phase Transducer (True RMS)			
Series	ACT	ACTR	3ACT	3ACTR			
Sensing Range	Selectable: ACT005: 0 to 2A 0 to 5A ACT050: 0 to 10A 0 to 20A 0 to 50A ACT200: 0 to 100A 0 to 150A 0 to 200A ACT750: 0 to 375A 0 to 500A 0 to 750A ACT2000: 0 to 1000A 0 to 1333A 0 to 2000A Fixed range: ACT400 0 to 400A ACT600 0 to 600A ACT800 0 to 800A ACT800 0 to 800A ACT1200 0 to 1200A	Selectable: ACTR005: 0 to 2A	Selectable: 3ACT030: 0 to 10A 0 to 15A 0 to 30A 3ACT100: 0 to 30A 0 to 50A 0 to 100A 3ACT200: 0 to 100A 0 to 150A 0 to 200A	Selectable: 3ACTR030: 0 to 10A 0 to 15A 0 to 30A 3ACTR100: 0 to 30A 0 to 50A 0 to 100A 3ACTR200: 0 to 100A 0 to 150A 0 to 200A			
Output	-10 models: 0–10 VDC, self-powered -42L models: 4–20 mA, loop-powered	4–20 mA, loop-powered True RMS	4 -20 mA, loop-powered	4–20 mA, loop-powered True RMS			
Frequency Range	-10 models: 50 to 60 Hz -42L models up to 200A: 20 to 100 Hz -42L models 400, 600, 800, 1200A: 50 to 60 Hz sinusoidal waveforms only	20 to 400 Hz; (40 to 400 Hz flexible split core models) sinusoidal and non-sinusoidal waveforms	50 to 60 Hz sinusoidal waveforms only	30 to 100 Hz sinusoidal and non-sinusoidal waveforms			
	ACT005, ACT050, ACT200: Fixed core: 0.75 in [19mm] dia. Split core: 0.85 in [21.6 mm] sq. ACT750, ACT2000: Fixed core: 3.0 in [76.2 mm] dia. ACT400, ACT600, ACT800: Split core: 2.22 X 1.19 in [56.3 X 30.2 mm] ACT1200 Split core: 3.44 X 2.31 in [87.3 X 58.8 mm]	ACTR005, ACTR050, ACTR200: Fixed core: 0.75 in [19mm] dia. Split core: 0.85 in [21.6 mm] sq. ACTR750, ACTR2000: Fixed core: 3.0 in [76.2 mm] dia. ACTR500, ACTR1000, ACTR2000: Flexible split core: 4.5 in [114.3 mm] dia. ACTR400, ACTR600, ACTR800: Split core: 2.22 X 1.19 in [56.3 X 30.2 mm] ACTR1200 Split core: 3.44 X 2.31 in [87.3 X 58.8 mm]	3x - Fixed core: 0.86 in [21.8 mm] dia.	3x - Fixed core: 0.86 in [21.8 mm] dia.			

www.automationdirect.com Current Sensors tCTS-1

AC Current Switches, Transducers and Indicators

			ACUAMP AC	Current Swit	ch Selectio	n Guide		
Specifications	AC Current Switches							
Series	ACSN100	ACSN250	ACS150	ACSL	ACS200	ACS050/ACS200	ACS035/ACS400	ACSX
Sensing Range	0 to 100A	0 to 250A	150A	0 to 50A	Jumper Selectable: Fixed core: 1 to 6A 6 to 40A 40 to 175A Split core: 1.75 to 6A 6 to 40A 40 to 200A	1 to 200A	2 to 400A	Jumper Selectable: Fixed core: 1.5 to 12A 12 to 55A 55 to 175A Split core: 2 to 12A 12 to 55A 55 to 200A
Setpoint (Trip Point)	Non- adjustable: 0.5 A	adjustable: Fixed core: 0.75A Split core: 1.25A	150 A (4-turn	Adjustable (3/4-turn potentiometer): ACSL010: 1-10A ACSL020: 2-20A ACSL050: 10-50A Monitored load current not required to adjust setpoint	Adjustable: (4-turn or 15-turn potentiometer) Fixed core: 1-175A Split core: 1.75-200A Monitored load current required to adjust setpoint	Adjustable: (Single turn potentiometer): ACS050: 1-50A ACS200: 4-200A	Adjustable: (3/4-turn potentiometer): ACS035: 2-35A ACS400: 25-400A	Adjustable: Fixed core: 1.5- 175A (15-turn potentiometer) Split core: 2-200A (4-turn potentiometer) Monitored load current required to adjust setpoint
Output	Isolated solid state: Normally Open 0.15 A @ 120VAC or VDC	Open 0.15 A @		Isolated solid state: Normally Open AC: 0.15 A @ 240VAC	Isolated solid state: Normally Open or Normally Closed AC model: 1A @ 240VAC Normally Open AC model: 3A @ 120VAC Normally Open or Normally Closed DC model: 0.15 A @ 30VDC	Isolated solid state: Normally Open 1A @ 240VAC	Two Independent Single Pole, Double Throw electro-mechanical relays AC: 1A @ 120VAC DC: 2A @ 30VDC	Isolated solid state: Normally Open or Normally Closed AC model: 1A @ 240VAC Normally Open AC/DC model: 0.15 A @ 240 VAC, VDC Normally Closed AC/DC model: 0.2 A @ 135 VAC/ VDC
Frequency Range	50 to 400 Hz	6 to 100 Hz	6 to 100 Hz	10 to 100 Hz	6 to 100 Hz	40 to 100 Hz	40 to 65 Hz	50 to 100 Hz
Response Time	N/A	120ms	120ms	100ms & 2s inrush delay	40 to 250 ms	0.50 sec. 5% over set point 0.20 sec. 50% over set point 0.15 sec. 100% over set point	40 - 120ms	Field adjustable time delay: 0.12 to 15 seconds
Sensing Aperture	0.30 in [8.13 mm] dia.	Split core: 0.85 in	Fixed core: 0.75 in [19mm] dia. Split core: 0.85 in [21.7 mm] sq.	Fixed core: 0.55 in [13.97 mm] dia. Split core: 0.85 in [21.7 mm] sq.	Fixed core: 0.55 in [13.97 mm] dia. Split core: 0.85 in [21.7 mm] sq.	0.75 in [19mm] dia.	1.31 in [33.3 mm] dia.	Fixed core: 0.75 in [19mm] dia. Split core: 0.85 in [21.7 mm] sq.

www.automationdirect.com Current Sensors

tCTS-3

AC Current Switches, Transducers and Indicators

AcuAMP AC Current Transducer/Switch and Indicator Selection Guide						
Specifications AC Current Transducer		AC Current Transducer/Switch	Indicator			
Series	ACTH	ACTS	ACL1			
Sensing Range	0 to 50A	1 to 200A	0 to 100A			
Setpoint (Trip Point)	Not Applicable	Adjustable: (Single turn potentiometer): ACTS050: 1-50A ACTS200: 4-200A	Non-adjustable: 0.5 A			
Output	4-20mA analog output and isolated solid state: Normally Open 1A @ 240VAC		LED Only (flashing, red)			
Frequency Range	40 to 400 Hz	40 to 400 Hz	50 to 400 Hz			
Response Time	400ms at 100% duty cycle, or duty cycle period plus 40ms	Switch: 0.50 sec. 5% over set point 0.20 sec. 50% over set point 0.15 sec. 100% over set point Analog: < 0.30 sec. 90% step change < 0.40 sec. 100% step change	N/A			
Sensing Aperture	0.86 in [21.9 mm] sq.	0.75 in [19mm] dia.	0.30 in [7.6 mm] dia.			



Click on the thumbnail or go to https://www.automationdirect.com/VID-CT-0001 for a short introductory video on the AcuAmp Current Switches, Transducers and Indicators

www.automationdirect.com Current Sensors

AC Current Sensors, Switches and Transducers Application Guide


Application Guide

ACUAMP current sensors are a great fit for many applications including material handling, fan and pump applications, and heating systems. With current transducers, current switches and current indicators, this sensor family gives you


valuable data for processes ranging from monitoring loads to preventive maintenance. Models with the ability to read True RMS non-sinusoidal waveforms make it easy to monitor applications using variable frequency drives.

Use the application examples to help choose the best sensor model for your

Pump Jam & Suction Loss Protection




Heater Life Prediction




Crusher/Grinder/Shredder Motor Interlocks

The performance of size reduction equipment like crushers or grinders can be optimized by controlling the in-feed in order to:


- Help prevent jamming
- Improve the uniformity of the resultant product
- Enhance overall production efficiency



Pump Load Monitoring



Lamp Failure Detection



Electric Motor Load Status

